

FIXTURE HANGING ACCESSORIES



TOP/END

FIXTURE HOOKS

STEEL ZINC CHROMATE
For Hanging Industrial Light Fixtures
PACKAGED IN 1/4 KEG CARTONS



SIDE



STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
FHK1	21400	Top/End Mount	4.50	100	45.13/c
FHK2	21405	Side Mount	4.80	100	45.13/c

TIE WIRE ACOUSTICAL TOGGLE BOLTS

TIE WIRE ACOUSTICAL TOGGLE BOLTS ARE PRIMARILY FOR OVERHEAD APPLICATIONS. THE WINGED END IS INSERTED THROUGH THE DRYWALL, CEILING, TILE, ETC., AND EXPANDS BEHIND THAT MEDIUM WHILE THE 1/4" x 1-1/4" FENDER WASHER AND HEX NUT ACT TO SECURE THE ANCHOR TO THE EXTERIOR OF THE HOLE.



INCLUDES:
(1) TIE WIRE 1/4-20
TOGGLE BOLT
(1) 1/4-20 NUT
(1) 1/4 WASHER
(1) 1/4 TOGGLE WING

STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
JTWA144	81402	1/4" x 4" Toggle Bolt	2.47	25	38.00/ea pkg
JTWA145	81404	1/4" x 5" Toggle Bolt	2.33	25	40.93/ea pkg



HANGER BOLTS

STEEL ZINC CHROMATE



STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
JHAB9	81000	10-24 x 2	1.12	100	11.75/c
JHAB10	81001	1/4-20 x 3	3.10	100	23.13/c
JHAB11	81002	3/8-16 x 3	7.65	100	50.50/c
JHAB13	84111	3/8-16 x 4	9.42	100	53.50/c NEW
JHAB12	84110	3/8-16 x 6	7.31	50	50.03/ea. pkg.



HANGER BOLT DRIVERS

WITH 1/4" POWER HEX SHANKS
INTERNAL THREADS FOR DRIVING
HANGER BOLTS AND THREADED ROD

STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
HABD10	23275	1/4-20 x 2 9/16 BOLT DRIVER	.06	1	11.23/ea
HABD12	23280	3/8-16 x 2 9/16 BOLT DRIVER	.08	1	14.28/ea