

LED Directional Lamps



Item Number	Ordering Abbreviation	ENERGY STAR®	Wattage (W)	Lumens	Beam Angle	CBCP (cd)	Color	CRI	Lifetime (Hrs)	Replacing
PAR38										
78735	LED10PAR38/SG/830/WSP15	Yes	10	640	15°	6900	3000K	82	50,000	60W Halogen
78796	LED15PAR38/SG/830/SP10	Yes	15	760	10°	16000	3000K	89	50,000	60W Halogen
78006	LED15PAR38/830/WSP12/SG2	N/A	15	760	12°	11000	3000K	89	50,000	60W Halogen
78795*	LED15PAR38/SG/830/WSP12	Yes	15	760	12°	11000	3000K	89	50,000	60W Halogen
78719	LED15PAR38/SG/827/WSP15	Yes	15	700	15°	7000	2700K	89	50,000	60W Halogen
78498	LED15PAR38/SG/830/WSP15	Yes	15	760	15°	7500	3000K	89	50,000	60W Halogen
78436	LED16PAR38/DIM/827/FL40	Yes	16	950	40°	1680	2700K	81	25,000	75W Halogen
78658*	LED18PAR38/DIM/827/FL40	Yes	18	860	40°	1150	2700K	84	25,000	75W Halogen
78435	LED16PAR38/DIM/827/NFL25	Yes	16	950	25°	4300	2700K	81	25,000	75W Halogen
78657*	LED18PAR38/DIM/827/NFL25	Yes	18	860	25°	3680	2700K	84	25,000	75W Halogen
78433	LED16PAR38/DIM/830/NFL25	Yes	16	1000	25°	4500	3000K	82	25,000	75W Halogen
78640*	LED18PAR38/DIM/830/NFL25	Yes	18	900	25°	3100	3000K	87	50,000	75W Halogen
78434	LED16PAR38/DIM/830/FL40	Yes	16	1000	40°	1745	3000K	82	25,000	75W Halogen
78641*	LED18PAR38/DIM/830/FL40	Yes	18	900	40°	1500	3000K	87	50,000	75W Halogen
72531	LED16PAR38/DIM/850/FL40 [RP]	N/A	16	950	40°	2000	5000K	86	25,000	75W Halogen
78761*	LED18PAR38/DIM/840/FL40	Yes	18	920	40°	1620	4000K	89	50,000	75W Halogen
78904	LED20PAR38/DIM/P/927/WSP12	Yes	20	1000	12°	14000	2700K	93	40,000	90W Halogen
78906	LED20PAR38/DIM/P/930/WSP12	Yes	20	1050	12°	18000	3000K	93	40,000	90W Halogen
78207	LED20PAR38/DIM/830/FL40	N/A	20	1300	40°	2500	3000K	82	25,000	120W Halogen
78807*	LED24PAR38/DIM/830/FL40	No	24	1300	40°	2020	3000K	85	25,000	90W Halogen
78745	LED21PAR38/DIM/P/930/FL30	Yes	21	1150	30°	3700	3000K	95	50,000	90W Halogen
78741	LED21PAR38/GU24/DIM/P/930/FL30	Yes	21	1150	30°	3700	3000K	95	50,000	90W Halogen
78806*	LED24PAR38/DIM/830/NFL25	No	24	1300	25°	4930	3000K	85	25,000	90W Halogen

PAR38 High Output

78958	LED15PAR38/SGHO/830/NFL25	Yes	15	1050	25°	5000	3000K	82	25,000	24W HID
78957	LED15PAR38/SGHO/830/SP10	Yes	15	1050	10°	26000	3000K	82	25,000	24W HID

PAR30

78662	LED10PAR30/DIM/SG/827/SP10	Yes	10	510	10°	11000	2700K	89	50,000	50PAR30
78576	LED10PAR30/DIM/SG/827/WSP15	Yes	10	510	15°	5000	2700K	89	50,000	50PAR30
78919	LED10PAR30/DIM/SG/827/NFL20	No	10	600	20°	3000	2700K	89	25,000	50PAR30
78663	LED10PAR30/DIM/SG/827/NFL25	Yes	10	510	25°	2300	2700K	89	50,000	50PAR30
78664	LED10PAR30/DIM/SG/830/SP10	Yes	10	550	10°	12000	3000K	89	50,000	50PAR30
78665	LED10PAR30/DIM/SG/830/WSP15	Yes	10	550	15°	5400	3000K	89	50,000	50PAR30
78666	LED10PAR30/DIM/SG/830/NFL25	Yes	10	550	25°	2500	3000K	89	50,000	50PAR30
78747	LED15PAR30/DIM/P/930/FL40	Yes	15	880	40°	1700	3000K	95	50,000	60W Halogen
78743	LED15PAR30/GU24/DIM/P/930/FL40	Yes	15	880	40°	1700	3000K	95	50,000	50W Halogen

*Products being phased out

N/A = Information not available at this time

O/T = Product is currently on test





Item Number	Ordering Abbreviation	ENERGY STAR®	Wattage (W)	Lumens	Beam Angle	CBCP (cd)	Color	CRI	Lifetime (Hrs)	Replacing
PAR30LN										
72526	LED13PAR30LN/DIM/850/FL40 [RP]	N/A	13	800	40°	1690	5000K	86	25,000	50W Halogen
78431	LED13PAR30LN/DIM/827/NFL25	Yes	13	790	25°	3400	2700K	82	25,000	50W Halogen
78655*	LED15PAR30LN/DIM/827/NFL25	Yes	15	700	25°	2910	2700K	84	25,000	50W Halogen
78432	LED13PAR30LN/DIM/827/FL40	Yes	13	790	40°	1400	2700K	82	25,000	50W Halogen
78656*	LED15PAR30LN/DIM/827/FL40	Yes	15	700	40°	1420	2700K	84	25,000	50W Halogen
78429	LED13PAR30LN/DIM/830/NFL25	Yes	13	820	25°	3600	3000K	82	25,000	50W Halogen
78638*	LED15PAR30LN/DIM/830/NFL25	Yes	15	770	25°	2900	3000K	87	50,000	50W Halogen
78430	LED13PAR30LN/DIM/830/FL40	Yes	13	820	40°	1450	3000K	82	25,000	50W Halogen
78639*	LED15PAR30LN/DIM/830/FL40	Yes	15	770	40°	1300	3000K	87	50,000	50W Halogen
78720	LED17PAR30LN/DIM/830/WSP20	N/A	17	1200	20°	5700	3000K	81	25,000	75W Halogen
78746	LED17PAR30LN/DIM/P/930/NFL25	Yes	17	970	25°	3400	3000K	95	50,000	75W Halogen
78742	LED17PAR30LN/GU24/DIM/P/930/NFL25	Yes	17	970	25°	3400	3000K	95	50,000	75W Halogen
78758	LED17PAR30LN/DIM/P/930/FL40	Yes	17	970	40°	1600	3000K	95	50,000	75W Halogen
78804*	LED18PAR30LN/DIM/830/NFL25	Yes	18	950	25°	3810	3000K	85	25,000	75W Halogen
78805*	LED18PAR30LN/DIM/830/FL40	No	18	950	40°	1500	3000K	85	25,000	75W Halogen



PAR20										
72527	LED7PAR20/DIM/850/FL36 [RP]	N/A	7	430	30°	1000	5000K	86	25,000	50W Halogen
78425	LED8PAR20/DIM/827/NFL25	Yes	8	450	25°	1700	2700K	82	25,000	50W Halogen
78653*	LED8PAR20/DIM/827/NFL25	Yes	8	320	25°	1150	2700K	85	25,000	35W Halogen
78426	LED8PAR20/DIM/827/FL36	Yes	8	450	36°	900	2700K	82	25,000	50W Halogen
78654*	LED8PAR20/DIM/827/FL36	Yes	8	320	36°	670	2700K	85	25,000	35W Halogen
78427	LED8PAR20/DIM/H/830/NFL25	Yes	8	450	25°	1900	3000K	82	25,000	50W Halogen
78802*	LED8PAR20/DIM/H/830/NFL25	Yes	8	400	25°	2000	3000K	85	25,000	35W Halogen
78428	LED8PAR20/DIM/H/830/FL36	Yes	8	450	36°	1000	3000K	82	25,000	50W Halogen
78803*	LED8PAR20/DIM/H/830/FL36	Yes	8	400	36°	675	3000K	85	25,000	35W Halogen
78963	LED10PAR20/DIM/825/WSP20/SG	N/A	10	550	20°	2200	2500K	80	25,000	50W Halogen
78748	LED10PAR20/DIM/P/930/FL30	Yes	10	550	30°	1600	3000K	95	25,000	50W Halogen
78744	LED10PAR20/GU24/DIM/P/930/FL30	Yes	10	550	30°	1600	3000K	95	25,000	50W Halogen



PAR16										
78964	LED7PAR16/DIM/GU10/830/FL36	Yes	7	350	36°	650	3000K	84	25,000	35W Halogen
78834*	LED5.5PAR16/GU10/830/NFL25	Yes	5.5	300	30°	460	3000K	84	25,000	35W Halogen
78965	LED7PAR16/DIM/830/FL36	Yes	7	350	36°	650	3000K	84	25,000	35W Halogen
78831*	LED5.5PAR16/830/NFL25	Yes	5.5	300	30°	460	3000K	80	50,000	35W Halogen
72546	LED8PAR16/DIM/930/FL36P [RP]	O/T	8	390	36°	950	3000K	90	25,000	35W Halogen
72547	LED8PAR16/GU10/DIM/930/FL36P [RP]	O/T	8	390	36°	950	3000K	90	25,000	35W Halogen
72676	LED8PAR16/DIM/GU10/830/FL35	N/A	8	490	35°	1300	3000K	81	25,000	60W Halogen
78896*	LED10PAR16/GU10/DIM/830/FL35	O/T	10	500	35°	1290	3000K	80	25,000	60W Halogen
72677	LED8PAR16/DIM/830/FL35	N/A	8	490	35°	1300	3000K	81	25,000	60W Halogen
78895*	LED10PAR16/DIM/830/FL35	N/A	10	500	35°	1290	3000K	80	25,000	60W Halogen



MR16										
78423	LED6MR16/DIM/827/NFL25	Yes	6	350	25°	1100	2700K	83	25,000	20W Halogen
78651*	LED6MR16/DIM/827/NFL25	N/A	6	240	25°	790	2700K	85	35,000	20W Halogen
78424	LED6MR16/DIM/827/FL36	Yes	6	350	36°	700	2700K	83	25,000	20W Halogen
78652*	LED6MR16/DIM/827/FL36	Yes	6	240	36°	440	2700K	86	35,000	20W Halogen
78421	LED6MR16/DIM/830/NFL25	Yes	6	350	25°	1300	3000K	85	25,000	20W Halogen
78634*	LED6MR16/DIM/830/NFL25	Yes	6	300	25°	860	3000K	87	35,000	20W Halogen
78422	LED6MR16/DIM/830/FL36	Yes	6	350	36°	730	3000K	85	25,000	20W Halogen
78635*	LED6MR16/DIM/830/FL36	Yes	6	300	36°	590	3000K	87	35,000	20W Halogen
78210	LED7MR16/DIM/825/NFL25	N/A	7	500	25°	1850	2500K	80	25,000	50W Halogen
78420	LED7MR16/DIM/830/NFL25	Yes	7	525	25°	2340	3000K	82	25,000	50W Halogen
78201*	LED8MR16/DIM/830/NFL25	Yes	8	525	25°	2325	3000K	82	25,000	50W Halogen
72544	LED7MR16/DIM/930/FL36P	N/A	7	400	36°	970	3000K	95	25,000	50W Halogen

*Products being phased out

N/A = Information not available at this time

O/T = Product is currently on test



Item Number	Ordering Abbreviation	ENERGY STAR®	Wattage (W)	Lumens	Color	CRI	Lifetime (Hrs)	Replacing
R20, BR30, BR40								
78694	LED5R20/DIM827	No	5	325	2700K	80	25,000	45W Incandescent
78489*	LED6R20/DIM/827	Yes	6	350	2700K	81	25,000	35W Incandescent
78485	LED7R20/DIM/HO/827/G3	No	7	500	2700K	80	25,000	50W Incandescent
78016	LED8R20/DIM/827	Yes	8	520	2700K	82	25,000	50W Incandescent
72890	LED8R20/DIM/SE/830	N/A	8	830	3000K	82	25,000	50W Incandescent
78691	LED9BR30/DIM/827	No	9	650	2700K	80	25,000	65W Incandescent
78413	LED11BR30/DIM/HO/827/G3	No	11	800	2700K	80	25,000	65W Incandescent
78014	LED12BR30/DIM/HO/827	Yes	12	850	2700K	82	25,000	65W Incandescent
78917*	LED12BR30/DIM/827	Yes	12	620	2700K	80	25,000	65W Incandescent
78809*	LED14BR30/DIM/827/NS	Yes	14	800	2700K	80	25,000	65W Incandescent
72888	LED12BR30/DIM/SE/830	N/A	12	850	3000K	82	25,000	65W Incandescent
72889	LED12BR40/DIM/SE/830	N/A	12	850	3000K	82	25,000	65W Incandescent
78416	LED15BR40/DIM/HO/827	No	15	1100	2700K	80	25,000	100W Incandescent
78627	LED16BR40/DIM/825	N/A	16	1000	2500K	80	25,000	100W Incandescent
78810*	LED18BR40/DIM/827	No	18	870	2700K	80	25,000	65W Incandescent
78386	LED16BR40/DIM/827	Yes	16	1100	2700K	82	25,000	65W Incandescent

*Products being phased out

N/A = Information not available at this time

O/T = Product is currently on test

OSRAM SYLVANIA

Corporate Headquarters:

100 Endicott Street
Danvers, MA 01923 USA
Phone 1-800-LIGHTBULB
www.sylvania.com

For additional information about our currently stocked products or to place an order, please contact your local Viking Electric Supply sales representative.

Viking Electric Supply
www.vikingelectric.com

SYLVANIA is a registered trademark of OSRAM SYLVANIA Inc.
ENERGY STAR is a registered trademark of the U.S. Government.
Specifications subject to change without notice.

