

RACK-A-TIERS®






* Established 1994 - Established 1994 - Established 1994 - BY ELECTRICIANS - BY ELECTRICIANS



2017-18 CATALOG

CALL on TEXT: 1-888-939-9991

| Description 6.5 Blank Plate | Page | Part# D612 | Description Mag Daddy | Page 50 | Part# RMseries |
|---|----------|---------------------|---|------------|-------------------|
| AC Sensor | 29 | 99000 | Magnepull | 22 | 42800 |
| Aerial Tool Bin | 31 | ATB1312 | | 23 | 42900 |
| Aircraft Cable & Wire Crimps | 44 | | Magnespot Magnetic Bit Holder | 42 | 72000 |
| Alignment Tool | 12 | SCseries 68075 | Magnetizer / Demagnetizer | 42 | 70988 |
| All-American Pull Buddies | 15 | 42series | Multi-Bit Step Drills | 34 | MLTseries |
| Auger - Standard & Tri-Cut | 37 | AWseries | Nut Blaster XL and XXL | 43 | 72101, 72102 |
| · · | 37 | AVVSEITES | | 43 19 | ENseries |
| Auger Bit File | 14 | BPseries | Nylon Fish Tapes OverDrive Bits | | AW34OD, AW78OD |
| Bag Pipers Bat Flashlight | 28 | 53700, 53750 | Owl Eye | 28 | 53300 |
| Bend-All | 7 | 77455 | Panel Buddy Knockout Kit | 43 | 7WBK100 |
| Better Bend | 11 | 6series | Pencil & Quick Draw Felt Pen | 24 | 52466, 52486 |
| | 6 | 55632 | | 14 | • |
| Big E-Z | | | Penguin Puller Sr & Jr, The | | 69700, 69705 |
| Bolt Star | 45 | 672series | Phase It Right | 18 | 526series |
| Bolt Template | 45 | 67441 | Phazer 3 | 18 | 52700 |
| Booty Pack | 32 | 47099 | Picquic Screwdrivers | 42 | Pseries |
| Breaker Lok | 52 | 75000 | Pipe Spinner | 34 | 409series |
| Bulldog Benders, The | 7 | 78series | Pipe Vipers | 11 | 58series |
| Bumper Balls | 37 | BB3412 | Piranhabits - High Speed Steel | 36 | FLXseries |
| Butt Pouches | 27 | 43015, 43095, 43100 | Plastic Coated Fiberfish | 20 | PCFseries |
| Cable Caddy & Cable Truck | 5 | CC1200, CT1100 | Plastic Coated Glowfish | 20 | GLFseries |
| Cable Cart & Cable Cart Data | 5 | CC2000, CC2000D | Plate Vise | 25 | 13355 |
| Cable Glydz | 14 | | Plug Master | 29 | 99102 |
| Caddy Mac | 4 | 11901, 11902 | Plugfones | 27 | Plseries |
| Carbide Tipped Steel Cutters | 34 | 92HCseries | Pocket-Kart | 3 | 56000 |
| Chip Catcher | 39 | 84100 | Polyester Fish Tape | 19 | EPseries |
| Code Simplified | | 731series | Pop Open Garbage Can | 33 | 51010 |
| Combo Tool Belt & Pouches | 26 | 432series | ProGrabit | 42 | 72120 |
| Copper Wire Stripper Jr. | 8 | 47030 | Q-Bit Drywall Hole Cutter | 34 | 427series |
| Countertop and Floor Boxes | 46-47 | Vseries | Quattro Flex Auger Bits | 36 | QTTseries |
| Croc's Needle Nose Wire Strippers & Jr. | 9 | 47000, 47002 | Rack-A-Tiers | 1 | 11455 |
| Crow's Feet | 49 | SCF38 | Rack-N-Go | 6 | 11460 |
| CWS-1, CWS-2 Copper Wire Strippers | 8 | 47100, 47200 | Racky Driver Bits | 40-41 | 7bitseries |
| Dirt Auger System | 37 | ETD034 | Racky Straps | 50 | RS10series |
| Dirt Bag | 39 | 84000 | Racky Wipes and Drop Sheet | 32 | RAGseries |
| Driller's Dust Bowl | 38 | 48000 | RAT500 & RAT750 | 49 | RAT500, RAT750 |
| Dryconn Waerproof Connectors | 45 | Kiseries | Reel Mac & Spindles | 5 | 118series |
| Dual Check Non Contact Voltage Tester | 29 | 99150 | Reusable Jar and Trar | 33 | REJAR |
| Easy Stripper | 8 | 47020 | Rev-Bit | 43 | 91700 |
| Efergy Products | 30 | EFseries | Robertson Screwdrivers | 51 | SDseries |
| Elasco Products | 48 | Elseries | Rolgear Screwdriver | 42 | SDR14 |
| Exploding Garbage Can | 33 | 51000 | Ropematic Pro | 16 | 42400 |
| Extendo Nut Driver | 13 | NT1050 | Rough-In Stick, The | 24 | 82000 |
| EZ Bulb | 53 | 54300, 54400, 54500 | Shinmates | 31 | 65100, 65200 |
| EZ Generator Switch | 30 | 99215 | Shoppe Rocket | 29 | 45200 |
| E-Z Roll & E-Z Roll Multi | 6 | 55455, 55456 | Sidewinders | 48 | U18series |
| Fiberfish Attachments | 21 | FIBseries | Silver Bullet Rechargeable Flashlight | 28 | 53800 |
| Fibersnakes 1/4" | 21 | FIBRseries | Sluggo-Ox | 25 | 67119 |
| Fibersnakes 3/16" | 21 | FIBTseries | Snatch Strap | 17 | 69455 |
| Fibersnakes 5/16" | 21 | FIBLseries | Spool Mac | 4 | 1190series |
| Fire Fly | 28 | 53400 | Spool Mule | 3 | 40500 |
| Fish Heads | 17 | 69010 | Standard Super Set, Super Set 18 | 20 | SS1series |
| Flex Flyers | 16 | 69050, 69075 | Staple Shark | 9 | 52455 |
| Flex Puller | 14 | 42620 | Steve's Sticky Tags | 18 | 52500 |
| GD Center Finder | 13 | 67500 | Stick Bug & Jr. | 28 | 53500, 53600 |
| Glow Safe 360 | 28 | 54000, 54020 | Stick, The | 2 | 11555 |
| Guide Tool | 36 | FIB-GUD | Sting Ray | 15 | 40400 |
| Guide-O, The | 35 | 94series | Stud Ball | 25 | 52300 |
| Handi Hoops | 50 | HH1010 | Stud Buddies Connectors | 49 | SBseries |
| Head Light | 28 | 54050, 54075 | Support Belt | 26 | 434series |
| Holdsabit | 43 | 70000 | Sure Mark | 24 | 82050 |
| Hole-In-One - Hole Cutters | 38 | 90200, 90300, 90400 | Suspenders | 27 | 43606 |
| Hooker - Wrench Adaptor | 6 | 10455 | Switch Bits | 36 | ETseries |
| Hoppy Bender, The | 10 | 57050, 57075 | Temporary Cable Guard | 48 | TCG5, TPG5 |
| Hot Spot | 52 | T2series | Timberwolf Hand Cleaning Products | 32 | TWseries |
| Industrial Cord Connector | 52 | 97series | Tom Two-Way Connector | 49 | TT500 |
| Javelin | 35 | 95000 | Tool Carriers | 26 | 43706, 43707 |
| Jet Level | 29 | 45404 | | 44 | TC1400 |
| Knee Pads | 29 | 66455 | Top Hat Cover Tug Wise Standard and Deluxe | 3 | 11931, 11932 |
| Knee Pads KO Killers | 49 | KOKseries | Ultimate AC Sensor | 3 29 | 99001 |
| Ladder-Mate | 31 | 65300 | U-Phase Wire Marker | 29 17 | 5249series |
| | | | | | |
| | 23 | 88455 | Van Magnets | 32-33 | RVseries |
| Laser Plumb Bob | | 83000 | V-Cutter | 9 | 47010 |
| Laserline | 22 | | Miss Ossellis 10 set | | 44700 |
| Laserline LB Wire Guide | 15 | 42200 | Wire Spool Hand Cart | 4 | 11700 |
| Laserline LB Wire Guide Level Jacks | 15 49 | 42200 LJseries | Wire Tub | 2 | 18455 |
| Laserline LB Wire Guide | 15 | 42200 | · | | |



FOLDING WIRE CADD

FEATURES

- Folds to 1" wide to easily fit in your van
- Easy to carry: 1" x 23"
- Holds up to six reels of wire

Maximum spool quantity: 6 reels 500' of #10 AWG wire Maximum spool diameter: 8" Max spool width: 9"



THE STICK

STUD MOUNTED WIRE DISPENSER

The Stick installs quickly & easily to any standard stud. Its compact design allows for easy storage once the job is complete.

FEATURES:

Weight capacity: 200 lbs Maximum 15" reel width Part# 11555



WRE TUB Part# 18455

The Wire Tub allows you to easily dispense and rewind wire. Don't waste a single foot of wire -- rewind it in the Wire Tub and get ready for installation!

- 360 degree feed adjusts automatically for easy dispensing
- 3-way adjustable center hub
- Removable top plate has a handle for rewinding wire!
- Large 24" diameter capacity















- *P. MODEL* (15" x 15") - 4 screw holes for easy attachment
- Works with wooden and plastic reels
- Standard model can handle up to 1000 lbs Part# 11931

MGUSE DELUXE MODEL (21.5" x 21.5")

- 4 screw holes for easy attachment
- Works with wooden and plastic reels
- Can handle up to 2000 lbs
- Made of 3/8" thick aluminum alloy and built to handle anything





Save your fingertips! Start using the Pocket Kart to easily carry wire reels of all sizes. Just slip it in and pick it up.



- Light weight
- Swivelling handle
- Folds up when not in use
- Fits in pouches
- Fits in pockets
- Holds up to 200 lbs

SPOOLMULE



The Spool Mule is a simple, yet effective tool for re-spooling wire, rope,

and a variety of other cables. Using only a drill, a 3/4" conduit and the Spool Mule kit you can easily roll up coils of wire or transfer cable from broken spools to an intact empty spool.

FEATURES:

- Kit includes: 3/4" conduit to drill attachment, and (2) Spool Mule brackets
- Works with any sized spool
- *34" Conduit and Rack-A-Tiers Not Included





Part# 56000

CADDY MAC 2...



Caddy Mac #2 holds 16 spools of #10 awg or 24 spools of #12 awg. Hinge design allows easy access to all spools for wire dispensing and folds for compact storage.

Spindles swing out to set position for convenient loading of wire spools.

Inner spindles store in special loops which can hold four pieces and will not fall out during transportation.

| Number of Spools | Max Spool Dia | Load Capacity | Weight | Width | Additional Features |
|------------------|---------------|---------------|--------|-------|-------------------------------|
| 16-#10 awg. or | 7.5 in | 400 lbs | 72 lb. | 26 in | Folds up for compact storage. |
| 24-#12 awg. | 19 cm | 180 Kg. | 33 kg. | 66 cm | |

- All steel frame construction
- Easy set-up for cable dispensing
- No loose pieces

- 350 lb (160 kg) load capacity
- Priced right built to last

| | Max Reel Width | Max Spool Dia | Reel Capacity | Weight | Width | Additional Features |
|--|------------------|---------------|---------------|------------------|-------|--|
| 63.5 cm 101 cm 160 kg 35 kg. 80 cm Compact storage. Ship weight: 150 | 25 in 63.5 cm | | | 76 lb. 35 kg. | | All steel frame, easy set-up for cable disper Compact storage. Ship weight: 150 lbs |

Caddy Mac #1 transports spools on spindles and works as a dolly! Wire is dispensed while laying flat. 1/2" solid spindles are attached to cart, no loose pieces. Spindles lock in place, even during transportation. Spindles swing out to set position for convenient loading of wire spools.

| Number of Spools | Max Spool Dia | Load Capacity | Weight | Width | Additional Features |
|------------------|---------------|---------------|--------|-------|--|
| 8-#10 awg. or | 7.5 in | 200 lbs | 72 lb. | 26 in | Transports spools on spindles and works as a dolly. Wire is dispensed while laying flat. |
| 12-#12 awg. | 19 cm | 90 kg | 33 kg. | 66 cm | |




WIRE SPOOL HAND CART

Dispenses (8) 5" Wide Reels Or 4) 6 to 10" Wide Reels, Up to 7" Dia.

- Height 20"
- Width 15"
- Length 26"
- Number of Spindles 4







Screw type telescoping reel jack for 26 to 56" diameter reels.

Screw type telescoping reel jack for 46 to 96" diameter reels.

REEL MAC 80

Heavy duty ratchet drive reel jack for reels up to 90" in diameter. Convenient, detachable ratchet handle stores in base when not in use. Mfg. Note: Reel Macs sold as singles, buy 2 for a set.



Part# 11860



Part# 11870



Part# 11880

| REEL MAC & JACK-A-TIER | | | | | | |
|------------------------|--------|---------------|----------|--------|--|--|
| Description | Part # | Reel Diameter | Capacity | Weight | | |
| Reel Mac #60 | 11860 | 26-56" | 2500lb | 27lbs | | |
| Reel Mac #70 | 11870 | 46-96" | 2500lb | 46lbs | | |
| Reel Mac #80 | 11880 | up to 90" | 3750lb | 99lbs | | |

| Corresponding SPINDLES | | | | | |
|------------------------|--------|---------------|----------|--------|--|
| Description | Part # | Dimensions | Capacity | Weight | |
| #61 | 11861 | 2 3/8" x 62" | 5000lb | 39lbs | |
| #71 | 11871 | 2 3/8" x 76" | 5000lb | 47lbs | |
| #81 | 11881 | 3 1/2" x 100" | 7500lb | 119lbs | |

CABLE TRUCK & CABLE CADDY



- Constructed of rugged 1" steel tubing.
- Both are 43" tall with 7" rubber wheels.
- Both can accommodate spools up to 16" wide on solid steel 1/2" axles.
- Cable Caddy features 6 axle positions for unlimited versatility.
- Cable Truck has 4 axle positions and a solid steel plate for transporting material.




Part# CT1100 - Cable Truck

Part# CC1200 - Cable Caddy




- Comes with interchangeable 1" and 3/4" axles.
- Holds up to 30 spools of THHN.
- Vertical racks swing forward for easy loading
- Space for plywood work table on top

Dimensions: 40W x 48L x 48H8" W / Shipping weight: 185 lbs









- 150 lbs load tested

- Rigid steel construction
- Light-weight design
- Compact (fits in any job box)
- Holds reels up to 24"
- Replacement wheels available

dispense wire directly from your pipe bender or 1" EMT.

The E-Z Roll Wire Rack is the ultra compact and collapsible wheeled wire dis-

penser. When you're ready to pull wire, wheel the E-Z Roll into position and

GET THE MOST OUT OF YOUR EZ-ROLL WIRE RACK WITH THE NEW EZ-ROLL MULTI. THIS HANDY ADD-ON EXTENDS THE EZ-ROLL'S USE BY ALLOWING MORE WIRE SPOOLS TO BE ADDED, GIVING IT EVEN MORE FUNTIONALITY 8 CAPACITY.





FEATURES:

- 300 lbs load tested
- Rigid steel construction
- Light-weight design
- Compact (fits in any job box)
- Holds up to 32"

The Big E-Z utilizes the same design and great features as the original EZRoll while allowing you to dispense larger wire spools.

*PIPE NOT INCLUDED

Part# 55455





The Hooker Pipe Wrench Adaptor lets you turn your Rack-A-Tiers Wire Dispensers into a pipe vise.

FEATURES

- Light weight
- Easy to use
- Fast implementation
- Inexpensive
- To be used with an 18" rigid pipe wrench

Part# 10455

THE RACK-N-GO GET MOVING WITH THE RACK-N-GO!

Easily mount your Rack-A-Tiers wire dispenser onto the mobile Rack-N-Go framework. The Rack-N-Go expands to support up to a 42" wide spindle.

- 320 lbs load tested

- Locking casters keeps your Racks in place while dispensing Roll your wire spools and dispensers easily through a bu

- Collapsed 16" x 32'

- Expanded 16" x 52"

*RACK-A-TIERS NOT INCLUDED











VISIT US AT: www.Rack-A-Tiers.com FMAIL; Sales@Rack-A-Tiers.com 7011 FREE: (888) 939-9991

Part# 77455

COPPER WIRE STRIPPE

RECOVER COPPER & ALUMINUM WIRE QUICKLY AND EASILY WITH THESE MONEY MAKING MACHINES!

The top selling CWS-2 model weighs in at only 45lbs. This wire stripper is compact enough to easily move around, but still has the ability to strip a wide range of wire.



- Strips from 14 AWG to 1000 MCM (1.45" diameter)
- Strips NMSC cable 10-14 AWG
- 1/2 HP Motor
- All aluminum frame
- Hardened one piece blade
- Strips solid core or braided wire Blade made from tool steel
- Blade easily re-sharpened
- Fully adjustable wire guide

Part# 47200

COPPER WIRE STRIPPER 1 -

The CWS-1 is the largest wire stripper available from Rack-A-Tiers. Powered by a 1 HP motor and with the ability to strip up to 3" in diameter, there isn't much this wire stripper can't handle.



- Strips 14 AWG to up to 3" in diameter
- Strips NMSC cable 10-14 AWG
- 1 HP motor
- All aluminum frame
- Hardened one piece blade
- Strips solid core or braided wire Blade made from tool steel
- Blade easily re-sharpened
- Fully adjustable wire guide
- Bench model anti-slip base

Part# 47100

CWS JR. OUTER JACKET AND I INNER WIRE



Strip the cover off your scrap wire in minutes with the Easy Stripper! Increase your earnings on every single job you complete



FEATURES:

- Less than 10% the price of a standard motorized wire stripper
- Strips 12 to 4/0 wire
- Powered by any normal power drill
- Way easier and faster than using your
- Environmentally friendly no burning
- For Light Use Only

Part# 47020



- Wire Range: 14 AWG 4/0
- Strips NMSC cable 10-14 AWG
- All aluminum frame

A low cost alternative to the CWS-2, the Copper Wire Strip-

per Jr. is the money making tool that you need in your ware-

house. Driven by a standard power drill, you'll get more than

double the money from your scrap wire. It's that simple!

- Single pass cuts outer jacket & one inner wire
- Hardened one piece blade
- Strips solid core or braided wire
- Blade made from tool steel
- Blade easily re-sharpened
- Fully adjustable wire guide

Part# 47030

REPLACEMENT PARTS

Replacement Blade - Part# 47100B Red Feed Guide - Part# 47100G Replacement Pulling Wheels - Part# 47100W

nent Blade - Part# 47200B Red Feed Guide - Part# 47200G Replacement Pulling Wheels - Part# 47200W

Replacement Blade 1st Edition - Part# 47020B Replacement Blade 2nd Edition - Part# 47020B2

ent Blade - Part# 47030B Red Feed Guide - Part# 47030G ment Pulling Wheels - Part# 47030W



NEEDLE NOSE WIRE STRIPPERS

Sometimes referred to as the best wire strippers on the market, the Croc's Needle Nose Wire Strippers will impress even the toughest critics. These strippers have countless features, each designed to make your job easier and more productive.

- Glow in the dark handles
- Ergonomic handle design for maximum comfort
- Needle nose tips
- Strip from 22-10 AWG
- Barrel Sleeve Crimper
- NMSC cutter near the "nose" of the stripper
- 8-32 and 6-32 bolt cutters

Part# 47000



Introducing the Croc's Jr., A compact and lightweight version of the original. This model serves as an affordable predecessor to the original without skimping on its numerous applications.

- Glow in the dark handles
- Ergonomic handle design for maximum comfort
- Compact design
- Strip from 22-8 AWG
- 8-32 and 6-32 bolt cutters

Part# 47002

SEE IT IN ACTION

STRIPS CABLE IN OR OUT OF ELECTRICAL

V-CUTTER

BOXES WITH EASY TO PUSH ACTION One of the smartest inventions to come to market this

decade is the V-Cutter. This simple little blade attaches to most wire strippers and allows you to strip cable with a single swipe.

- A new way to strip NMSC cable
- Easily attaches to most wire strippers
- Strips cable in or out of electrical boxes with action
- Virtually eliminates nicking or cutting the wire insulator

PART# 52455

Part# 47010



- Includes a handy staple puller and pry bar for multi-purpose use!
- Ruler for quick on the job measurements.
- Use as a quick carpenter's square.
- Holds staples in tight spots and will open a beer bottle at the end of the day.





HOLDS STAPLES!



PRY BAR!




SEE IT IN ACTION









STEP THREE



- A "Stop" attached to the Bender head used to create exact & repeatable bends every time.


- Simplified "Multipliers" engraved into the bender for placing the "Stop" prior to making offsets & four-point saddles.
- Special 22.5 and 45 degree marks engraved into the bender for placement of conduit bend marks as well as standard degree marks for stop placement. Used together for bending three-point saddles without reversing the conduit in the shoe.
- Handy reference charts attached to the handle for locating bend marks.

57050 - 1/2" Hoppy Bender

57075 - 3/4" Hoppy Bender

See it in action!





COLLAPSE OR FRACTURE



58200 - 2" PVC Spring Bender

58300 - 3" PVC Spring Bender 58350 - 3 1/2" PVC Spring Bender

58400 - 4" PVC Spring Bender

58250 - 2 1/2" PVC Spring Bender

It's a shoehorn for your pipe bender! No longer do you need to do the time consuming math for bending 90's in multiple size of pipes. The Better Bend comes in a variety of sizes to meet the majority of your pipe bending needs.

Part#'s

MAKE CONCENTRIC 61050 - 1-1/4" to 1/2" 61075 - 1-1/4" to 3/4" 90 DEGREE BENDS QUICK 61100 - 1-1/4" to 1"

8 EASY WITH 60150 - 1" to ½" 60175 - 1" to ¾"

Patent Pending

BEFORE

MFG NOTE:

Needs to be at least 50 degrees

Fahrenheit to work effectively







VISIT US AT: www.Rack-A-Tiers.com FMAIL: Sales@Rack-A-Tiers.com 70LL FREE: 1 (888) 939-9991

ALIGNMENT TOOL

Utilizing rare earth magnets, the alignment tool easily snaps into place and allows you to align all your 3/4" conduit without the need for a level or measuring tape.

Part# 68075







HIRE Vortex



If you need an extra pair of hands on the job, try the Wire Vortex. This wire pulling guide fits on 4" square boxes and saves you tons of time when pulling wire.

Part# 40001

- Protects wire from damage when pulling
- Can pull wire in all 4 directions
- Use for standard (shallow) or deep boxes
- Built with durable, impact-resistant plastic
- Easy to slip on and off

vallable Sizes:

Part# 79050 - 1/2" Part# 79075 - 3/4"

Part# 79100 - 1" Part# 79150 - Locknut Wrench Kit (Includes 1/2" & 3/4")



How many locknuts have you bashed with your flat blade screw driver? The Locknut Wrench allows you to tighten locknuts quickly and works great in tight spaces. The patent pending design is available in 3 sizes.

- Offset ends allow access in tight locations. Handle cut away sections are engineered to exact lock nut engagement and rotation
- Singular handle prevents wrist tension
- Clear permanent laser etched markings to ease use
- Comprised of durable steel and strong enough for any job

SEE IT IN ACTION



The Extendo Nut Driver kit is designed to adapt a standard 1/2" conduit into an extension nut driver for threaded rod. Utilizing the concept of a hollow shank nut driver, the Extendo Nut Driver gives you the flexibility to cut the conduit any length you need to drive the nut up the full length of threaded rod. With this tool on hand, you no longer need to buy multiple size hollow shank nut drivers! Save yourself time and money with this complete extension nut driver kit.

- Kit includes: 7/16", 9/16" sockets, and 1/4" adaptor
- No need to buy multiple hollow shank nut drivers
- Drill attachment designed for 3/8" chuck, will fit quick change drills
- Made from hardened steel
- Adaptable to any length nut driver needed
- Extends up to 10'

Part# NT1050



7/16" nut driver for 1/4" rod 9/16" nut driver for 3/8" rod

GDCENTER FINDER®

Part# 67500

The GDCenter Finder is a new product that revolutionizes the


installation of electrical panels and junction boxes. No need to learn a new installation process. Pull your layout just as you always have, but this time aided with the GDCenter Finder. Your center point will always be level and clearly identified. The days of "close enough" are

over. Finally a center tool that works!









The Penguin Puller Sr. and Penguin Puller Jr. are revolutionary new tools designed to aid in easily pulling large cables. The sleek, bullet shape allows for seamless pulling, no tape or crimps required. Utilizing four slots and allen-key set screws, the Penguin Puller Sr. and Penguin Puller Jr. are rated for 4000 lbs. of pull strength. These tools are the cool new kids on the block and here to stay when it comes to pulling wire!

69700 - Penguin Puller Sr. For Pipe 2 1/2" and Larger

69705 - Penguin Puller Jr. For Pipe 2" and Larger

Features:

- 4000 LBS. MAX PULL STRENGTH
- Penguin Puller Sr. 3/0 to 350 MCM Copper or Aluminum
- Penguin Puller Jr. 2/0 to 4/0 Copper or Aluminum
- No tape, no crimps, no mess
- Reusable



Cable Glydz can take any wire jacket type by any manufacturer and achieve consistent coefficient of friction factors as low as .07 on average. Soaping is NEVER needed regardless of length of installation For more information go to WWW.RACK-A-TIERS.COM/321/CABLE-GLYDZ



THE ALL AMERICAN **PULL BUDDY SHOEHORNS FOR YOUR WIRE**

Part#

42000 - Multi-Pack (6 pack / 2 of each)

42050 -1/2" Blue (10 Pack)

42075 - 3/4" Red (10 Pack)

42100 - 1" White (10 Pack)

FEATURES:

- Reduces time & labor
- Reduces the chance of damaging wires
- Turns wire pulling into a one person job



THE LB WIRE GUIDE IS A "SHOE HORN" FOR 2" LB'S.

FEATURES:



See It In Action!

- ASSISTS WHILE WORKING ON YOUR OWN
- FOR PVC LB FITTINGS AND IS ADAPTABLE TO MOST METAL LB'S
- FAST FOR ONE PERSON CONDUCTOR INSTALLATIONS
- INSTALLS IN TWO POSITIONS TO FIT BOTH "ENDS" OF THE LB

MFG NOTE

TWO HUNDRED AMP SERVICES (3/0 WIRE) CAN BE HARD ON YOUR KNUCKLES. THE LB WIRE GUIDE PUTS THE WIRE IN THE PIPE AND LEAVES THE SKIN ON YOUR FINGERS.

Part# 42200







SNAP IN PLACE AND PULL YOUR WIRE

- PROTECTS EXPENSIVE AND FRAGILE CABLES
- PROTECTS CEILING FROM TWISTING AND MARRING
- PREVENTS CABLES FROM TANGLING WITH THE CEILING, SAVING TIME AND LABOR
- SMOOTH INTERIOR CREATES AN ALMOST FRICTIONLESS CHASE
- SIDE SLIT ALLOWS FOR EASY CABLE REMOVAL AT ANY TIM
- EASY TO INSTALL AND REMOVE





The Ropematic has a durable latch that grabs rope or fish tape when you are pulling down. As you pull back up, the latch loosens and easily slides up the rope or fish tape. You can then pull down again and the Ropematic will grab the rope or fish tape, pulling it down.

PART# 42400

FLEX FLYER

The Flex Flyer features a guick change swivel head that installs on the end of a fish tape in 20 seconds by twisting the fish tape with 2 pairs of pliers. The loop technology allows the leader to move smoothly through all types of conduit including flex. The standard 1/4" - 28 threads allow for other types of leaders to be attached to the quick change base.



- Installs in under 20 seconds using two pairs of pliers, no torch needed
- Flies through those tough conduit runs
- Loop technology allows leader to glide through flex as well as all other types of conduit
- Loops allow leader to be snagged from other end of conduit run when necessary
- Standard 1/4"-28 threads allow for the use of other types of leaders on quick change base


Part#

69050 - Flex Flyer 1/2" 69075 - Flex Flyer 3/4"



Snatch Straps

Use the Snatch Strap for fast attachment on conduit pulls. No stripping or taping required!



- Color coded for easy circuit and phase identification

Snatch Strap handles #22 - #12 AWG. If additional wires are required simply add additional straps.

Part# 69010

Part# 69455


FISH-HEAL

Tired of fish tapes getting snagged or breaking? Try Fish Heads to fix and improve your broken fish tape end.

FEATURES:

- Complete spherical head reduces the chance of getting stuck
- Tapered back end
- Tested 500+ pounds
- Reusable





- Identifying Wiring Circuits CAT-5 Ethernet Cable
 - Audio/Video Cable HDMI Cable

Electrical Panels Color Coding Wire

Automotive wire

PHASE Wire Marker

52490BK - Black - 4 pack

Quickly and conveniently use the UPhase wire marker to color cords and wires for fast and easy organization

52490BL - Blue - 4 pack

52490RD - Red - 4 pack

52490WT - White - 4 pack

52490GR - Green - 4 pack

52491 - 4 pack Kit (blue, red, white, green)


52493 - 4 pack Kit (gray, orange, yellow, brown)

52492 - Replacment tip

BEFORE AFTER

PHASE IT RIGHT PRE-PRINTED COLOR WIRE MARKERS

Phase marking is more than just a numbers game. Get it right with Rack-A-Tiers' colored phase marking tags



Low Voltage #46-90 (Red, Black, Blue) - 52620

High Voltage #1-45 (Orange, Brown, Yellow) - 52635

High Voltage #46-90 (Orange, Brown, Yellow) - 52650



Durable Clear Coat

Easy To Read Lettering

Aggresive

DURABLE

Adhesive

The Phazer 3 sticker allows electricians on the job to associate the correct circuit with the corresponding number accurately. The Phazer 3 reference guide, which fits conveniently on your tape measure, will ensure every job is completed as quickly as possible, saving time and money.

Part# 52705



art# 52500

Steve's Sticky Tags all-purpose self-laminating armored cable markers.

WATERPROOF

- Durable
- Waterproof
- Designed specifically for B/X and MC Ultra-Flexible
- Includes permanent marker

ULTRA-FLEXIBLE

- 100 Tags per book





THE 4 CORE TWISTED POLYESTER FISH TAPE IS THE STRONGEST AND MOST POWERFUL PRODUCT SUITABLE FOR LONG DISTANCE ELECTRICAL WORK. PART# EP430G

PART# EP330R

2 CORE TWISTED POLYESTER FISH TAPE COATED FOR REDUCED FRICTION. PART# EP250Y

1 CORE BLACK POLYESTER FISH TAPE: 100FT (80M)

SINGLE CORE TWISTED POLYESTER FISH TAPE FOR A LIGHT, ECONOMICAL OPTION. PART# EP130B

NYLON FISH TAPE

NYLON FISH TAPE Ø4MM WITH M5 THREADED INTERCHANGEABLE TERMINALS FLEXIBLE STARTING SPINNER WITH EYELET AND EYELET ON THE BACK SIDE OF THE FISH TAPE.

AVAILABLE LENGTHS: 15M (49FT) & 30M (98FT) Part# EN050.BK Part# EN098.BK



- Reinforced eyelet with special formation which facilitates excellent tying of cables
- Available lengths: 15M (49FT) & 20M (65FT)

Part# EN065.OR



PLASTIC COATED GLOWFISH II

5/32" Diameter luminous rods

Super flexible glow-in-the-dark rods with our new plastic coating process. Great for tight jobs. The handy clear carry case keeps them constantly "charged" and ready.

GLF407 Glowfish Kit contains: 1 - 6' B/F, 4 - 6' M/F w/ tips GLF408 3' Glowfish Kit contains: 1 - 3' B/F, 7- 3' M/F rods w/ tips

REPLACEMENT RODS

GLF403 6' Bullnose/Bullnose (B/B) rod GLF406 6' Bullnose/Female (B/F) rod

GLF410 6' Male/Female (M/F) rod

GLF414 3' Bullnose/Female (B/F) rod

GLF415 3' Male/Female (M/F) rod

FishHook - Use to retrieve or snag wire & cable.

Directional Tool - Offset bend helps guide the Fiberfish around obstructions in walls. Magnet Head - Used with Fish Finder or to catch the ball chain inside wall cavities.

Pull Ring - Used to attach multiple wires for larger pulls.

Ball Chain - Attach to Fiberfish for interior wall pulls - can be retrieved

through small access hole in wall with magnet or Flex-Fish.

Wisp Head - Use over suspended ceilings — won't catch on T-bars.

Screw Tip - Screws into the end of small communication wires for faster and easier pulls.

ATTACHMENT KIT

- CONTAINS: - FishHook
- Directional Tool
- Magnet Head - Pull Ring
- Ball Chain
- 2 replacement tips

- Stored in convenient vinyl pouch



FIB520 Universal Attachment Kit for ALL (3/16" rods) & (5/32" rods)

PLASTIC COATED FIBERFISH AND GLOWFISH

Our Fiberfish and Glowfish rods with a durable plastic coating offer the same great performance with no risk of splintering or slivering of the fiberglass.

PLASTIC COATED FIBERFISH II

3/16" Diameter orange rods

The most versatile of the Fiberfish with our new plastic coating process. Perfect for a wide range of installation situations and challenges.

PCF207 Fiberfish Kit contains: 1 - 6' B/F, 4 - 6 M/F w/ tips

PCF208 3' Fiberfish Kit contains: 1 - 3' B/F, 7- 3' M/F rods w/ tips

PCF230 "FourPack" contains: 1 - 3' B/F, 3 - 3' M/F, tip, and FishHook in vinyl pouch

REPLACEMENT RODS

PCF206 6' Bullnose/Female (B/F) rod PCF210 6' Male/Female (M/F) rod

PCF214 3' Bullnose/Female (B/F) rod

PCF215 3' Male/Female (M/F) rod

(1/2" FIBERSNAKES ALSO AVAILABLE)

Add the LED tip to your Fiberfish Rods to see exactly where your Rod is going. LED Tip Part# FIB555.

for 5/32, 3/16 and 1/4 Rods

Fibersnake, Fishtapes and Rodders are designed for use in conduit. The reinforced fiberglass core is jacketed with a plastic coating for superior flexibility and durability. Non-conductive, so it's great for conduit with existing wiring. Rust-proof brass tips and

FIBT50 Fibersnake 50 Replacement Rodder only FIBT100 Flbersnake RT100 100 Replacement Rodder only RT150 150 Replacement Rodder only FIBT150 Fibersnake FIBT200 Fibersnake RT200 200 Replacement Rodder only FIBT250 Fibersnake RT250 250 Replacement Rodder only

FIBT300 Fibersnake RT300 300 Replacement Rodder only

DELUXE SET 15



4 x 3/16" Orange fiberfish Rods

1 x 5/32" Glow In The Dark Fiberfish Rod

Flexfish Leader


Fish Hook

Pull Ring

Bull Nose Tip

1 Carrying Case

DELUXE SET 18



1 Fish Hook

1 Pull Ring

1 Bull Nose Tip 1 Carrying Case

1/A" FIRERSNAKE

| | | IUIII | |
|---------|-----------------|-------|------------------------------|
| FIBR200 | 200' Fibersnake | RR200 | 200' Replacement Rodder only |
| FIBR250 | 250' Fibersnake | RR250 | 250' Replacement Rodder only |
| FIBR300 | 300' Fibersnake | RR300 | 300' Replacement Rodder only |
| FIBR350 | 350' Fibersnake | RR350 | 350' Replacement Rodder only |
| FIBR400 | 400' Fibersnake | RR400 | 400' Replacement Rodder only |
| FIBR450 | 450' Fibersnake | RR450 | 450' Replacement Rodder only |
| FIBR500 | 500' Fibersnake | RR500 | 500' Replacement Rodder only |
| FIBR550 | 550' Fibersnake | RR550 | 550' Replacement Rodder only |
| FIBR600 | 600' Fibersnake | RR600 | 600' Replacement Rodder only |
| | | | |

MFG. NOTE: 5/16" Fibersnake cages include wheels, 3/16" and 1/4" do not.

Fibersnakes and Replacement Rodders are available in 400\, 1000\,

Fibersnakes Part # FIBL400-FIBL1000 Replacement Rodder Part # RL400-RL1000

| Rodder Diameter | Recommended conduit sizes (in inches) | Maximum Length |
|-----------------|--|----------------|
| (FIBT) 3/16" | 1/2, 3/4, 1, 11/4 | 300' |
| (FIBR) 1/4" | 1, 1 1/4, 1 1/2, 2, 2 1/2 | 600' |
| (FIBL) 5/16" | 1 1/2, 2, 2 1/2 3, 3 1/2, 4 | 1000' |

MAGNEPUL

Extremely powerful, yet delicate, magnetic wire snake for fishing wire through walls. It even works through insulation! This new version has a much stronger magnet and a smoother rolling surface.

- Hand roller with powerful magnet & smooth finish to avoid damaging walls
- 6' ball chain included
- Flexible leader with magnet head
- Also makes a great stud finder

Any fiberfish can easily be threaded onto the magnet head. This will help push through dense insulation and guide through fire-block drill holes.

Part# 42800

22



REDUCE EFFORT IMPROVE PRODUCTION CUT LABOR EXPENSE



Tired of wiggling through a crawl space just to drag your wire to the other end? Fire the Laserline, attach your wire, then walk around and pull it across while standing. It's that easy!

The CO2 powered gun shoots a foam dart with a line attached to it up to 200ft. Stop climbing your ladder and moving it every ten feet to pull your wire across a t-bar ceiling. Pull your wire the entire distance in one shot with the Laserline!

- Accurately install a pull line up to 200ft
- Cuts labor costs and improves production
- Ability to span over heavy and hard to move objects found in many commercial structures
- Replacement line and darts available

MEG NOTE

- The Laserline Kit includes 1 gun, 2 spools of line (1200 ft each)
- 2 darts and 2 generic CO2 cartridges.

PART

83000 - LASERLINE KIT

83001 - REPLACEMENT LINE 2-1200FT

83003 - DART 3 PACK

VIAGNESPO

Part# 42900 Senses up to 30" through concrete & 60" wood frame wall

The Magnespot is a reference point locator that gives users complete self-assurance before drilling, cutting, or any other task you may previously had to do blindly. Place the Magnespot Transmitter on the wall, ceiling, or floor that you need to drill. On the other side hold the Receiver in the general direction of the transmitter, the red LED arrows on the Receiver will indicate to you which direction to move. When all 4 Arrows illuminate, the Transmitter and Receiver are lined up within a 1/2 inch.





NEED A NEW LADDER? CHECK OUT THE BACK PAGE FOR MORE INFORMATION

LASER PLUMB BOB

Looking for a better way to lay out complex ceiling and high bays? The Laser Plumb Bob, self leveling vertical laser from Rack-A-Tiers is the answer!

- Solid brass construction
- Factory aligned laser module calibrated to precise 0.15 accuracy
- Magnetic damping for quick stabilization
- Self leveling and aligning (vertically)
- Durable plastic carry case
- Battery included

MFG NOTE:

For all commercial, industrial, or residential installations. Great for laying out ceiling lights.

88455 -LASER PLUMB BOB

REPLACEMENT PARTS 88-ARM - LASER PLUMB BOB ARM WITH MAGNET ATTACHED 88-BASE - LASER PLUMB BOB BASE

88-BAT - LASER PLUMB BOB BATTERY CR 123







VISIT US AT: www.Rack-A-Tiers.com EMAIL: Sales@Rack-A-Tiers.com 7011 FREE: 1 (888) 939-9991

SURE MARK FULLY ADJUSTABLE MARKING SYSTEM SAVES TIME AND MONEY ON OUTLET LAYOUT! Set 'Sure Mark' to the height of plugs, switches, holes to drill or any other marks needed to be made in the same location throughout the same building!

Show up your buddies on the job site with your Rack-A-Tiers branded carpenter's pencil. They do the job and look Part# 52466 MACH-4-THERS CON SERVICE STREET





Complete your tool kit with a black felt marker from Rack-A-Tiers. hese things come in andy and ours won't un dry on you.



THE ROUGH-IN STICK

The Rough-In Stick allows you to mark out devices conveniently and efficiently by utilizing specifically designed holes to fit your felt marker. The Rod also - Extends up to 16' features a telescopic pole for those tricky fishes

- Easily mark stud walls for device installation
- No need to use your tape measure while laying out devices
- Telescopic pole aids in pulling wire above ceiling grids and areas of limited access



LUGGO

GROUND ROD DRIVING TOOL

Just one piece and incredibly strong. It delivers the kind of power and strength you need to easily install ground rods, rebar, & other metal objects.

- Rare Earth magnets with 27 lbs of pull

- Detects screws or nails in wood frame walls

- No batteries required

- Incredibly strong: made of 3" hot-rolled, heat-treated, hardened steel
- 3 1/2" bore to accept 3/4" and 5/8" ground rods
- 80% more striking surface

MAGNETIC STUD FINDER

types of magnetic stud finder on the market. Unlike other steel stud finders, the

Stud Ball can detect metal through 1/2" or 5/8" drywall or other thicker building

materials. Will also work through ceramic tiling and up to 3/4" plywood paneling.

- Yellow zinc chromate surface to deter rust

"I THINK IT'S TIME WE GOT A SLUGGO-OX!"

I SURE COULD

HAVE USED THAT

LAST WEEK



PLATE VISE

1/2" - 3/4" Pipe & Conduit

3"- 4" Pipe Conduit 4"x4" Lumber & 4" Angle Iron & Tubing

Part# 67119



- This one size fits all
- Holds many sizes of pipe, lumber, unistrut, and more
- Contact points do not allow materials to move or spin
- Labor and time saving
- Lightweight and portable







COMBO TOOL BELT Part# 43241 - Small Combo 43242 - Medium Combo 43243 - Large Combo 43244 - X-Large Combo 43344 - X-Large Combo

Molded support belt, Electrician's tool pouch, Large 9 pocket tool pouch, Hammer holster and tape holder

FEATURES:

- Reinforced with bar-tack stitching & heavy duty metal rivets
- 1250 denier DuraTek fabric with high density nylon webbing around pocket openings



MOLDED AIR-CHANNEL SUPPORT BELT

43245 - XX-Large Combo

43246 - XXX-Large Combo 43201 - Electrician's Tool Pouch

43202 - Lrg 9 Pocket Tool Pouch

- The first ever 'Molded Air-Channel Tool Belt' that offers incredible comfort. support, & ventilation for your back
- The high density nylon 'Web Core' inside the padded belt provides strength to stitching & stress points
- Metal rings are stitched to the belt's web core with high-density nylon webbing that provides the strongest way possible to attach suspenders
- All stress points are reinforced with 'bar-tack' stitching along with heavy duty rivets.
- Double metal buckles that add strength and dependability
- All of our belts and bags are made from double layered 1250 denier DuraTek fabric.
- Available in sizes from 26" to 54"

SMALL 25 POCKET TRAY TOOL CARRIER

- 16 exterior pockets
- 9 interior compartments and pockets
- 1 gty 7" x 5.5" 12 compartment plastic tray
- 10.5" W x 10.5" L x 8" H
- Tape holder
- Includes shoulder strap

LARGE 44 POCKET TRAY TOOL CARRIER

- 29 exterior pockets
- 1 large clear pocket
- 14 interior compartments and pockets
- 2 gty 7" x 5.5" twelve compartment plastic tray
- Tape holder
- Includes shoulder strap

Part# 43706



PLUGFONES

AT WORK: Ear plugs certified to the ANSI noise reduction standards up to 30 dB. Head phone volume limiting technology that keeps the volume level of the Plugfones speakers at or below 82 dB per OSHA standards. Built with Tuff Cord

AT PLAY: Wireless Bluetooth battery lasts up to 12 hours of play, USB re-chargeable. Comfortable design that won't fall out like regular ear buds.

MFG NOTE: All kits come with carrying case, cable mgmt. clip, USB charge cable and 2 sets of replaceable tips. For more information visit rack-a-tiers.com

EARPLUGS AND HEADPHONES ALL IN ONE. SO YOU CAN WORK HARD AND ROCK HARD

Protector- wired earphones, replaceable foam/silicone tips

Protector Plus - wired earphones, mic, replaceable tips

Protector Plus VL - 82db Volume Limited, wired earphones, mic, replaceable tips

Freedom - Bluetooth wireless earphones, mic, replaceable tips Freedom VL - Bluetooth 82db Volume Limited, mic, replaceable tips Black/Green

Part# PIPP-UY Blue/Yellow

Part# PIF-BE Black/Green

MOLDED AIR-CHANNEL SUSPENDERS

- Adjustable thick molded foam shoulder pads
- 2" wide adjustable nylon straps
- Leather crossover divider
- Heavy duty spring hooks that attach to the rings on the molded Air-Channel belts



FEATURES: Sturdy

set of suspenders for your tool belt rig

Our popular padded suspenders easily clip onto the

sturdy metal rings that are built into our tool belts.

The padded shoulder straps make these the ideal

- Comfortable
- Hook & Loop Straps



- Quick to put on & COMFORTABLE!
- Tool pouches fit in your pocket
- Made of ballistic nylon
- Lightweight & durable














FLASHLIGHTS



Part# 53500 Stick Bug Jr. 60 lumens

THE STICK BUG

The Pocket Light just got brighter, stronger and better. Some call it supercharged! With the new technology of COB LED technology, it has 150/160 lumens - 2 times the amount of the original pocket light. With the durable and strong pocket clip and improved magnetic base, you'll never be left out in the dark again



- COB LED
- 160 Lumens
- Operates on (3) AAA batteries
- Up to 7 hours run time
- Water resistant button



Part# 53600 Stick Bug 160 lumens



USB RECHARGEABLE

Part# 54075 Bulb: COB LED

Max Output: 150 Lumens

3 Modes: High, Low and Strobe

Runtime: High (4 Hours) Low (12 Hours)

4-hour charge time

Impact and Water Resistance

STANDARD BATTERY OPERATED

Part# 54050 Features:

Bulb: COB LED

3 AAA Batteries Included

Runtime: 5 hours

Max Output: 150 Lumens

BAT LIGHT

The Bat flashlight has a durable, scratch and corrosion resistant anodized aluminum frame.

10" Bat Flashlight

Part# 53700

- 3W Cree LED 300 Lumens
- 3 x AA Batteries Included

12" Bat Flashlight

Part# 53750

- 3W Cree LED 300 Lumens
- 3 x AAA Batteries Included

THE SILVER BULLET Part# 53800

12-24v Car Charger Flashlight CREE LED 300 Lumen Li-ion Battery Aluminum Alloy Recharge Time 2-3 hours

FIREFLY Part# 53400

The Fire Fly is a compact aluminum flashlight that features 3 light outputs with and has an output of 120 lumens.

FEATURES:

- 120 lumen output
- Light Modes: High output, low output, flash
- Mechanical zoom function
- 3 AAA batteries included

THE OWL EYE Part# 5330

Multi-function electronic switch. Softly press the switch once for high output. Press the switch and hold for dimming function (10%-100% brightness), press quickly two times at any position for strobe function. Takes 3X AAA Batteries (not included)

FEATURES:

- Waterproof
- Dustproof
- 120 Lumens

GLOW SAFE 360°

The Glow Safe 360 attaches to any hard hat and produces a ring of light around the wearer, enabling him or her to be easily seen in all directions.



FEATURES:

- Shadow-free, panoramic visibility
- Non-slip hard hat attachment
- Only 40 grams (1.4 oz) extra hard hat weight
- Powered by two button cells or rechargable LED
- Operates up to 24 hours with premium brand batteries or USB Charger

Part#'s 54000 – Standard 54020 – Rechargeable



PLUG MASTER

The Plug Master combines a full function dual-outlet circuit tester with 220V detection and multiple direction bubble-levels. Eliminate the need for multiple tools to test and straighten any wall outlets.

FEATURES:

- Acts as horizontal and vertical level
- Use for diagnostics
- Perform quick wiring checks
- Panel identifies conditions shown by LED indicators
- Removable side panels cover outlet during insertion

AC SENSOR & ULTIMATE AC SENSOR ■

Prevent electrical shock with this simple tool to locate dangerous defective grounds. This handheld device helps you determine the presence or absence of 50-1000 Volts AC in insulated wires, wall receptacles, fuses, junction boxes, and voltage carrying electrical systems. The bright, red glow indicates AC voltage.

FEATURES:

- Non-contact detection of 50-1000 VAC
- Includes 2 replaceable AAA alkaline batteries
- Senses voltage without metallic contact
- Outstanding safety instrument



Part# 99000 (Red Glow - No Sound)

Part# 99102

Part# 99150

Part# 45404

Part# 99001 (Red Glow - w/Sound)

DUALCHECK™ NON-CONTACT VOLTAGE TESTER

Save time and money with 2 popular testers in 1 unit - featuring a Non-Contact Voltage Detector on one end and GFCI Outlet Tester on the other.

FEATURES:

- 360 degree LED indication
- Loud beeping audible indication
- Exclusive 1 LED readout. No Charts. Instant results
- On/Off button

JET LEVEL


This convenient and strong pocket level comes with 4 precision vials of 0, 30, 45, and 90 degrees.

FEATURES

- CNC milled from 6061 aluminum extra large "VD" groove, straddles up to 10" diameter
- Rare Earth magnets for extra holding
- Water and shock resistant




This tool offers a better, faster, more cost effective solution for tasks commonly performed by electricians, plumbers and pipe fitters. Trade professionals will now have a multi-function tool that is designed to perform a number of tasks simultaneously & accurately, while increasing efficiency and reducing material waste.



- Built with aerospace engineered high impact polymer resin, this durable material will provide years of use for all trade professionals.
- Super grip rare earth magnets for hands free use on any magnetic surface



Part# 45200



EFERGY ELITE



Wireless Energy Monitor

Save up to 15% on your electricity bill through greater awareness!

- Great for sub panels to monitor tenant energy use



The Elite Classic is our latest and renewed version of our Elite Wireless Power Monitor. It updates every 10 seconds so you can instantly see the impact of turning a light on or off, boiling the kettle or using your tumble dryer. It has an innovative memory function that allows you to see how much you have used today, yesterday and in the last week or month. The Elite Monitor also displays your daily average so you can see when you are using more electricity than normal and see how your average usage reduces as you change the way you do things

Accessories 100A Current Sensor

Additional sensor for measuring current up to 100 amperes. Works with the elite or e2. These sensors are compact so they are suitable for use in air conditioning disconnects or any other location where space is limited. Split core design easily fits around wire sizes up to #2 AWG without breaking any con-



200A Current Sensor

Additional sensor for measuring current up to 200 amperes. Works with the elite or e2. Perfect for whole house applications where a 200 ampere service is installed. Split core design easily fits around wire sizes up to #4/0 AWG without breaking connections.



Part# EF012

Hub Online Accessory Kit

Monitor your home energy use online in real-time engage hub accessory kit. Online platform FREE of charge with no subscription or monthly fees Access your energy data anytime, from anywhere



EZ Generator Switch is the most affordable & efficient generator connecting manual transfer switch on the market. We are the only company in both the United States & Canada that builds switches that are matched to your exact generator. Our switches are safe and code compliant.



Our switches energize only essential circuits such as; heating circuits, kitchen circuits, lighting circuits, hot water systems, sump pumps and general outlets. Because you are only energizing essential circuits the need for large inefficient generators are not needed. More user friendly, fuel economical generators can be used.

Because we have designed an essential circuit transfer switch that only handles the items you need during power outages we are able to provide you with the lowest cost manual transfer switch on the market. By only powering essential items during power outages, there is no need for larger, more expensive systems which also require larger generators, expensive systems which also require large generators. We conform to CAN/CSA Std. C22.2 #14 and UL standard 1640





The Aerial Tool Bin offers a safe and efficient way of storing your tools at waist height while a variety of Man-Lifts. It is designed to be used on: Aerial Platforms, Scissors Lifts, Boom Lift Scaffolding, Swing Stage Railings, and Mast Climbers.







*Tools sold separately

MULTI-USE LADDER ORGANIZER

- ADAPTER CLIPS INCLUDED
- WORKS WITH MOST FIBERGLASS, ALUMINUM & WOOD STEP LADDERS

*Tools sold separately





65100 - STEP LADDER SHINMATE 65200 - EXTENSION LADDER SHINMATE


The Shinmate provides SUPERIOR COMFORT & BETTER BALANCE. Designed by a tradesman for tradesmen, electricians, painters, carpenters & window washers or anyone who works on ladders for hours on end will benefit from the ShinMate.



VISIT US AT: www.Rack-A-Tiers.com EMAL: Sales@Rack-A-Tiers.com 70LL FREE: 1 (888) 939-9991

PO PORTOR















Part# RV025 - 25 lbs 3 Pack

Part# RV050 - 50 lbs 2 Pack

KEEP IT CLEAN

RACKY WIPES

Available in 2 different size bags, Racky Wipes are convenient, affordable rags made from recycled t-shirt material.

RAG05C - 5 lbs. colored RAG10C - 10 lbs. colored

4'x 6' DROP SHEET Every van needs a drop sheet for those days

when you gotta make a mess!







Kit includes: 6 pairs of booties, 4 pairs of nitrile gloves, 4 pairs of vinyl gloves, and 3 N95 respirators



PART#

47099 - BOOTY PACK 47099B - BOOTIES ONLY (40 PAIRS)

47099BB - SIX PACK OF BOOTIES

TIMBERWOLF: WATERLESS HAND CLEANER -

Packed with a variety of uses this hand cleaner isn't just for getting rid of dirt and grime it also makes for a great anti-itch remedy!

- Biodegradeable
- Contains no petroleum solvents
- Repels mosquitoes
- Prevents and relieves bug bits & poison ivy symptoms

- TW008 8oz. Bottle
- TW016 16 oz. Bottle
- TW100 1 Gallon Jug W/ Pump
- TW714 Wipes Cannister

Pop Open Garbage Can

- Folds flat for easy storage
- Perfect for quick cleanups
- Includes handy pipe bending reference guide & Ohms law wheel

Part# 51010





One of our classic products that everybody

loves, the Exploding Garbage Can comes in use every single day. This collapsible trash container, featuring an internal support spring that "springs into action", is made of heavy duty, tear resistant polytuftm fabric.



FEATURES:

Size of 19" x 24" when open Size of 1 1/2" x 24" when collapsed



PART# 51000

RECYCLE THOSE OLD EXPLODING BOXES...



No more spilling screws on the job because of a flimsy box. Reusable Containers from Rack-A-Tiers are a great way to organize your van, and go green at the same time!

PART# REJAR

DRYWALL HOLE CUTTER



The Q-Bit is a revolutionary hole cutter that allows you to quickly cut out device holes. The Q-Bit is built to work with any standard oscillating tool

42700 - Single Gang Box 2 3/8" x 3 3/4"

42710 - Single Gang Line Voltage Box 2 1/8" x 3 5/16"

42720 – 2 Gang Low Voltage Box 3 3/4" x 4" 42740 – Single Gang Low Voltage Mud Ring 2 1/4" x 3 5/8"

NEW SIZES AVAILABLE!



Part# 40905 - 1/2" thread 40907 - 3/4" thread 40910 - 1" thread

Wrap a 10 foot pipe in 10 – 20 seconds!

The Pipe Spinner allows you to speed up the process of taping IMC, galvanized conduit or black iron conduit in mil tape for underground applications. Instead of taping the pipe by hand, simply attach The Pipe Spinner to your drill and have your co-worker hold the

1/4" drill attachment for quick change drills Available in 3 sizes: ½", 3/4" and 1" Saves time and money

Part#'s

92HC4 - Steel Cutters 7/8"

92HC8 - Steel Cutters 1 1/8"

92HC14 - Steel Cutters 1 3/8"

92HC20 - Steel Cutters 1 3/4"

92HC22 - Steel Cutters 2" 92HC24 - Steel Cutters 2 1/2"

92KIT4 - 4-Pc Set: 7/8", 1-1/8", 1-3/8", extra pilot bit

92KIT8 - 8-Pc Set: 7/8", 1-1/8", 1-3/8", 1-3/4", 2", 2-1/2", 2 extra pilot bits

- Ejector spring
- Tapered center drill
- Carbide tipping allows for repeated regrinding

LTI BIT: STEP DRILLS*

Hardened stepped bits for clean cuts in sheet metal, electrical boxes, arborite, etc. Handy for creating knockouts. Made from high grade cobalt.

Part# MLT1 - Size: 1/8" - 1/2" 13 Step

Part# MLT3 - Size: 1/4" - 3/4" 9 Step Part# MLT4 - Size: 3/16" - 7/8" 12 Step

Part# MLT5 - Size: 7/16" - 1 1/8" 12 Step Part# MLT7 - Size: 1/4" - 1 1/2" 11 Step

THE GUIDE-0 *

The Guide-O allows you to enlarge holes utilizing a pilot bit the same size as the existing hole. By using a pilot bit that matches up to the existing hole, the hole cutter will stay centered while drilling the new, larger hole.



FEATURES:

- Fits most standard carbide and bi-metal hole cutters
- Kit includes 1/2", 3/4" and 1" pilot bits
- Made from carbon steel

*Hole Cutter not included



Part#'s 94050 - 1/2" 94075 - 3/4"

94100 - 1"

94200 - Guide-O Kit (1/2", 3/4", 1") 94225 - 2 1/2" Shaft Replacement

94226 - 2" Shaft Replacement

94050B - 1/2" Bi-Metal 94075B - 3/4" Bi-Metal


94100B - 1" Bi-Metal 94200B - Guide-O Bi-Metal Kit (1/2". 3/4", 1")



The Javelin is here to change the way we drill holes. Never get caught in a drilling extension jam again! This all-in-one extension drill can reach up to 10 feet. It comes with a fully adjustable hole cutter and auger bit extension kit. Just cut a 3/8" - 16 threaded rod to any length you need.

FEATURES

- Holds drivers bits
- Holds nut drivers
- Holds drill bits
- Reaches up to 10 feet long



Part# 95000





Rack-A-Tiers is proud to announce the Switch Bit line, our newest line of flexible installer bits. Quickly and easily customize your own set with these flexible bits featuring interchangeable heads and different shank lengths to fit any job.

| _ | - | | |
|-----------|---------------------|-----------|----------|
| ETS31621 | SINGLE SHANK | 3/16" | 21" |
| ETS31633 | SINGLE SHANK | 3/16" | 33" |
| ETS31654 | SINGLE SHANK | 3/16" | 51" |
| ETS31669 | SINGLE SHANK | 3/16" | 69" |
| ETS1421 | SINGLE SHANK | 1/4" | 21" |
| ETS1433 | SINGLE SHANK | 1/4" | 33" |
| ETS1454 | SINGLE SHANK | 1/4" | 51" |
| ETS1469 | SINGLE SHANK | 14" | 69" |
| ETB38316 | INTERCHANGEABLE H | HEAD | 3/8" |
| ETB916316 | INTERCHANGEABLE H | HEAD | 9/16" |
| ETB3414 | INTERCHANGEABLE H | HEAD | 3/4" |
| | | | |
| ETC38S316 | SWITCHBIT COMBO I | HEAD (3/8 | 8") & SI |
| | 014/ITQLIDIT 004400 | | |

SHANK (3/16" x 33") ETC916S316 SWITCHBIT COMBO HEAD (9/16") & SHANK (3/16" x 33")

PIRANHABITS

Piranhabits have 3/16" flexible shafts so they can bend while rotating. This allows drilling inside wall cavities, through box cut-outs or through other small openings.

QUATTRO FLEX AUGER BITS

Fast and aggressive self feed auger bits, welded to a flexible shaft. Cuts clean holes. Crossbored at both ends for easy wire pulling. Use for wood only.

| Part# QTT3824 | 3/8"x24" | Part# QTT1224 | 1/2"x24" | Part# QTT91624 | 9/16"x24" | Part# QTT3424 | 3/4"x24" |
|---------------|----------|---------------|----------|----------------|-----------|-------------------|----------|
| Part# QTT3836 | 3/8"x36" | Part# QTT1236 | 1/2"x36" | Part# QTT91636 | 9/16"x36" | Part# QTT3436 | 3/4"x36" |
| Part# QTT3848 | 3/8"x48" | Part# QTT1248 | 1/2"x48" | Part# QTT91648 | 9/16"x48" | Part# QTT3448 | 3/4"x48" |
| Part# QTT3854 | 3/8"x54" | Part# QTT1254 | 1/2"x54" | Part# QTT91654 | 9/16"x54" | Part# QTT3454 | 3/4"x54" |
| Part# QTT3872 | 3/8"x72" | Part# QTT1272 | 1/2"x72" | Part# QTT91672 | 9/16"x72" | Part# QTT3472 | 3/4"x72" |
| | | | | | | More sizes availa | hle |

HIGH SPEED STEEL

Superior quality M-2 High Speed Steel drill bit welded to a flexible shaft. Cuts both metal and wood. No need to worry about hidden nails or metal studs when drilling.

| Part# FLX1424 | 1/4"x24" | Part# FLX3824 | 3/8"x24" | Part# FLX1224 | 1/2"x24" |
|---------------|----------|---------------|----------|---------------|----------|
| Part# FLX1436 | 1/4"x36" | Part# FLX3836 | 3/8"x36" | Part# FLX1236 | 1/2"x36" |
| Part# FLX1448 | 1/4"x48" | Part# FLX3848 | 3/8"x48" | Part# FLX1248 | 1/2"x48" |
| Part# FLX1454 | 1/4"x54" | Part# FLX3854 | 3/8"x54" | Part# FLX1254 | 1/2"x54" |
| Part# FLX1472 | 1/4"x72" | Part# FLX3872 | 3/8"x72" | Part# FLX1272 | 1/2"x72" |

GUIDE TOOL

Allows the Piranhabits to bend for drilling from outside the wall cavity.



OverDR VE™

FAST BORING AUGER BITS

The Over-Drive boring auger bits are specifically designed to not bog down your battery drill. Designed with a 1/4" chuck and available in 3/4" and 7/8".

Features:

- Available in 7" lengths
- 1/4" drill chuck
- Designed to put less strain on your battery drill

Part# AW34OD-3/4" x 7" # AW78OD-7/8" x 7"

DIRT AUGER SYSTEM

USE FOR AUGURING AND INSTALLING WIRE OR PIPE **UNDER SIDEWALKS AND DRIVEWAYS**

Features:

- 5' long 1/4" Shaft, 3/4" Auger Fish hole for easy retrieval of wire
- Custom heat treated drill bit designed for organic material
- Long taper for easy retrieval
- Interchangeable lengths
- Custom heat treated spring steel shank for optimum memory

NAIL CHIPPER & STANDARD CHIP AUGER

Applications:

- Cable Installation - Landscape Lighting
- Sprinkling Systems
- Landscape Feeding Stakes

Part# ETD034

AUGER FILE

DON'T THROW AWAY EXPENSIVE AUGER BITS!

Save those precious auger bits from being another dull tool lying around your shop or work truck. Save time and money by sharpening your bits from the comfort of your own home.

FEATURES:

- Top teeth for auger's main cutters
- Side teeth for sharpening tip

Part# AUFILE

7 1/2" AUGER BITS **18" AUGER BITS**

Part# AW3818 3/8" Part# AW1218 1/2" Part# AW11618 11/16" Part# AW3418 3/4" Part# AW7818 7/8" Part# AW118 1" Part# AW1418 1 1/4"

Part# AW3807 3/8" Part# AW1207 1/2" Part# AW11607 11/16" Part# AW3407 3/4" Part# AW7807 7/8"

Part# AW107 1"

NAIL CHIPPER SHIP AUGER

TRI-CUT design with 3 precision ground edges for fast, smooth cutting

> REDUCES NAILS TO CHIPS without grabbing and leaves a clean hole with minimal "blowout."

without resistance.

STANDARD SHIP AUGER



Precision ground cutting edge for fast cutting of clean holes in wood.

Burr-free lead screw for easy starts and pull-through without material build-up.

BUMPER BALLS

To order Tri-Cut Bits add a 'T' to the part #'s


AUGER SHAFT CENTERING TOOL

- No more bit walking, nail hitting, wall patching or carpet replacing
- Fits all 3/16" shaft auger bits
- Includes 1 each of 1-3/4" & 2-1/4" Balls (Drill Bits not included









The Chip Catcher adheres to metal surfaces using rare earth magents. Metal shavings are attracted to the magnets embedded in the cylinder walls. Makes for easy clean up!







Part# 84100

- INCREASES SAFETY
- MAGNET BASE ATTACHES TO METAL SURFACES & CATCHES METAL SHAVINGS
- QUICK & CONVENIENT CLEAN-UP



- Magnet in base of bag attracts filings
- Increases safety
- Easily attaches to metal surfaces
- Made from non-conductive material
- Removable magnet included in bag pocket - Fits most panels

Part# 84000

DIRTBAG Electrical Safety Drilling Tool

The Dirt Bag is specifically designed to eliminate metal shavings from spreading throughout a panel while drilling. Utilizing extra strong rare earth magnets in the frame. The Dirt Bag clings to the metal surface to catch all debris caused by drilling.



It's so simple but it works.

Racky Bits are easier to use and harder to lose. If that's not enough, our genuine Robertson® RACKY BITS have hardened tips that fit better and last longer.

COLOR CODED DRIVER BITS

GENUINE ROBERTSON BITS



DOUBLE ENDED HEX BIT





MAGNETIC HEX BITS



DOUBLE ENDED BITS



PHILLIPS BITS



WE HAVE SQUARE DRIVE SCREWS AVAILABLE IN THE USA. THE BEST SCREW ON THE STREET.

#O YELLOW ROBERTSON® SQUARE BIT PART#'S

Part# 70030Y - 3" Bulk Bit Part# 70040Y - 4" Bulk Bit Part# 70030YP1 - 3" Packaged Bit

Part# 70040YP1 - 4" Packaged Bit

#1 GREEN ROBERTSON® SQUARE BIT PART#'S

Part# 70120G - 2" Bulk Bit Part# 70120GP1 - 2" Packaged Bit Part# 70130G - 3" Bulk Bit

Part# 70140G - 4" Bulk Bit Part# 70160G - 6" Bulk Bit

Part# 70130GP1 - 3" Packaged Bit Part# 70130GP2 - 3" Packaged Bits (Qty 2)

Part# 70140GP1 - 4" Packaged Bit Part# 70140GP2 - 4" Packaged Bits (Qty 2)

Part# 70160GP1 - 6" Packaged Bit

Part# 70160GP2 - 6" Packaged Bits (Qty 2)

#2 RED ROBERTSON® SQUARE BIT PART#'S

Part# 70220R - 2" Bulk Bit

Part# 70220RP1 - 2" Packaged Bit

Part# 70230R - 3" Bulk Bit Part# 70240R - 4" Bulk Bit Part# 70260R - 6" Bulk Bit

Part# 70230RP1 - 3" Packaged Bit

Part# 70230RP2 - 3" Packaged Bits (Qty 2) Part# 70240RP1 - 4" Packaged Bit Part# 70240RP2 - 4" Packaged Bits (Qty 2)

Part# 70260RP1 - 6" Packaged Bit Part# 70260RP2 - 6" Packaged Bits (Qty 2)

#2 BLUE PHILLIPS BIT PART#'S

Part# 70241BL - 4" Bulk Bit Part# 70241BL - 6" Bulk Bit

Part# 70241BLP1 - 4" Packaged Bit

Part# 70241BLP2 - 4" Packaged Bits (Qty 2)

#2 BLUE PHILLIPS BIT PART#'S (CONT)

Part# 70261BLP1 - 6" Packaged Bit Part# 70261BLP2 - 6" Packaged Bits (Qty 2)

#3 BLACK ROBERTSON® SQUARE BIT PART#'S

Part# 70340BK - 4" Bulk Bit Part# 70360BK - 6" Bulk Bit Part# 70340BKP1 - 4" Packaged Bit Part# 70360BKP1 - 6" Packaged Bit -

#4 ORANGE ROBERTSON® SQUARE BIT PART#

Part# 70430P

1/4" RED HEX BIT PART#'S

Part# 70531R - 2.5" Bulk Hex Bit Part# 70561R - 6" Bulk Hex Bit Part# 70531RP1 - 2.5" Packaged Hex Bit Part# 70561RP1 - 6" Packaged Hex Bit

Part# 70631Y - 2.5" Bulk Hex Bit Part# 70661Y - 6" Bulk Hex Bit Part# 70631YP1 - 2.5" Packaged Hex Bit Part# 70661YP1 - 6" Packaged Hex Bit

3/8" BLUE HEX BITS PART#'S

Part# 70731BL - 2.5" Bulk Hex Bit Part# 70761BL - 6" Bulk Hex Bit Part# 70731BLP1 - 2.5" Packaged Hex Bit Part# 70761BLP1 - 6" Packaged Hex Bit

7/16" BROWN HEX BIT PART#'S

Part# 70831BR - 2.5" Bulk Hex Bit Part# 70861BR - 6" Bulk Hex Bit Part# 70831BRP1 - 2.5" Packaged Hex Bit Part# 70861BRP1 - 6" Packaged Hex Bit

1/2" BLACK HEX BIT PART#'S

Part# 70931BK - 2.5" Bulk Hex Bit Part# 70961BK - 6" Bulk Hex Bit Part# 70931BKP1 - 2.5" Packaged Hex Bit Part# 70961BKP1 - 6" Packaged Hex Bit

DOUBLE HEX BIT PART#

Part# 72564RY - 5/16" & 1/4" Hex Bit Part# 72564RYP1 - 5/16" & 1/4" Hex Bit Packaged

#1 & #2 DOUBLE ENDED SOUARE BIT PART#'S

Part# 72124GR - 4" Bulk Bit Part# 72126GR - 6" Bulk Bit Part# 72124GRP1 - 4" Packaged Bit

Part# 72124GRP2 - 4" Packaged Bits (Qty 2)

Part# 72126GRP1 - 6" Packaged Bit

Part# 72126GRP2 - 6" Packaged Bits (Qty 2)

#2 PHILLIPS & 1/4" SLOT DOUBLE ENDED BIT PART#'S

Part# 72204BY - 4" Bulk Bit Part# 72204BYP1 - 4" Packaged Bit

#1 LIGHT BLUE PHILLIPS BIT PART#'S

Part# 70141LB - 4" Bulk Bit Part# 70141LBP1 - 4" Packaged Bit Part# 70141LBP2 - 4" Packaged Bits (Qty 2)

Part# 7011PI - Impact Driver Bit - Phillips #1 x 1"

IMPACT DRIVER BITS PART#'S

Part# 7012PI - Impact Driver Bit - Phillips #1 x 2" Part# 7011RI - Impact Driver Bit - Square Green #1x1" Part# 7012RI - Impact Driver Bit - Square Green #1 x 2" Part# 7021PI - Impact Driver Bit - Phillips #2 x 1" Part# 7022PI - Impact Driver Bit - Phillips #2 x 2" Part# 7021RI - Impact Driver Bit - Square Red #2 x 1" Part# 7022RI - Impact Driver Bit - Square Red #2 x 2"

Part# 7031RI - Impact Driver Bit - Square Black #3 x 1"

Part# 7032RI - Impact Driver Bit - Square Black #3 x 2"

RACKY BITS COUNTERTOP DISPLAY



ATTENTION WHOLESALERS!


Add a Racky Bits Acrylic Display Kit to your counter and watch the sales soar. Color-coded driver bits enable the contractor to quickly identify tip-styles and find their bits faster. Once a contractor experiences the quality and efficiency of Racky Bits, they will never want to buy another generic unpainted bit again.

Part# 70SKE12 - Empty 12-slot plexi-glass display Part# 70SK1 - 35 bits + plexi-glass display Part# 70SK2 - 51 bits + plexi-glass display

lockHARD bit

.This allows it to lock into place and makes sure you NEVER strip another screw

72133P - 3" BULK BIT 72134P - 4" BULK BIT











SIXPAC plus
- 7 - 3" LENGTH, 1/4" HEX POWERBITS
- 11.5" TOTAL LENGTH

PART# P88001

888 888 888



DASH 7

- 7 - 2" LENGTH, 1/4" HEX POWERBITS - COMES IN 4 BRIGHT NEW COLORS PART# P05001





- SOLID, COMFORTABLE, HIGH TORQUE HANDLE

- 6 HIGH QUALITY 1.3" LENGTH INSERT BITS - IDEAL FOR WORK IN CLOSE QUARTERS









BLACK ROBBY #12-13-14 SQUARE DRIVE

GREEN ROBBY #5-6-7 SQUARE DRIVE

PART# SD110G


RED ROBBY

#8-9-10 SQUARE DRIVE



MAGNETIZES OR DEMAGNETIZES DRIVER BITS, TOOLS AND SMALL STEEL PARTS INSTANTLY!

MAGNETIC BIT HOLDER





- WORKS ON JAGGED, UNEVEN AND ROUGH BREAKS
- SELF CENTERING TIP, NO WALKING - COMPATIBLE WITH QUICK CONNECT CHUCK SYSTEMS
- EASY TO USE WITH 3/8" VARIABLE SPEED REVERSIBLE DRILL
- EXTRACTS SCREWS UP TO 4 INCHES



MULTIBIT RATCHET SCREWDRIVER / 15 TIPS (DOUBLE ENDED BITS)

- Slotted: 3/16", 1/4"
- Smooth and silent ratcheting
- Phillips: 1, 2, 3, 4
- Torx: 10, 15, 20, 25
- Square: 1, 2, 3, 4
 - Single-handed ratchet adjustments from forward, locked, & backward
 - Ergonomic, cushion comfort handle
 - Magnetic components for drop-safe bit changing
 - Stainless steel bit adapter

PART# SDR14



Tired of trying to remove knockouts? Let the Panel Buddy take care of them for you. This simple but genius tool removes knockouts in half the time, with half the effort.

FEATURES

- Kit removes knockouts on Electrical, Security, Alarm, and **Datacom Panels**
- Works with lipped and non-lipped panels



Every moment during a project that you spend looking for the right tool is wasted time and results in frustration and bad decisions. The ingenious HOLDSaBIT slips on or off a drill in seconds. Simply pull one loop over the front of the drill and pull the second loop to the back of the drill. The HOLDSaBIT will hold any 1/4" hex shank item as well as pencils, nut drivers and hex shank drill bits. Tips and bits are easily inserted and removed.



Part# 7WBK100

FEATURES:

- Sold in a kit with bits or sold separately.
- Hold any 1/4" hex shank items as well as pencils, drill bits, etc.
- 4 channels to fit a variety of length bits



Part# 70000 (Bits Not Included) Part# 700.kit (includes 1-70140G, 1-70240R, 1-70241BL, 1-70531R, 1-70631Y & 1-72133P)

REVBIT: REVERSE PILOT BIT

The RevBit takes a common item, the pilot bit, and perfects it. By being reverse twist the RevBit eliminates any bending, breaking and mess caused by hole saw teeth catching once your pilot bit goes through the material.

- Reverse threaded pilot bit for a soft landing once the pilot bit breaches the work surface
- 4" in length
- Made from high speed steel
- Works with any standard hole saw
- Will not tear sheetrock, or finished wall surface
- Preserves the hole saw teeth, for the entire life of the tool
- Made in the USA



Part# 91700



NUT BLASTER

Universal Wire Connector

- Fast, easy installation
- Prevents sore fingers and cramping hands
- Available in two sizes

Part#

XL - 72101 - Fits all brands yellow, tan & red twist on wire connectors XXL - 72102 - Fits all brands large grey & blue twist on wire connectors



NUT BLASTER In-Store Display

Contact us to order this counter display. Other counter displays also available.

THE TOP HAT


PART# TC1400 *PACKAGED IN 50 & 5 PACKS

As a simple box cover, the Top Hat is used instead of a blank cover with several important advantages. It allows installers to leave wires that enter the junction boxes extending straight. With the depth of the Top Hat there is no need to coil wires and stuff them into the smaller parts of the junction box. This will save time during installation and more importantly during troubleshooting. Additionally, this high volume cover makes it easier to access the contents of any junction box.

FEATURES

- ULC Approved
- Adds 35.8 cubic inches to the existing junction box
- Plenum Rated









6.5 INCH PLATE

- Installs in seconds with rare earth magnets snaps in place to metal
- White decorative plate covers and 5-1/2" square hole or electrical box
- Can also be used to cover a round hole with up to a 5-1/2" diameter
- Visually appealing white decorative plate no need to paint metal covers



Part# D612

- AVAILABLE IN 500 AND 1.000 FEET
- NO NEED TO GO ANYWHERE ELSE BUY IT FROM US!

SC500 - Aircraft Seismic Cable 500' SC1000 - Aircraft Seismic Cable 1000' SCC116 - Aircraft Seismic Cable Clamps

BULT STAR BULT TEMPLATE POLE POSITIONING TOOL The Bolt Template helps you easily layout bolts to be used in concrete for future installation of poles or beams. The template in concrete for future installation of poles or beams. The template is constituted and have a possess guide for containing bolts.

An innovative, multi-function reusable bolt template engineered to hold four anchor bolts, rebar cage and conduits securely in place during the pour of a concrete pole base. The result of years of design refinement and testing, BOLT STAR radically improves the productivity of crews in the construction of light pole bases and round column forms. Available for 180 and 240 tube sizes, the tool virtually eliminates the drawbacks



SAVES LABOR - REUSABLE - REDUCES RISK

Part# 67224 - Large Size 24" - Orange Part# 67230 - Extra Large Size - Yellow

Part# 67234 - Extension Set of 4 Pcs. - Black

is multi-functional and has an easy guide for centering bolts.



DRYCONN® WATERPROOF CONNECTORS

FILLED CONNECTORS FOR OUTDOOR USE



Selling Unit Wire Range KI62110 Card of 6 22 - 12KI62125 Bag of 25 22 — 12 KI62210 Card of 5 22 - 8KI62225 Bag of 20 22 - 8KI62310 Card of 3 14 —6 KI62335 Bag of 50

"One-Step"® Installations Corrosion Proof Reduces Risk of Fire CSA certified as a Pressure Type Connector



FILLED CONNECTORS FOR DIRECT BURY USE

| Part # | Selling Unit | Wire Range |
|---------|--------------|------------|
| KI10600 | Card of 2 | 22 — 8 |
| KI10666 | Bag of 10 | 22 — 8 |
| KI10999 | Bag of 8 | 14 — 6 |
| KI10444 | Bag of 10 | 18 — 12 |
| KI10555 | Bag of 10 | 14 —10 |

"One-Step" Installations CSA certified as a Pressure Type Connector CSA certified as Direct Bury Corrosion proof

COUNTERTOP BOXES FLOOR BOXES




Rack-A-Tiers carries and extensive line of floor and countertop boxes. They all feature a sleek and compact design offering a great option when needing to install an outlet into a countertop or floor.



SQUARE COUNTERTOP POP-UP BOXES

SQUARE COUNTERTOP POP-UP PLATE ASSEMBLY WITH 20 AMP GFI RECEPTACLE





SQUARE COUNTERTOP POP-UP PLATE ASSEMBLY WITH 15 AMP W/2 USB

STAINLESS - PART# VPU.SS.2USB BLACK - PART# VPU.BK.2USB BRASS - PART# VPU.BR.2USB **OFF WHITE** - PART# VPU.WT.2USB

DESKTOP POP-UP BOX

Pop-up desktop box includes: 1 - Decora 15 Amp Duplex Receptacle W/ 2USB and 6 Port Empty Communication Plate.mpty Communication Plate. 9 foot power cable. Part # VPU.DTB.BK



Part# VKJ.BK - Black Voice Modular Coupler Part# VKJIT.BK - Black Cat 5E Modular Coupler Part# VKC.BK - Black Blank Modular Fill Part# VKJHDMI.BK - Black HDMI Modular Coupler Part# VKJUSB.BK - Black USB Pass Through

- 120 V male cord attached
- Mounts flush in boardroom tables, desks, etc.
- 15 Amp Duplex Receptacle W/ 2USB
- 6 Port Empty Communication Plate



SQUARE FLOOR POP-UP BOXES WITH SLIDE BUTTON

SQUARE POP-UP FLOOR PLATE ASSEMBLY WITH 20 AMP GFI RECEPTACLE

- PART# VFPU.SS.GFI STAINLESS BRASS - PART# VFPU.BR.GFI

SQUARE POP-UP FLOOR PLATE ASSEMBLY WITH 15 AMP W/2 USB

- PART# VFPU.SS.2USB STAINLESS BRASS - PART# VFPU.BR.2USB

SQUARE POP-UP FLOOR PLATE ASSEMBLY WITH 15 AMP

STAINLESS - PART# VFPU.SS - PART# VFPU.BR BRASS

SQUARE FLOOR POP-UP PLATE ASSEMBLY INCLUDE VPU.WB WOOD ENCLOSURE BOX. CONCRETE BOX SOLD SEPARATELY - PART# VPU.CB

ASSEMBLED FLOOR BOXES

PLASTIC QUICK INSTALL FLOOR BOXES



HINGED SINGLE GANG

ALUMINUM - PART# VRHC.AL BRASS - PART# VRHC.BR



HINGED ROUND

ALUMINUM - PART# VRHB.AL BRASS - PART# VRHB.BR



MEDALLION SINGLE GANG

ALUMINUM - PART# VRMC.AL - PART# VRMC.BR BRASS



MEDALLION ROUND

ALUMINUM - PART# VRMB.AL BRASS - PART# VRMB.BR

> *NOT FOR USE IN CONCRETE

ROUND FLOOR BOXES

ROUND FLOOR POP-UP PLATE ASSEMBLY WITH 15 AMP DECORA

STAINLESS - PART# VPU.FD.SS - PART# VPU.FD.BR

ROUND FLOOR POP-UP PLATE ASSEMBLY WITH 15 AMP GFI

STAINLESS - PART# VPU.FB.SS BRASS - PART# VPU.FB.BR

ROUND FLOOR POP-UP PLATE ASSEMBLY WITH 6 DATA PORTS

STAINLESS - PART# VPU.FC.SS BRASS - PART# VPU.FC.BR

ROUND FLOOR POP-UP PLATE ASSEMBLIES DO NOT INCLUDE ENCLOSURE BOX, WOOD BOX, PART# VPU,WB AND CONCRETE BOX, PART# VPU.CB, SOLD SEPARATELY.





5' LONG X 10.5" WIDE X 2.75" HIGH

Accommodates a cable/bundle up to 2.25". Withstands heavy vehicle traffic.

5' LONG X 4.5" WIDE X 1.25" HIGH

commodates cable up to .75" in diameter. Withstands heavy vehicle traffic. Part# TCG5

The Temporary Cable Guard withstands heavy vehicle traffic without damaging cable. Easily anchored with concrete screws if needed. The Temporary Cable Guard helps you restore services quickly by allowing you to run temporary cables over most any surface. It reduces truck rolls and eliminates downtime due to cable cuts, storm damage, traffic or roadway activities.



Our Ultra Guards Collection can be used from light duty to heavy duty projects.



The LiteGuard collection offers 1" to 1.38" size channels. While smaller in size and weight, these products are still designed for significant load bearing strength. Commonly used in vehicle or pedestrian settings, the LiteGuard collection provides invaluable protection.

Elasco Dropover: Single channel that is 4 inches wide by 1 inch tall. Offered in a black color and solves your basic needs in the office or on site.



Elasco's UltraGuard collection cable guards come in standard 3-foot lengths. If your projects needs are to go in multiple directions, our 45 degree right angled turns assist in configuring

NOT ALL OPTIONS PICTURED, FOR FULL RANGE OF ITEMS AND PART NUMBERS VISIT RACK-A-TIERS.COM

FILLERS & CONNECTORS *

KO KILLERS: PLASTIC KNOCKOUT FILLERS Fits thin (1/32") and thick (1/8") wall thickness

Features:

- No tools required
- Snap in and out with ease
- Non-conductive, safer



Part# KOK50 - 1/2" Filler (50/bag) Part# KOK75 - 3/4" Filler (50/bag)

Part# KOK100 - 1" Filler (25/bag) Part# KOK125 - 1 1/4" Filler (25/bag) Part# KOK150 - 1 1/2" Filler (25/bag)

Part# KOK200 - 2" Filler (25/bag) Part# KOK999 - Assorted Fillers Kit (25)

RAT 500

Rapid Fire NMSC connector (100 Pack)

Suitable for all 1/2" knockouts Fast and Easy. No tools required Features:

- 100/bag
- Single cables
- Two cables
- Install from outside

RAT 750

Rapid Fire NMSC connector (50 pack)

Suitable for all 3/4" knockouts Fast and Easy. No tools required Features:

- 50/bag
- Single cables
- RAT500 1/2" Connector

RAT750 3/4" Connector - Install from outside



TT500

NMSC Two Way 1/2" Connector (100 Pack)

Installs from inside and outside the box Features:

- 100/bag
- Single cables
- Two cables

Part# TT500



STUD BUDDIES

(100 Pack) Why Square Bushing? 70% More cross sectional area! More cables, easier pulls,

- One piece
- One hand installation
- Fits all standard steel studs & punches
- Fire rated V.O.
- Faster, easier to use



3/8"Metal Flange



LJ50R - 1/2" (30 pack) LJ58R - 5/8" (25 Pack)



LEVEL JACK

HOW DOES IT WORK?

Alignment tabs reach across wood/metal studs to level low voltage outlets with A.C. boxes.

NO TAPE MEASURE • NO LEVEL REQUIRED

Available in 1/2", 5/8" and 1" rise

If you're fussy about your rough-in layout, the Level Jack makes life easy. If you're not, no one will notice because you can't screw up with the Level Jack.

Just clip it on to the AC box and screw it down. No level, no tape measure, no special boxes, no special fittings required. Level Jacks fit most AC boxes.



WS/T US AT: www.Rack-A-Tiers.com EMAIL: Sales@ Rack-A-Tiers.com 7011 FREE: 1 (888) 939-9991

MAGNETIC

MAG DADDY MAGNETIC FASTENERS UTILIZE ULTRA-STRONG MAGNETS TO STRAP WIRE AND CABLE. MAG DADDY MAGNETS WILL STAY ATTACHED THROUGH OIL, GREASE, PAINT OR DIRT. A VARIETY OF CONFIGURATIONS ARE AVAILABLE TO SUIT YOUR NEEDS.

CABLE HOLDERS



Magnetic Cable Holder (10 Pack)

Part# RM050BK - 1/2" Black Part# RM050WT - 1/2" White Part# RM075BK - 3/4" Black Part# RM075WT - 3/4" White Part# RM100BK - 1" Black Part# RM100WT - 1" White

CABLE TIE MOUNTS



Magnetic Cable Tie Mount (10 Pack) Holds Standard Zip Ties

Part# RM110BK - 10 lb Black Part# RM110WT - 10 lb White Part# RM115BK - 15 lb Black Part# RM115WT - 15 lb White

MAGNET MOUNT



Magnet Mounts (10 Pack)

Part# RM164SL - 19 mm/16 lb Silver Part# RM265SL - 23 mm/26 lb Silver Part# RM266SL - 26 mm 26 lb Silver



Magnetic Clamp (10 Pack)

Magnetic Strength: 15 lbs. Part# RM051BK - 1/2" Black

1/4-20



3/4" Wide Cable Mount (10 Pack) Part# RM215BK - 15 lbs Black



Mini Magnet Cable Tie Mount (10 Pack)

Color: Black Magnetic Strength: 5 lbs Part# RM020BK



Cable Hanger

Cable Hanging Tool Part# RM300HT



Magnetic Bridle Ring

Part# RM125BR - 1.25" 1/4-20 Part# RM200BR - 2" 1/4-20

TOP J-HOOKS



360° Rotation

Part# RMJ075T - 3/4" Part# RMJ131T - 1 5/16" Part# RMJ200T - 2"



SIDE J-HOOKS

360° Rotation Part# RMJ075S - 3/4" Part# RMJ131S - 1 5/16" Part# RMJ200S - 2"

Racky Strap utility straps hold almost anything wherever you need them. These are handy on any site with several wires or

- Holds anything up to 33lb per sq. inch
- Quality hook and loop may be used with soft side up or down
- Available in 1/2" x 8" and 1"x12" strips
- Great for data cable



- Use for cable management in telecommunication
- Used as guides and supports to organize existing runs or assisting with new installs
- Install to conform to NEC and local codes
- A smart Handi-Hoop pathway creates the condition whereby "one man pulls" can be accomplished

Part# HH1010

ROBERTSON SCREWS

ANCHORS, WASHERS, NUTS & BOLTS

The Original Robertson screw is the only one that guarantees a perfect "Cling Fit"

Please Call For Part Numbers

WOOD SCREWS



SHEET METAL SCREWS



ROUND HEAD MACHINE SCREWS



CAMTAP® SELF-DRILLING SCREWS



TRUSS HEAD SCREWS



Ask Your Wholesaler to bring in Robertson Screws from Rack-A-Tiers!

BREAKER LOK

Secure any circuit breaker in the ON Position with ease!

- Universal lock fits most breakers & standard toggle switches.
- Set screw and rigid leg prevents lock from slipping off breaker.
- Reusable & corrosion resistant.
 Part# 75000 5 Pack


ELECTRICAL CODE SIMPLIFIED PS KNIGHT ** Part# 73129

FEATURES


- Now over 1200 pages
- Over 1000 code rules & revisions, clearly explained & indexed
- Code tables & practice exam
- 400 questions & answers added

MFG NOTE

The industry's most comprehensive publication on Canadian electrical code that clarifies the New Code Rules.







HOT SPOTS

ELECTRICAL FIRE SAFETY & CONDITION MONITORING LABELS

They work on electrical door panels of all types MCC/ Fuse/CDP/ECT. They work of fuses/breakers/switch gear or any other electrical components.


INACTIVE

Hot Spots 23 C

s c

Hot Spots find and categorize your electrical faults by changing colors. When the fault is fixed they change back to the original color. CSA approved. Patent pending.

ACTIVE



For Part Numbers visit Rack-a-Tiers.com



NEED A NEW FILLER KIT? CHECK OUT OUR BACK PAGE FOR OUR NEW SEARCH SERVICE

Industrial CORD CONNECTOR

Part # 97100

A construction quality Cord Connection System for protecting your corded power tools and extension cords. The Industrial Cord Connector extends cable life and adds convenience to all your corded tools and extension cords. Simply add a Cord Stop to the ends of both the corded tool and the extension cord, cover the Stops with the Barrel Cover and cinch the straps tight. The snug Barrel Cover protects your electrical connection from the outdoor elements and job site knocks and bangs. The Industrial Cord Connector holds your cords tight and eliminates time wasting disconnects. The Industrial Cord Connector puts an end to cord wear from knotting and tying.



Industrial Cord Connector Kit, includes: 1x Barrel Cover, 2x Cinch Straps and Cord Stops for #10, #12, #14, #16 Cables. Additional Cord Stops are available to protect all your corded tools and cords. For more information on the Industrial Cord Connector and accessories visit Rack-A-Tiers.com









GOODBYE DIALING - HELLO TEXTING


If you run a business and want to enable texting on your existing business line, use what Rack-A-Tiers uses - Text Groove.

Text 888-939-9991 for information





Need a specific product? We'll help you find it!



Rack-a-tiers has over 25 years experience in the electrical manufacturing industry and if we don't have what you are looking for we will find it for you!

TEXT: 888-939-9991 OR EMAIL: SALES@RACK-A-TIERS.COM



INVENTOR'S CORNER



Find yourself flipping through the Rack-A-Tiers catalog wishing you had thought of that tool, or frustrated that you thought of that idea first? Well, here's your chance to put your ideas into action. Rack-A-Tiers launched Inventor's Corner for creative folks like you to pitch ideas and read testimonials from past inventors. Even if Rack-A-Tiers is unable to add your idea to our product line, we have the experience and knowledge to provide advice for your next move as an inventor. Check out the Inventor's Corner at rack-a-tiers.com/inventors and who knows maybe in next year's catalog your product could have a full-page spread.

