

PROJECT NAME:	CATALOG NUMBER:
NOTES:	FIXTURE SCHEDULE:

Page: 1 of 3

### **LED T5 - LINEAR REPLACEMENT TUBE**

BYPASS COATED GLASS SERIES **UL TYPE-B** 















#### PRODUCT DESCRIPTION:

MaxLite LED T5 Linear Replacement lamps are the ideal energy saving choices when upgrading traditional linear T5 fluorescent lamps in fixtures containing standard G5 (mini bi-pin) sockets. The LED T5 lamps are designed to provide appropriate light levels while utilizing a dedicated internal driver and require non-shunted G5 mini bi-pin lamp holders. Tested to NSF Standards, these lamps carry the **ETL Sanitation Mark** and are suitable for use in an environment where food intended for human consumption is produced.

#### **FEATURES:**

- · Wattage:
  - -12W 2FT, 1,400-1,500 lumens, replaces 2FT 24W T5HO
  - -16W 3FT, 1,800-1,900 lumens, replaces 3FT 39W T5HO -25W 4FT, 3,200-3,400 lumens, replaces 4FT 54W T5HO
  - -13W 4FT, 1,600-1,700 lumens, replaces 4FT 28W T5HE
- Input Voltage: 120-277V
- Beam Angle: 240°
- Color Rendering Index (CRI): ≥80
- THD: <20%
- Power Factor: ≥0.90
- Suitable for use in dry and damp locations
- Suitable for totally enclosed recessed fixture
- · All glass construction with PET coating
- PET film is 0.1mm thick
- · Mercury, UV and IR free
- Five year limited warranty
- Rated Lifetime @ L70: 50,000 Hours
- No DLC category for 2FT & 3FT T5 HE & HO tubes

MODEL SELECTION (Full list of order of	codes on pg. 2)	Typical order example: L12T5SE240-CG			
L12	T5	SE	2		
FAMILY	LAMP TYPE	OPERATION	LENGTH	сст	
L12= 12W, LED Linear	<b>T5=</b> T5 tube	SE= Single-Ended Power	<b>2=</b> 2FT	<b>35-CG=</b> 3500K, Coated Glass <b>40-CG=</b> 4000K, Coated Glass <b>50-CG=</b> 5000K, Coated Glass	
L16	T5	SE	3		
FAMILY	LAMP TYPE	OPERATION	LENGTH	сст	
L16= 16W, LED Linear	<b>T5=</b> T5 tube	SE= Single-Ended Power	<b>3=</b> 3FT	<b>35-CG=</b> 3500K, Coated Glass <b>40-CG=</b> 4000K, Coated Glass <b>50-CG=</b> 5000K, Coated Glass	
	T5	SE	4		
FAMILY	LAMP TYPE	OPERATION	LENGTH	сст	
L13= 13W, LED Linear L25= 25W, LED Linear	<b>T5=</b> T5 tube	SE= Single-Ended Power	<b>4=</b> 4FT	<b>35-CG=</b> 3500K, Coated Glass <b>40-CG=</b> 4000K, Coated Glass <b>50-CG=</b> 5000K, Coated Glass	

### NOTES:

- 1. This device is not intended for use with emergency exits or for emergency lighting
- 2. Do not use with dimmers





# **LED T5 - LINEAR REPLACEMENT TUBE**

BYPASS COATED GLASS SERIES **UL TYPE-B** 

Page: 2 of 3

SPECIFICATIONS:		L12T5SE2xx-CG	L16T5SE3xx-CG	L25T5SE4xx-CG	L13T5SE4xx-CG	
ITEM	SPECIFICATION	2FT HO- DETAILS	3FT HO- DETAILS	4FT HO- DETAILS	4FT HE- DETAILS	
	Bare Lamp Wattage	12W	16W	25W	13W	
	Lumens Delivered	1,400-1,500	1,800-1,900	3,200-3,400	1,600-1,700	
GENERAL	CRI	≥80				
PERFORMANCE	Beam Angle	240°				
	Color Temperature (CCT)	3500K, 4000K, 5000K				
	Lumen Maintenance (L70)	50,000 hours				
ELECTRICAL	Power Factor	≥ 0.90				
ELECTRICAL	Input Voltage	120-277V				
PHYSICAL	Operating Temperature	-4°F to 113°F				
PHYSICAL	Dimensions	MOL: 22.20"	x Width: 0.80"	MOL: 45.80" x Width: 0.80"		
	Qualification	cULus classified, ETL Sanitation Listed DLC Standard, cULus cl		classified, ETL Sanitation		
OHALIFICATION	Material Usage	RoHS compliant, no mercury				
QUALIFICATION	Environment	Dry, Damp, ETL Sanitation Listed				
	Warranty	5 Years				

## **ORDERING:**

ORDER CODE	MODEL	WATTAGE	LUMENS	EFFICACY (Im/W)	CRI	сст	BASE	
2FT T5 - HO	2FT T5 - HO							
1409907	L12T5SE235-CG		1,400	116		3500K		
1409908	L12T5SE240-CG	12	1,450	120	83	4000K	<b>G</b> 5	
1409909	L12T5SE250-CG		1,500	125		5000K		
3FT T5 - HO								
1409910	L16T5SE335-CG		1,600	112		3500K		
1409911	L16T5SE340-CG	16	1,650	115	83	4000K	<b>G</b> 5	
1409912	L16T5SE350-CG		1,900	118		5000K		
4FT T5 - HO	4FT T5 - HO							
1409601	L25T5SE435-CG		3,200	128		3500K		
1409602	L25T5SE440-CG	25	3,300	132	83	4000K	<b>G</b> 5	
1409603	L25T5SE450-CG		3,400	136		5000K		
4FT T5 - HE								
1409889	L13T5SE435-CG		1,600	123		3500K		
1409890	L13T5SE440-CG	13	1,650	127	83	4000K	G5	
1409891	L13T5SE450-CG		1,700	131		5000K		

Specifications are subject to change without notice.



# **LED T5 - LINEAR REPLACEMENT TUBE**

BYPASS COATED GLASS SERIES UL TYPE-B

Page: 3 of 3

	ACCESSORIES					
ORDER CODE	MODEL NUMBER	DESCRIPTION	ACCESSORIES IMAGE			
14098784	G5KIT1	1-LAMP WIRING HARNESS FOR LED T5 - BYPASS UL TYPE-B				
14098785	G5KIT2	2-LAMP WIRING HARNESS FOR LED T5 - BYPASS UL TYPE-B				
14098786	G5KIT4	4-LAMP WIRING HARNESS FOR LED T5 - BYPASS UL TYPE-B				
14098787	G5KIT6	6-LAMP WIRING HARNESS FOR LED T5 - BYPASS UL TYPE-B				