

# GLAYSE

Inspired by modern architecture, Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function.

ALSO AVAILABLE IN  
Bath & Vanity



FINISHES  
● Brushed Nickel - 09

WALL SCONCE  
**P300105-009** Brushed Nickel  
7" W., 8-3/8" ht.  
Extends 5-1/2". H/CTR 5-3/8".  
One medium base lamp,  
60w max.

SEMI-FLUSH CONVERTIBLE  
**P350090-009** Brushed Nickel  
Hanging and ceiling mount  
hardware included.  
16-3/4" Sq., 14-3/4" ht.  
Overall ht. w/chain 80", wire 10'.  
Four medium base lamps,  
each 60w max.

FIVE-LIGHT LINEAR  
CHANDELIER  
**P400116-009** Brushed Nickel  
36-3/4" W., 10" L., 15-3/4" ht.  
Overall ht. w/stem 82", wire 15'.  
Five medium base lamps,  
each 60w max.

MINI-PENDANT  
**P500073-009** Brushed Nickel  
6-1/2" Sq., 11-7/8" ht.  
Overall ht. w/stem 77", wire 10'.  
One medium base lamp,  
60w max.

FIVE-LIGHT PENDANT  
**P500074-009** Brushed Nickel  
22-3/4" Sq., 13-3/4" ht.  
Overall ht. w/chain 80, wire 15'.  
Five medium base lamps,  
each 60w max.

FOUR-LIGHT FOYER PENDANT  
**P500095-009** Brushed Nickel  
14-3/4" W., 28-3/8" ht.  
Overall ht. w/stem 94-1/2", wire 15'.  
Four medium base lamps,  
each 60w max.

Fixtures shown with P7825-01  
vintage lamps.



P500095-009



P500095-020



P350090-020



P500073-020



P500074-020



P500095-020



P400116-020



P300105-020

# GLAYSE

*FINISHES*

- Antique Bronze - 20

*WALL SCONCE*

**P300105-009** Brushed Nickel  
7" W., 8-3/8" ht.  
Extends 5-1/2". H/CTR 5-3/8".  
One medium base lamp,  
60w max.

*SEMI-FLUSH CONVERTIBLE*

**P350090-020** Antique Bronze  
Hanging and ceiling mount  
hardware included.  
16-3/4" Sq., 14-3/4" ht.  
Overall ht. w/chain 80", wire 10'.  
Four medium base lamps,  
each 60w max.

*FIVE-LIGHT LINEAR  
CHANDELIER*

**P400116-020** Antique Bronze  
36-3/4" W., 10" L., 15-3/4" ht.  
Overall ht. w/stem 82", wire 15'.  
Five medium base lamps,  
each 60w max.

*MINI-PENDANT*

**P500073-020** Antique Bronze  
6-1/2" Sq., 11-7/8" ht.  
Overall ht. w/stem 77", wire 10'.  
One medium base lamp,  
60w max.

*FIVE-LIGHT PENDANT*

**P500074-020** Antique Bronze  
22-3/4" Sq., 13-3/4" ht.  
Overall ht. w/chain 80, wire 15'.  
Five medium base lamps,  
each 60w max.

*FOUR-LIGHT FOYER PENDANT*

**P500095-020** Antique Bronze  
14-3/4" W., 28-3/8" ht.  
Overall ht. w/stem 94-1/2", wire 15'.  
Four medium base lamps,  
each 60w max.

*Fixtures shown with P7825-01  
vintage lamps.*

# GLAYSE

Inspired by modern architecture, Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function.

ALSO AVAILABLE IN  
Fixture Collections



P300105-009



P300105-020

## FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

## ONE-LIGHT BATH

**P300105-009** Brushed Nickel  
**P300105-020** Antique Bronze  
7" W., 8-3/8" ht.  
Extends 5-1/2". H/CTR 5-3/8".  
One medium base lamp,  
60w max.

## TWO-LIGHT BATH

**P300106-009** Brushed Nickel  
**P300106-020** Antique Bronze  
14-7/8" W., 8-3/8" ht.  
Extends 5-1/2". H/CTR 5-3/8".  
Two medium base lamps,  
each 60w max.

## THREE-LIGHT BATH

**P300107-009** Brushed Nickel  
**P300107-020** Antique Bronze  
22-3/4" W., 8-3/8" ht.  
Extends 5-1/2". H/CTR 5-3/8".  
Three medium base lamps,  
each 60w max.

Fixtures shown with P7825-01  
vintage lamps

Fixture mounts up or down.



P300106-009



P300106-020



P300107-009



P300107-020

P300106-020