

LINE VOLTAGE RECESSED 4" HOUSINGS

Recessed Lighting

All 4" Line Voltage Housings are:

- UL damp location listed
- UL feed through listed
- Can be retrofitted to use 120V MR16 lamps with PSA28 adapter.



4" Miniature Housing

EL99

EL99A (airtight) NEW!

- Height: 5 1/2"
- Opening: 4 1/4"
- Lamp: 50W max



4" Miniature Airtight IC Housing

EL99ICA

- Height: 5 1/2"
- Opening: 4 1/4"
- Lamp: 50W max



4" Miniature Remodel Housing

EL99R

EL99RA (airtight) NEW!

- Height: 5 1/2"
- Opening: 4 1/4"
- Lamp: 50W max

4" HOUSINGS for 120V MR16

The following housings *only* work with 4" Low Voltage trims on **pages 64-69**.



4" Miniature Housing for 120V MR16

EL1299

- Height: 5 1/2"
- Opening: 4 1/4"
- Lamp: 50W max
- Lamp is included



4" Miniature Remodel Housing for 120V MR16

EL1299R

- Height: 5 7/8"
- Opening: 4 1/4"
- Lamp: 50W max
- Lamp is included

LINE VOLTAGE RECESSED BAFFLE TRIMS 4"

Recessed Lighting



Airtight Baffle Cone Trim

EL902W All White

Lamp: 75W PAR30

O.D.: 5 1/16"



Phenolic Baffle with Metal Ring

EL993W All White

EL993N All Nickel

EL993BZW Bronze Bfl. White Ring

EL993BZ All Bronze

EL993CP All Copper

EL993NW Nickel Bfl. White Ring

EL993WBZ White Bfl. Bronze Ring

EL993WG White Bfl. Gold Ring

EL993WN White Bfl. Nickel Ring

Lamp: 40W R16, 50W PAR20, R20

O.D.: 4 3/4"



Diecast Round Stepped Trim

EL941B Black Bfl. White Ring

EL941W All White

Lamp: 50W PAR20, R20

O.D.: 4 3/4"



Pinhole Trim with Baffle

EL990W Black Bfl. White Ring

EL990BZ All Bronze **NEW!**

EL990CP All Copper **NEW!**

EL990N All Nickel

Lamp: 55W R16, 50W PAR20, R20

I.D.: 2", O.D.: 4 7/8"



Metal Baffle with Metal Ring

EL993MB Black Bfl. White Ring

EL993MW All White

Lamp: 50W PAR20, R20

O.D.: 4 3/4"



Black Phenolic Baffle with Metal Ring

EL993B Black Bfl. White Ring

EL993BCP Black Bfl. Copper Ring

EL993BB All Black

EL993BC Black Bfl. Clear Ring

EL993BG Black Bfl. Gold Ring

EL993BN Black Bfl. Nickel Ring

Lamp: 40W R16, 50W PAR20, R20

O.D.: 4 3/4"



Phenolic Baffle with Metal Ring and Lamp Holder Bracket

EL993KBN Black Bfl. Nickel Ring

EL993KB All Black

EL993KCPW Copper Bfl. White Ring

EL993KN All Nickel

EL993KW All White

Lamp: 40W A19, 40W R16, 50W PAR20, R20

O.D.: 4 3/4"

ARCHITECTURAL HID

4" MH PAR20 DOWNLIGHT

20W-39W Electronic Ballast Metal Halide

- Height: 6 1/2"
- Ceiling opening: 4 3/8"
- Trim O.D.: 4 3/4"



E4M20E 20W PAR20 Med. Base MH Lamp (M156) 120V Electronic Ballast

E4M35E 39W PAR20 Med. Base MH Lamp (M130) 120/277V Electronic Ballast

4" REMODEL MH PAR20 DOWNLIGHT

20W-39W Electronic Ballast Metal Halide

- Height: 6 1/2"
- Ceiling opening: 4 3/8"
- Trim O.D.: 4 3/4"



ER4M20E 20W PAR20 Med. Base MH Lamp (M156) 120V Electronic Ballast

ER4M35E 39W PAR20 Med. Base MH Lamp (M130) 120/277V Electronic Ballast

ARCHITECTURAL HID

TRIMS FOR MH PAR 20 DOWNLIGHTS 4"



Reflector with Lamp Holder Bracket

EL977G Gold Ref. White Ring
EL977B Black Ref. White Ring
EL977C Clear Ref. White Ring
EL977W White Ref. White Ring
 Lamp: 39W M.H. PAR20
 O.D.: 4 3/4"



Adjustable Gimbal Ring

EL985N Nickel
EL985B Black
EL985BZ Bronze **NEW!**
EL985CP Copper **NEW!**
EL985G Gold
 Lamp: 39W M.H. PAR20
 O.D.: 4 3/4"



Metal Step Baffle

EL993MB Black Bfl. White Ring
EL993MW All White
 Lamp: 39W M.H. PAR20
 O.D.: 4 3/4"



Metal Step Baffle with Lamp Holder Bracket

EL993KB Black Bfl. White Ring
EL993KN All Nickel
EL993KW All White
 Lamp: 39W M.H. PAR20
 O.D.: 4 3/4"



Baffle with Lamp Holder Bracket

EL995W All White
EL995B Black Bfl. White Ring
EL995BZ All Bronze
EL995CP All Copper
EL995N All Nickel
 Lamp: 39W M.H. PAR20
 O.D.: 4 3/4"



Eyeball Trim

EL998W White
EL998B Black
EL998BZ Bronze **NEW!**
EL998C Clear
EL998CP Copper **NEW!**
EL998G Gold
EL998N Nickel
 Lamp: 39W M.H. PAR20
 O.D.: 4 3/4"



Reflector with Lamp Holder Bracket

EL999KC Clear Ref. White Ring
EL999KG Gold Ref. White Ring
 Lamp: 39W M.H. PAR20
 O.D.: 4 3/4"



Reflector Trim

EL999C Clear Ref. White Ring
EL999CC All Clear
EL999CN Clear Ref. Nickel Ring
EL999B Black Ref. White Ring
EL999G Gold Ref. White Ring
EL999GG All Gold
EL999GN Gold Ref. Nickel Ring
EL999W All White
 Lamp: 39W M.H. PAR20
 O.D.: 4 3/4"



Reflector with Diecast Ring

EL999DG Gold Ref. White Ring
EL999DC Clear Ref. White Ring
 Lamp: 39W M.H. PAR20
 O.D.: 4 3/4"