


- Features a single-use ceramic mold which eliminates the need for a mold and frame and / or handle clamps.
- Produces a permanent connection that will not loosen or corrode.
- Fits copper-bonded (threaded and plain), galvanized and stainless steel ground rods.
- Simple to use.
- NEC[®] compliant
- cULus[®] Listed
- Rural Utilities Service (RUS) accepted

CADWELD® ONE SHOT

For Connections to Ground Rods



The CADWELD[®] ONE SHOT produces a permanent exothermically welded connection to a ground rod that will not loosen, corrode away, or increase in resistance for the life of the installation.



Position CADWELD ONE SHOT and wire on prepared ground rod. Dump the welding material into the ceramic crucible.



Initiate the reaction with T320 flint ignitor



Set the lid on the CADWELD ONE SHOT body and add the starting material.



The reaction produces a finished permanent exothermic connection







CADWELD® ONE SHOT

For Connections to Ground Rods

Ordering Information

Ground Rod	Concentric Conductor		Metric Cable Conductor	CADWELD ONE SHOT Part Number			
	Solid	Stranded	Square mm	Type GR	Type GT	Туре NT	Туре NX
1/2" (12.7 mm)	6, 8 3, 4 1, 2	8 4, 6 2, 3	8-10 14-22 30-38	GR1141G GR1141L GR1141V	GT1141G GT1141L GT1141V	NT1141G NT1141L NT1141V	NX1141G NX1141L
5/8" (14.2 mm)	6, 8 3, 4 1, 2 2/0, 1/0	8 4, 6 2, 3 1/0, 1 2/0 4/0	8-10 14-22 30-38 50-60 70	GR1161G GR1161L GR1161V GR1162C GR1162G GR1162Q	GT1161G GT1161L GT1161V GT1162C GT1162G	NT1161G NT1161L NT1161V	NX1161G NX1161L NX1161V
3/4" (17.2 mm)	6, 8 3, 4 1, 2 2/0, 1/0	8 4, 6 2, 3 1/0, 1 2/0 4/0	8-10 14-22 30-38 50-60 70	GR1181G GR1181L GR1181V GR1182C GR1182G GR1182Q	GT1181G GT1181L GT1181V GT1182C GT1182G	NT1181G NT1181L NT1181V	NX1181G NX1181L NX1181V

Note: T320 flint ignitor sold separately.

NEC is a registered trademark of, and National Electric Code (NEC) standard is a copyright of the National Fire Protection Association. cULus is a registered trademark of the Underwriters Laboratories, Inc.

WARNING – ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright ©2007 ERICO International Corporation. All rights reserved. CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

EG535 E1144LTOGEN 00210M7

www.erico.com