



PRODUCT SPECIFICATION

COLEMAN PART NUMBER: See table below

DESCRIPTION: 16/2 w/gnd SPT-3 replacement power supply cord

APPROVALS: UL Listed (UL 817)

CONSTRUCTION PARAMETERS:

Conductor:	16 AWG, 26/30 bunched bare copper
Conductor O.D. (nom):	0.063"
Insulated ground conductor O.D. (nom):	0.091"
Insulation material:	PVC, gray
Overall cable dimensions (nom):	0.181 x 0.413"
Cord length:	See table below
Attachment plug configuration:	NEMA 5-15P, see chart below
Plug material:	PVC, gray
Open end configuration:	1.5" separation, 0.38" strip

ELECTRICAL PROPERTIES:

Temperature rating:	-20 to +60 °C
Nominal operating voltage:	125 VAC
Maximum operating current:	13 A
Maximum operating wattage:	1625 W

CATALOG NUMBERS

Catalog number	Cord length	Plug configuration
09723	3 ft	Right angle
09724	4 ft	
09726	6 ft	
09733	3 ft	Straight
09734	4 ft	
09736	6 ft	

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Inc. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Inc.

CUSTOMER APPROVAL: Approved by: _____ Date: _____

Title: _____