


ILSCO

connections
matter

www.ilsco.com



A


TYPE CRAM

Features

- Electro-tin plated
- Sight hole
- Solid seamless tang
- Electrolytic copper
- Suitable for use in circuits rated 35KV or less, proper high voltage spacing and insulation techniques must be used
- Rated to 90° C

Benefits

- Provides low contact resistance
- Visual inspection of proper cable insertion
- For performance and strength
- For high conductivity
- Application versatility



Catalog Number	Alt Wire Size	Wire Size	Bolt Size	Tang Length	Tang Width	Tang Thickness	Overall Length	Die Color Code	I.D.	O.D.
CRA-1-14M	1 FLEX	1/0 AWG	1/4	0.791	0.713	0.110	1.831	PINK	0.406	0.516
CRA-1-516M	1 FLEX	1/0 AWG	5/16	0.791	0.713	0.110	1.831	PINK	0.406	0.516
CRA-1-38M	1 FLEX	1/0 AWG	3/8	0.791	0.713	0.110	1.831	PINK	0.406	0.516
CRA-1-12M	1 FLEX	1/0 AWG	1/2	0.890	0.815	0.110	1.902	PINK	0.406	0.516
CRA-1/0-14M	1/0 FLEX	2/0 AWG	1/4	0.929	0.815	0.110	2.055	BLACK	0.461	0.571
CRA-1/0-516M	1/0 FLEX	2/0 AWG	5/16	0.929	0.815	0.110	2.055	BLACK	0.461	0.571
CRA-1/0-38M	1/0 FLEX	2/0 AWG	3/8	0.929	0.815	0.110	2.055	BLACK	0.461	0.571
CRA-1/0-12M	1/0 FLEX	2/0 AWG	1/2	0.929	0.815	0.110	2.055	BLACK	0.461	0.571
CRA-2/0-14M	2/0 FLEX	3/0 AWG	1/4	0.969	0.894	0.118	2.161	ORANGE	0.512	0.630
CRA-2/0-516M	2/0 FLEX	3/0 AWG	5/16	0.969	0.894	0.118	2.161	ORANGE	0.512	0.630
CRA-2/0-38-M	2/0 FLEX	3/0 AWG	3/8	0.969	0.894	0.118	2.161	ORANGE	0.512	0.630
CRA-2/0-12M	2/0 FLEX	3/0 AWG	1/2	0.969	0.894	0.118	2.161	ORANGE	0.512	0.630
CRA-3/0-38M	3/0 FLEX	4/0 AWG	3/8	1.071	1.035	0.130	2.382	PURPLE	0.591	0.720
CRA-3/0-12M	3/0 FLEX	4/0 AWG	1/2	1.071	1.035	0.130	2.382	PURPLE	0.591	0.720
CRA-4/0-38M	4/0 FLEX	250 kcmil	3/8	1.228	1.201	0.130	2.614	YELLOW	0.685	0.815
CRA-4/0-12M	4/0 FLEX	250 kcmil	1/2	1.228	1.201	0.130	2.614	YELLOW	0.685	0.815

Tooling Information

		ILSCO	Burndy
Flex Size	AWG Size	MT-25 Hand Dieless (A) No. of Crimps	MY29-3 Hand Dieless (A) No. of Crimps
1	1/0	(1)	(2)
1/0	2/0	(1)	(2)
2/0	3/0	(1)	(2)
3/0	4/0	(2)	(2)
4/0	250 kcmil	(2)	(2)

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)
UL File E6207