


THE LEDPANEL G3 IS OUR LATEST GENERATION OF EDGE-LIT LED FLAT PANEL FIXTURES, WHICH INTEGRATES REMPHOS' FLEXCOLOR, FLEXWATT & FLEXCONTROL TECHNOLOGIES.

selectable wattage & color temperature



12 FIXTURES IN 1 WITH FLEXWATT™ & FLEXCOLOR™ TECHNOLOGY

- Eliminate ordering and stocking multiple wattages and color temperatures. Product offers 12 SKUs in 1 unit which can easily be configured to 4 different wattage packages and 3 different CCTs.
- Product ships at a default color temp (K) and wattage setting (install as is, or tailor the settings to ft your needs at your facility or on the job site)
- Save on labor costs by having us factory pre-set the wattage and color temperature to fit your project needs.

NEW PMMA LENS – HIGH EFFICIENCY 120-140LPW

- High transmission and high definition (HD) lens.
- Beautiful uniform illumination.
- PMMA material will not yellow over time like other market products.
- LPW varies based on wattage and color selected.

FLICKER-FREE LED DRIVER

FLEXCONTROL™ TECHNOLOGY

- Order control ready or basic control (integrated high/low and daylight sensor) or LG advanced control.
- Vandal Resistant Sensors are completely adjustable and hidden behind the fixture lens.
- Adjustable via remote for sensitivity, duration of time at high light level before dimming to low, duration of time at low light level before dimming to off (factory default is to disable), daylight hold-off, and the dimmed light level.

MANY MOUNTING OPTIONS

- Ships standard with clips for recessed and pendant install.
- Optional low-profile surface mount kit available.

10 YEAR WARRANTY, L70 > 100,000HRS

OPTIONAL EMERGENCY BATTERY BACKUP



























LEDPANEL G3 LED FLAT PANEL FIXTURE | FLEXWATT + FLEXCOLOR + FLEXCONTROL



PART NUMBER BUILDER

MFR FAMILY PRODUCT GEN **FUNCTION OPTIONS** SIZE WATTAGE **COLOR** BAA **RPT** Ρ **LEDPANEL FWFC** G3

> 2X2 --- 20L,25L,31L,36L 1X4 → 20L,25L,31L,36L 2X4 --- 25L,33L,43L,53L

835=3500K/85CRI 840=4000K/85CRI 850=5000K/85CRI FWFC= OCC=high/low motion sensor BLANK=NON-BAA FlexWatt + EMG=120min emergency FlexColor battery backup

LG=LG dongle LGS=LG dongle + sensor BAA=BAA Section 1605 Compliant

ORDERING EXAMPLE

OPDEDING GUIDE

RPT-P-LEDPANEL-G3-2X2-20L-840-FWFC

Default lumen package (wattage and CCT) are shown below in bold. There are two ways to achieve a non-default lumen package and/or CCT:

1. You can easily adjust in field via our FlexWatt and FlexColor internal switches. 2. Have us adjust the FlexWatt and FlexColor at the factory for an additional charge.

SURFACE MOUNT ACCESSORIES RPT-LEDPANEL-SMK-2X2 RPT-LEDPANEL-SMK-1X4

RPT-LEDPANEL-SMK-2X4

CASE QTY	QUICK SHIP	REMPHOS PART #	QUICK SHIP UPC CODE	LUMEN OUTPUT (LM)	WATTAGE (W)	LPW	CCT (K)	WARRANTY (YRS)
_								
4	•	RPT-P-LEDPANEL-G3-2X2-20L-835-FWFC	04400400045	2000	16	125	3500	10
4		RPT-P-LEDPANEL-G3-2X2-20L-840-FWFC	844006020965	2032	16	127	4000	10
4	•	RPT-P-LEDPANEL-G3-2X2-20L-840-FWFC-OCC-A	844006020996	2032	16	127	4000	10
4		RPT-P-LEDPANEL-G3-2X2-20L-850-FWFC		2032	16	127	5000	10
4		RPT-P-LEDPANEL-G3-2X2-25L-835-FWFC		2500	20	125	3500	10
4		RPT-P-LEDPANEL-G3-2X2-25L-840-FWFC		2540	20	127	4000	10
X 4		RPT-P-LEDPANEL-G3-2X2-25L-850-FWFC		2540	20	127	5000	10
4		RPT-P-LEDPANEL-G3-2X2-31L-835-FWFC		3072	24	128	3500	10
4		RPT-P-LEDPANEL-G3-2X2-31L-840-FWFC		3120	24	130	4000	10
4		RPT-P-LEDPANEL-G3-2X2-31L-850-FWFC		3120	24	130	5000	10
4		RPT-P-LEDPANEL-G3-2X2-36L-835-FWFC		3584	28	128	3500	10
4		RPT-P-LEDPANEL-G3-2X2-36L-840-FWFC		3640	28	130	4000	10
4		RPT-P-LEDPANEL-G3-2X2-36L-850-FWFC		3640	28	130	5000	10
4		RPT-P-LEDPANEL-G3-1X4-20L-835-FWFC		1968	16	123	3500	10
4		RPT-P-LEDPANEL-G3-1X4-20L-840-FWFC		1984	16	123	4000	10
4		RPT-P-LEDPANEL-G3-1X4-20L-850-FWFC		2000	16	124	5000	10
4		RPT-P-LEDPANEL-G3-1X4-25L-835-FWFC		2460	20	123	3500	10
4	•	RPT-P-LEDPANEL-G3-1X4-25L-840-FWFC	844006020972	2480	20	124	4000	10
4	•	RPT-P-LEDPANEL-G3-1X4-25L-840-FWFC-OCC-A	844006021009	2480	20	124	4000	10
½ 4		RPT-P-LEDPANEL-G3-1X4-25L-850-FWFC		2500	20	124	5000	10
4		RPT-P-LEDPANEL-G3-1X4-31L-835-FWFC		3000	24	125	3500	10
4		RPT-P-LEDPANEL-G3-1X4-31L-840-FWFC		3048	24	127	4000	10
4		RPT-P-LEDPANEL-G3-1X4-31L-850-FWFC		3100	24	127	5000	10
4		RPT-P-LEDPANEL-G3-1X4-36L-835-FWFC		3500	28	125	3500	10
4		RPT-P-LEDPANEL-G3-1X4-36L-840-FWFC		3556	28	127	4000	10
4		RPT-P-LEDPANEL-G3-1X4-36L-850-FWFC		3556	28	127	5000	10
4		RPT-P-LEDPANEL-G3-2X4-25L-835-FWFC-A		2540	20	127	3500	10
4		RPT-P-LEDPANEL-G3-2X4-25L-840-FWFC-A		2600	20	130	4000	10
4		RPT-P-LEDPANEL-G3-2X4-25L-850-FWFC-A		2600	20	130	5000	10
4		RPT-P-LEDPANEL-G3-2X4-33L-835-FWFC-A		3350	26	129	3500	10
4	•	RPT-P-LEDPANEL-G3-2X4-33L-840-FWFC-A	844006021535	3390	26	131	4000	10
4	•	RPT-P-LEDPANEL-G3-2X4-33L-840-FWFC-OCC-A		3390	26	131	4000	10
* 4		RPT-P-LEDPANEL-G3-2X4-33L-850-FWFC-A	5	3400	26	131	5000	10
۸ 4		RPT-P-LEDPANEL-G3-2X4-43L-835-FWFC-A		4390	34	129	3500	10
4		RPT-P-LEDPANEL-G3-2X4-43L-840-FWFC-A		4450	34	131	4000	10
4		RPT-P-LEDPANEL-G3-2X4-43L-850-FWFC-A		4450	34	131	5000	10
4		RPT-P-LEDPANEL-G3-2X4-53L-835-FWFC-A		5160	40	129	3500	10
4		RPT-P-LEDPANEL-G3-2X4-53L-840-FWFC-A		5300	40	132	5000	10
4		RPT-P-LEDPANEL-G3-2X4-53L-850-FWFC-A		5300	40	132	5000	10
4		KF I-F-LEDPANEL-U3-ZA4-33L-03U-FWFC-A		5300	40	132	5000	10



FOR PRODUCT INFO ("LED" MODEL #) CONTACT......Light Efficient Design • 188 S. Northwest Highway • Cary, IL 60013 • 847.380.3540 • led-Ilc.com FOR PRODUCT INFO ("RP" MODEL #) CONTACT......RemPhos by Light Efficient Design • 30 Log Bridge Road, Building 200 • Middleton, MA 01949 • 877.997.3674 • remphos.com

LEDPANEL G3 LED FLAT PANEL FIXTURE | FLEXWATT + FLEXCOLOR + FLEXCONTROL





HOW DOES IT WORK?

Our exclusive LED driver is designed to operate at 90%+ efficiency at each wattage setting. Standard drivers would have much lower efficiency as low as 60% and would result in poor performance and


WHAT ARE THE WATTAGE CHOICES?

The 2x2, 1x4 & 2x4 fixtures have different wattage/lumen offerings. Please reference this table and the ordering guide on the last page of the cut sheet.

FLEXWATT TURN DIAL POSITION								
SIZE	0	1	2	3				
2X2	16W (20L)	20W (25L)	24W (31L)	28W (36L)				
1X4	16W (20L)	20W (25L)	24W (31L)	28W (36L)				
2X4	20W (25L)	24W (31L)	28W (36L)	40W (53L)				

HOW EASY IS IT TO SET?

Simply open the driver cover, adjust the 4-position turn dial with a small, flat-head screw driver, and replace the cover. Quick and easy. Can be "locked-out" to prevent field-adjustability if desired.





HOW DOES IT WORK?

We select the highest efficacy, multiple color LED diodes from quality suppliers, and mount them on t he same circuit board. A proprietary LED binning process ensures color consistency between fixtures. The FlexColor technology controller ensures the correct color is selected, every time.


WHAT ARE THE COLOR CHOICES?

3500k, 4000k and 5000k. Please reference this table and the ordering guide on the last page of the cut sheet.

FLEXCOLO	FLEXCOLOR SLIDE SWITCH POSITION						
TOP	MIDDLE	воттом					
3500K	4000K	5000K					

HOW EASY IS IT TO SET?

Adjust the 3-position slide switch with your finger. Quick and easy. Can be "locked-out" to prevent field-adjustability if desired.







10.18.18 Information is subject to change without notice.

LEDPANEL G3 LED FLAT PANEL FIXTURE | FLEXWATT + FLEXCOLOR + FLEXCONTROL









SURFACE MOUNT KIT ACCESSORY (2X2 SHOWN) HEIGHT/DEPTH OF KIT 2.5"

CONTROL OPTIONS

CONTROL READY 10V DIM

All LEDCR/SR come standard as factory enabled to add controls at the factory, in the field or at a later date. Driver comes with 10V dimming and 12V DC power wiring.

BASIC CONTROL



Integrated high frequency, high/low motion and daylight sensor. Can be mounted behind glass or plastic lens. Default settings: SENSITIVITY: 75%, TIME DIM: 5MIN, TIME OFF = DISABLED, PHOTOCELL: DISABLED, DIM LEVEL: 20%. Purchase optional remote control to adjust settings.

ORDERING CODES
SENSOR = OCC / REMOTE CONTROL = HC REMOTE

LG SENSOR CONNECT



LG's intelligent wireless lighting control system. ZigBee technology. Allows for occupancy sensing, daylight harvesting, grouping, scheduling, high-end trim and more. Adjust settings via Android app. Contact us for more details.

ORDERING CODE = LG or LGS

