

42 LED LED Premium Channel

APPLICATIONS

Premium grade LED narrow channel fixture. For use in indoor applications such as factories, warehouses, workshops, utility areas, coves and public buildings where industrial grade is required.

FEATURES & BENEFITS

- ♦ Snap-on components for easy assembly and maintenance
- Versatile end plate doubles as coupler for continuous row mounting
- Available in 24", 36" 48", 72" and 96" (2', 3', 4', 6', & 8' lengths)
- Surface, stem or chain mountable
- ♦ Narrow body width 2 3/4" nominal
- ♦ ETL Listed for damp locations
- Min CRI 82



SPECIFICATIONS

Housing is die-formed from cold rolled steel. Finish is high reflectance baked white enamel. Single wireway cover on non-tandem units. Knockouts are provided for stem mounting. Mounting holes are provided.

ORDERING DATA

EXAMPLE: 42-48LED32DMV40

42					
Series Length	Gear Wattage/ Lumens	Driver ¹	Optics	Color Temp	Options
42 24 24" 48 48" 72** 72" 96 96"	LED 2 ft. 18 Watts 2590 Lumens 24 24 Watts 3355 Lumens 28 28 Watts 3705 Lumens 30 30 Watts 3925 Lumens 4 ft. 24 24 Watts 3475 Lumens 30 30 Watts 4310 Lumens 35 35 Watts 4920 Lumens 48 Watts 6475 Lumens 57 Watts 7755 Lumens 70 70 Watts 9840 Lumens 70 70 Watts 9840 Lumens 97 Watts 12950 Lumens	DMV 120-277VAC 0-10V Dimmable SDMV Step Dimming 120-277VAC 100%-40% D347V 347VAC 0-10V Dimming D120 Triac Dimming 120VAC D277 Triac Dimming 277VAC	(Blank) No Lens FR Frosted Lens	30 3000K EM 35 3500K EM 40 4000K 50 5000K EM LR WP OS SS CS **See chart below ordering options	17 7W Emergency battery pack ~900 Lumens 15 5W Emergency battery pack ~650 Lumens Lens ready (Lens must be ordered on separate line) 9 6' WIP 3 wire Occupancy Sensor Occupany Sensor-Internal Microwave Cord 18/3 6"

ACCESSORIES

A69 Wireguard per 4 ft.

L1084 4 ft. lens

 $\mbox{\bf M38-LED}$ (ends to add lens; need 2

per fixture)

**Cord & Whip Ordering Chart (Add to End of Fixture Part Number)									
Part No.	# of Wires	Length	End Fitting	Finish	Voltage	Amps (TL Only)			
WP - Whip CS - Cordset	(Blank) 3 Wire 4 - 4 Wire 5 - 5 Wire 6 - 6 Wire	(Blank) 6 feet 8 - 8 feet 10 - 10 feet 12 - 12 feet 15 - 15 feet	(Blank) No Plug P* - Standard Plug TL* - Twist Lock	BK - Black WH - White	(Blank) 120-277V 120 - 120V 277 - 277V 347 - 347V 480 - 480V	15 - 15 Amps 20 - 20 Amps			

^{**} Consult factory for 36" & 72".

3 Ft. is special. Consult factory for wattages.

Dimensions and specifications subject to change without notice.








♦ 800-444-WATT → www.mobern.com →
 8200 Stayton Dr., Ste. 500, Jessup, MD 20794


CAT#
JOB NAME





DIMENSIONS





Dimensions and specifications subject to change without notice.







• 800-444-WATT • www.mobern.com • 8200 Stayton Dr., Ste. 500, Jessup, MD 20794

CAT#
JOB NAME

TYPE