

Date:	Type:	
	<i>,</i> .	
ïrm Name:		
Project:		

# iPlayer 3


Author, configure, and control dynamic LED light shows for DMX lighting networks

iPlayer 3 controller is a compact yet powerful show storage and playback device capable of delivering light shows to installations with up to 340 unique light addresses. Packaged with ColorPlay 3 light show authoring software, iPlayer 3 is designed to add new levels of sophistication and flexibility to your lighting installations while eliminating the need for expensive lighting boards and technical programming expertise.

- Easy to use With factory preset shows, custom show-authoring capabilities, an intuitive LCD interface, removable SD card storage, and onboard light addressing features, iPlayer 3 enables you to spend more time on the creative aspects of lighting design and less time on setup.
- Packaged with ColorPlay 3 light show authoring software — ColorPlay 3 gives you the flexibility to create and manage light shows using fully customizable effects, multi-track editing, timeline layering, and transition styles.
- Designed for use with the optional Controller Keypad — Controller Keypad is a wall-mounted user interface providing instant pushbutton playback of up to eight light shows.

- Supports the optional AuxBox expansion device AuxBox automatically triggers up to eight iPlayer 3 light shows using any remote triggering device with a dry-contact closure. Via the AuxBox, you can trigger light shows by motion sensors, 3rd party control or sensor systems, and more.
- Control two DMX universes iPlayer 3 has two DMX output ports, each controlling a universe of 512 DMX channels.
- Automate show playback Set alarms to automatically trigger show playback based on a specific date, day of the week, weekdays, weekends, or an astronomical event, such as sunrise or sunset.

For detailed product information, please refer to the iPlayer 3 Product Guide at www.philipscolorkinetics.com/ls/controllers/iplayer3/



### ColorPlay 3 Effects

Fixed Color

Cross Fade

Color Wash

Chasing

Chasing Node

Sweep

Sweep Node

Sparkle

Streak

Spiral

Burs

Random Color

Image Fade

Video

TXT Text

Strobe

01.00

Ripple

Particle Particle

Colored Bars

Constant Modifier

Wave Modifier

Fade In Fade Out Modifier

RGB Range Modifier

Perlin Noise Modifier



#### **Specifications**

Due to continuous improvements and innovations, specifications may change without notice


Item	Specification	Details	
Capability	Capacity	2 universes of 512 DMX addresses each	
Electrical	Input Voltage	100 – 240 VAC, 50 / 60 Hz, 5 W	
Control	Computer Interface	USB 2.0	
	External / Auxiliary Interface	Two DMX512 RJ45 ports Two RS-232 9-pin serial ports	
	Data Storage	Removable Secure Digital Card drive	
Physical	Dimensions (Width x Depth x Height)	8.2 × 5.4 × 1.3 in (209 × 137 × 33 mm)	
	Weight	1.2 lb (0.54 kg)	
	Housing	Polycarbonate	
	Operating Temperature	14° – 104° F (-10° – 40° C)	
	Humidity	0 – 95%, non-condensing	
Certification and Safety	Certification	UL / cUL, FCC Class B, CE, CQC, C-Tick	














# Software Requirements


System Requirements	Specification	PC	Mac
Software	Operating System	Windows 2000 / XP / Vista	Mac OS 10.4 or greater
	Memory	512 MB RAM	512 MB RAM
	Disk space	60 MB free disk space	60 MB free disk space


## iPlayer 3 and Accessories

11 14/61 5 4114 7 16665501 165					
Item	Туре	Item Number	Philips 12NC		
iPlayer 3	North America Power Cord	103-000019-00	910403327101		
	Europe Power Cord	103-000019-01	910503700392		
	China (CCC) Power Cord	103-000019-02	910503700738		
Controller Keypad	DB-9 Serial	103-000020-00	910503700223		
AuxBox	DB-9 Serial	103-000021-01	910503702433		

Use Item Number when ordering in North America.

**8** For detailed product information, please refer to the iPlayer 3 Product Guide at www.phlipscolorkinetics.com/ls/controllers/ iplayer3/







Fax 617.423.9998

www.philipscolorkinetics.com

Copyright © 2015 Philips Solid-State Lighting Solutions, Inc. All rights reserved. Chromacore, Chromasic, CK, the CK logo, Color Kinetics, the Color Kinetics logo, ColorBlast, ColorBlaze, ColorBurst, ColorGraze, ColorPlay, ColorReach, iW Reach, eW Reach, DIMand, EssentialWhite, eW, iColor, iColor Cove, IntelliWhite, iW, iPlayer, Optibin, and Powercore are either registered trademarks or trademarks of Philips Solid-State Lighting Solutions, Inc. in the United States and / or other countries. All other brand or product names are trademarks or registered trademarks of their respective owners. Due to continuous improvements and innovations, specifications may change without notice. DAS-000020-01 R06 12 Aug 2015

