

LED Temporary High Bay Fixture

120-277 Dual Voltage

Features

- Up to 75% Energy savings over HID
- Light weight; less than 6lbs
- Vibration, shock, and impact resistant
- Corrosion resistant heavy-duty safety cage
- 5 foot power cord; Type SJTW300V
- 5A resettable fuse
- 120V-277V with plug adapter
- Self-locking hook/Carry handle
- Advanced thermal management with aluminum heatsink
- Plug and socket enables luminaires to be linked (100W, max. 6 fixtures; 150W, max. 4 fixtures) with anti-pull metal buckle to ensure strong connection***
- UL 94v0 rating



Applications

Suitable for use in the following areas:

- New building construction or renovation
- Any location where temporary lighting is required



Plug adapter (sold separately)

Catalog Number	UPC	Ship Case	Weight Case	Watts	Lumens	CCT	Volts	HID Equivalent**
17100LEDP2*	03179	4	27	100W	11,000	5000K	120V/277V	400W
17150LEDP2*	03180	4	30	150W	16,500	5000K	120V/277V	600W
Plug Adapter (Sold separately)				Size				
17120277P15	03181	60	25	15AMP	---	---	120V/277V	---
17120277P20	03182	60	28	20AMP	---	---	120V/277V	---

*Suitable for 277V when used with plug adapters 17120277P15, 17120277P20.

**HID equivalent may vary dependent on application and required illuminance.

***Socket can only be used for linking temporary lights. Do not connect any other devices to the socket as this can damage the unit.