# **Metalux AP Series**

#### DESCRIPTION

The Metalux FM is an Energy Star LED flushmount with a field selectable CCT switch that enables customization (from warm to bright white) to suit any decor. The FM has a 120V FCC Class B dimming driver, round or square low-profile lens, and LEDs rated for 50,000 hours. The FM LED energy savings is up to 80% over traditional incandescent or fluorescent options. Typical surface mount applications include bedroom, closet, corridor, stairway and utility rooms.

Catalog #	Туре
Project	
Comments	Date
Prepared by	

#### **SPECIFICATION FEATURES**

#### Construction

- Die formed post painted white steel housing
- Available sizes: 9", 11", 15" and 19" nominal
- Injection molded acrylic round lens
- Tool-less twist and lock channel groove lens retention design for easy maintenance
- Cam-latch lens retention design (19" FM round only)

#### Controls

- Standard 120V Dimming drivers
- Compatible with most standard dimmer switches

# Electrical

- Selectable switch configuration includes 3000K, 4000K, and 5000K
- 120V, FCC Class B rated, Dimming Driver
- L70 at 50,000 rated life-hours (TM-21), or greater than 43 years at 3 hrs/day
- LEDs are 80 CRI minimum

## Shielding

- Round low-profile die formed lens design
- Standard smooth opal white blend provides even illumination with no pixelization
- Lens provides 360-degrees of light distribution

## Installation

- Surface (wall or ceiling) mount capable via junction box
- Includes hardware, cross-bar and wire connectors
- Ambient temperature range: 0°F-122°F

#### Compliance

- UL/cUL listed for dry location
- Energy Star qualified
- RoHS compliant
- LED complies with IESNA LM-79 and LM-80

#### Warranty

Five year warranty



# FM WR CCT SELECT

LED Low Profile Round Flushmount

Wall or Ceiling Mount









	Feature	Benefit
Performance	Field Selecctable CCT (3000-4000-5000K)	Customize light color to match any space
	Energy Star certification	Eligible for Energy Rebates
	5-year warranty	Certified and guaranteed performance
Construction	Long life LED source, 50K life-hrs.	No costly lamp replacements
	J-Box mountable, Hardware included	Easy to install
	Opal white lens for 360-degree of light	Even illumination and light for safety

## ORDERING INFORMATION

Catalog Number	Unit Carton UPC	l2of5	Pallet Qty.
FM9WRCCR	080083845392	10080083845399	96
FM11WRCCR	080083840151	10080083840158	72
FM15WRCCR	080083845378	10080083845375	32
FM19WRCCR	080083845415	10080083845412	24

# PERFORMANCE DATA\*

Catalog Number	Lumens	Watts
FM9WRCCR	900	12.3
FM11WRCCR	1100	14
FM15WRCCR	1800	21.4
FM19WRCCR	2500	32.8


<sup>\*</sup> Performance is measured at 3000K CCT





## **DIMENSIONS**

Catalog Number	Α	В	С	D
FM9WRCCR	10-1/4" [260mm]	3-3/8" [86mm]	8-11/16" [221mm]	11/16" [18mm]
FM11WRCCR	11" [280mm]	3-3/16" [80mm]	9-7/8" [251mm]	5/8" [17mm]
FM15WRCCR	15-1/16" [383mm]	4-1/8" [105mm]	13-1/4" [336mm]	11/16" [18mm]
FM19WRCCR	19" [483mm]	4-5/8" [118mm]	17-9/16" [446mm]	11/16" [18mm]



## SHIPPING DATA

Catalog No.	Individual Wt.	Master Pack	Pallet
FM9	1.2 lbs.	8	96
FM11	2.9 lbs.	4	72
FM15	3.8 lbs.	4	32
FM19	4.9 lbs.	2	24