AMERICAN FITTINGS

2-1/2" to 4" Connectors Set Screw UL Rated & Listed for Dual Use on EMT & Rigid/IMC Conduit



This Product Replaces 2-1/2" to 4" SS and SNT Series Fittings

ERS Series: 2 1/2" to 4" Trade Sizes
EMT & Rigid/IMC Conduit Dual Rated Set Screw Fittings
UL Listed & UL Approved Dual Use on EMT & Rigid/IMC Conduit


Alloy Steel Consruction Precision Machined
Zinc Plated with Clear Chromate Finish
Features: AMFICO's *EZ* **Torque** Combo-Hex/Slot Screws
Furnished with an Industrial Grade Steel Locknut

Twice the Strength and Brinell Hardness of Malleable Iron Fittings with 1/3 the Weight Greatly Reduces Hanging Loads

Improves Installation Time

Unique Low Profile Design Allows Greater Installation Space Conforms to Conduit OD





Trade Size"	Cat #	Configuration	Box Qty.	Weight Each lbs	NAED UPC
2 1/2	ERS250BCONN	Set Screw Connector w/Insul Throat	6	1.2	66236419204
2 1/2	ERS250CONN	Set Screw Connector	6	1.2	66236419200
3	ERS300BCONN	Set Screw Connector w/Insul Throat	6	1.7	66236419205
3	ERS300CONN	Set Screw Connector	6	1.7	66236419201
3 1/2	ERS350BCONN	Set Screw Connector w/Insul Throat	6	2.0	66236419206
3 1/2	ERS350CONN	Set Screw Connector	3	2.0	66236419202
4	ERS400BCONN	Set Screw Connector w/Insul Throat	3	2.4	66236419207
4	ERS400CONN	Set Screw Connector	3	2.4	66236419203

Compliances:

Certified Made in the USA UL 514B Set Screw Fittings UL Rated Concrete Tight When Taped NEMA Standard FB1

Federal Standard A-A-50553 UL Standards: 514B, 467

Certified for MIL-STD 810 Sinusoidal Vibrations

CSA Standard: C22.2 No. 18F

RoHS Compliant REACH Compliant CA Prop 65 Compliant UNSPSC 39121434



Available Options:

Insulated Throat - (Shown Above "B")
Galvanized Plating **
Painted Fittings Color Coded **

Dimensions

Size	Α	В С		D
2-1/2"	2-3/8"	3-7/16"	3-1/4"	2-7/16"
3"	2-7/16"	4"	3-15/16"	3"
3-1/2"	2-7/16"	4-9/16"	4-7/16"	3-1/2"
4"	2-7/16"	5-1/8"	4-15/16"	3-15/16"

Hex Set Screw Recommended Torque 160-200 in-lb

Page

^{**} Consult Factory for Specifics

AMERICAN FITTINGS

2-1/2" to 4" Couplings Set Screw UL Rated & Listed for Dual Use on EMT & Rigid/IMC Conduit



This Product Replaces 2-1/2" to 4" EC and NT Series Fittings

ERS Series: 2 1/2" to 4" Trade Sizes
EMT & Rigid/IMC Conduit Dual Rated Set Screw Fittings
UL Listed & UL Approved Dual Use on EMT & Rigid/IMC Conduit


Alloy Steel Consruction Precision Machined Zinc Plated with Clear Chromate Finish Features: AMFICO's *EZ* **Torque** Combo-Hex/Slot Screws

> **Twice the Strength** and Brinell Hardness of Malleable Iron Fittings with 1/**3 the Weight** Greatly Reduces Hanging Loads

> > Improves Installation Time

Unique Low Profile Design Allows Greater Installation Space Conforms to Conduit OD





Trade Size "	Cat #	Configuration	Box Qty.	Weight Each lbs	NAED UPC
2 1/2	ERS250CPLG	Set Screw Coupling	5	1.1	66236419216
3	ERS300CPLG	Set Screw Coupling	3	1.3	66236419217
3 1/2	ERS350CPLG	Set Screw Coupling	2	1.6	66236419218
4	ERS400CPLG	Set Screw Coupling	2	1.7	66236419219

Compliances:

Certified Made in the USA
UL 514B
Set Screw Fittings UL Rated Concrete Tight When Taped
NEMA Standard FB1

Federal Standard A-A-50553 UL Standards: 514B, 467

Certified for MIL-STD 810 Sinusoidal Vibrations

CSA Standard: C22.2 No. 18F

RoHS Compliant REACH Compliant CA Prop 65 Compliant UNSPSC 39131707



Available Options:

* Galvanized Plating **
Painted Fittings Color Coded **

Dimensions

Size	Α	В	С	D
2-1/2"	2-9/16"	3-7/16"	3-1/4"	2-13/16"
3"	2-5/8"	4"	3-15/16"	3-7/16"
3-1/2"	2-5/8"	4-9/16"	4-7/16"	3-15/16"
4"	2-5/8"	5-1/8"	4-15/16"	4-7/16"

Hex Set Screw Recommended Torque 160-200 in-lb

Page

^{**} Consult Factory for Specifics