

ESL

Escalate™ Stairwell Luminaire

SURFACE



FEATURES

- Long life 60,000 hour LEDs at L80 for reduced maintenance
- Superior color consistency within a 3-step MacAdam ellipse and greater than 80 CRI
- Available in 2', 4' or 8' lengths
- Optional integral emergency battery pack
- Heavy die-formed steel channel with 100% acrylic formed diffuser
- Modular replaceable LED boards and driver accessible for future maintenance or upgrades
- Surface mount, wall mount
- DLC® (DesignLights Consortium) Qualified, with some Premium Qualified configurations - see www.designlights.org
- The DTS, Dimming Bypass Module, is for emergency circuit control loads including sensors and wireless systems listed to UL924
- NX Distributed Intelligence™ provides options for standalone and networked integrated sensor with wired or wireless connectivity for NX system deployments
- Occupancy controlled dimming of the LEDs increases energy savings while maintaining base light levels in stairwells at all times (see Occupancy Sensor on Specification Sheet)
- Five year warranty

ORDERING INFORMATION

ESL						W	ED		
MODEL	SIZE	COLOR TEMP	LUMEN OUTPUT ¹	LENS	DRIVER	DISTRIBUTION		OPTIONS	
ESL Escalate™ Stairwell Luminaire	2 2'	30 3000K	VW 2' (1700), 4' (3300), 8' (6600)	FA Frosted Acrylic	ED 0-10V Dimming ²	W Wide Distribution		ELL14 Emergency Battery Pack, 10W ^{4,5}	CONTROL OPTIONS ⁷
	4 4'	35 3500K	VWHE 4' (3200), 8' (6400)	FP Frosted Polycarbonate				DTS Dimming Bypass Module ^{5,6}	
	8 8'	40 4000K	MW 2' (2200), 4' (3700), 8' (7400)					GLR Fast Blow Fuse	
		50 5000K	MWHE 2' (2000), 4' (3600), 8' (7200)						
			LW 2' (2400), 4' (4100), 8' (8200)						
			LWHE 2' (2600), 4' (4000), 8' (8000)						
			ML 2' (3500), 4' (4600), 8' (9200)						
			MLHE 4' (4600), 8' (9200)						
			HL 4' (5800)						
			HLHE 4' (5500)						
See Lumen Tables below.									
						VOLTAGE			
						U 120V-277V			
						347 347V ³			

¹ Nominal lumen output, refer to specification sheet Performance Tables for exact values and available lumen outputs for fixture size. High efficacy versions designated with "HE"

² External dimming leads not available

³ Not available with HE lumen packages


⁴ For compatibility with Dual-Lite LiteGear® inverters in lieu of installed battery pack, contact Hubbell Lighting representative

⁵ Not available with 2 ft size

⁶ For emergency circuit control loads including sensors and wireless systems listed to UL924. Universal voltage only

⁷ Universal voltage only

⁸ Not available with battery backup



See [Escalate specification sheet](#) for detailed dimensional drawings.

PRODUCT AVAILABILITY

LUMEN OUTPUT	LUMENS (FAW LENS, 4000K)			WATTS	LPW
	2'	4'	8'		
VW	1681	3321	6642	13.8 - 53.4	122 - 124
VWHE		3195	6390	24.4 - 48.8	131
MW	2229	3702	7405	18.2 - 60.8	122
MWHE	2013	3593	7186	15.5 - 55.2	130
LW	2475	4095	8190	20.4 - 68.8	119 - 121
LWHE	2592	4013	8025	20.2 - 58.2	128 - 138
ML	3496	4614	9227	29 - 80.2	115 - 121
MLHE		4599	9199	33.8 - 67.6	136
HL		5833		49.5	118
HLHE		5560		40.8	136