

PHILIPS

LED

Specialty lamps



Special applications deserve **only the benefits of LED**

Philips specialty lamps allow you to maintain a classic feel while enjoying the saving of LED.

Benefits

- Lowers Maintenance cost by reducing re-lamp frequency
- Huge energy savings when comparing to halogen counterparts
- Suitable for damp applications

Features

- Rugged plastic design on many models
- Capsule lamps fit into existing landscape lighting
- C7 is ideal for night-light for night time visibility

Specialty lamps

Ordering, electrical and technical data continued (subject to change without notice)

| | Product Number | 12NC | Description | Bulb | Base | Watts | Lumens | Volts | CRI | LED Lifetime ^{1,2} | CCT | MC/CP ³ | Dim | Legend | Replacement Wattage |
|---------|----------------|--------------|---------------------------------|------|---------------|-------|--------|-------|-----|-----------------------------|------|--------------------|-----|--------|---------------------|
| D E T20 | 477166 | 929001844003 | 1T3/LED/830/G4/ND/12V 6/1BC | T3 | G4 | 1 | 100 | 12 | 80 | 15,000 | 3000 | MC | N | A | 10 |
| D E T20 | 477174 | 929001844203 | 2T3/LED/830/G4/ND 12V 6/1BC | T3 | G4 | 2 | 200 | 12 | 80 | 15,000 | 3000 | MC | N | B | 20 |
| D E T20 | 477240 | 929001844425 | 2T3/PER/830/ND/GY6.35/12V 6/1BC | T3 | GY6.35 | 2 | 200 | 12 | 80 | 15,000 | 3000 | MC | N | C | 20 |
| D E T20 | 477208 | 929001840625 | 2.2T3/PER/830/ND/G8/120V 6/1 | T4 | G8 | 2.2 | 200 | 120 | 80 | 15,000 | 3000 | MC | N | D | 20 |
| D E T20 | 465138 | 929001266825 | 3T3/PER/830/ND/G9/120V 6/1BC | T3 | G9 | 3 | 250 | 120 | 80 | 15,000 | 3000 | MC | N | E | 25 |
| D E T20 | 534263 | 929001840835 | 3.6T3/PER/830/ND/G9/120V 6/1BC | T3 | G9 | 3.6 | 370 | 120 | 80 | 15,000 | 3000 | MC | N | F | 40 |
| D E T20 | 463448 | 929001236903 | 1.2T5/SPC/830/ND/12V/BC/2PK 6/2 | T5 | Wedge | 1.2 | 120 | 12 | 80 | 15,000 | 3000 | MC | N | G | 7 |
| D E T20 | 463455 | 929001237036 | 2T5/LED/830/ND/12V 6/2BC | T5 | Wedge | 2 | 200 | 12 | 80 | 15,000 | 3000 | MC | N | H | 18 |
| D T20 | 471946 | 929001357525 | 7.5R7S/PER/830/ND/120V 4/1BC | T3 | Double end R7 | 7.5 | 800 | 120 | 80 | 15,000 | 3000 | MC | N | I | 100 |
| D T20 | 471952 | 929001373325 | 14R7S/PER/830/ND/120V 4/1BC | T3 | Double end R7 | 14 | 1500 | 120 | 80 | 15,000 | 3000 | MC | N | J | 200 |
| D T20 | 462977 | 929001224603 | BC0.5C7/LED/827/E12/ND 120V 2pk | C7 | E12 | 0.5 | 30 | 120 | 80 | 15,000 | 2700 | MC | N | K | 7 |

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
2. Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.
3. MC/CP = MasterClass or CorePro product.

T20 Title 20 qualified.

E Suitable for use in enclosed luminaires.

W Wet location.

D Damp location.



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008