



Table of Contents

TunableTask Undercabinet Lighting Page 3

120V RSD Regressed Slim Downlight Page 5

GMEXT LED Tape - Dry Location Extended Run Tape - 60' Max Page 7

GMEXT LED Tape - Wet Location Custom Cuts Page 9

HDT Standard / High Output High Density LED Tape Page 11

GeoTask Grandè 12" Square / Round Accent Lighting Page 12

New LED Tape Mounting Channels 8' Lengths and Accessories Page 13





Adjustable Kelvin Undercabinet Lighting

Able to achieve color temps. of 2700K, 3000K and 4000K in a single fixture, this dimmable, adjustable Kelvin undercabinet fixture features excellent color rendering in a powder coated aluminum housing with polycarbonate lens. Low profile and easy to mount in 8", 16", 24" and 32" lengths.

KEY FEATURES

- Adjustable Kelvin 2700K, 3000K, 4000K
- Damp location
- · Powder coat aluminum housing
- Low profile (less than 1")
- Durable polycarbonate lens with even light distribution
- Modular easy to connect multiple fixtures for longer runs
- Dimmable (Triac)
- Maximum Run: 200W

ELECTRICAL

- 120V (remote power supply not required)
- Easy kelvin temperature switching 2700K, 3000K, 4000K
- Rated life: 50,000 hrs.

OPTICS

- 90+ CRI
- 2700K, 3000K, 4000K

CERTIFICATION

· ETL, Energy Star

WARRANTY

• 5 year warranty














ORDERING INFORMATION

Catalog Number	Length	Wattage	Lumens* (@2700K)	CRI	Finish
UCTUN-8-WH	8" / 203mm	6W	400	90+	White
UCTUN-8-BZ	8" / 203mm	6W	400	90+	Bronze
UCTUN-16-WH	16" / 406mm	10W	850	90+	White
UCTUN-16-BZ	16" / 406mm	10W	850	90+	Bronze
UCTUN-24-WH	24" / 610mm	14W	1000	90+	White
UCTUN-24-BZ	24" / 610mm	14W	1000	90+	Bronze
UCTUN-32-WH	32" / 1100mm	16W	1150	90+	White
UCTUN-32-BZ	32" / 1100mm	16W	1150	90+	Bronze
Each fixture comes with a	ne LICTUN-E7-1 connector				

^{*} Kelvin temperature (color) ±200K

ACCESSORIES


Catalog Number	Description
UCTUN-CP6-WH (B)	Plug-in 5' power cord - white or black
UCTUN-EZ-1-WH	Fixture to fixture connector - white
	3" Flexible fixture to fixture connector - white or black
	12" Flexible fixture to fixture connector - white or black
	Quick-Box wiring junction box with EZ connectors and knock-outs - white or olack



Application Guide


144" TYPICAL CABINET CONFIGURATION

TUNABLETASK™ FIXTURES LINKED WITH UCTUN-EZ-12 CONNECTORS



126" TYPICAL CABINET CONFIGURATION

TUNABLETASK™ FIXTURES LINKED WITH UCTUN-EZ-1 CONNECTORS



Color Temp. Guide


Tunable white lighting has become one of the most popular trends in lighting design. In residential kitchen lighting, tunable white undercabinet lighting enables a variety of color renditions that effect ambience and mood.


TunableTask enables three distinct color temperatures:

2700K: Traditional warm white. Similar to incandescent.

3000K: Modern, updated warm white. Similar to halogen.

4000K: Crisp, clean pure white that is closer to daylight.





NOTE: Colors depicted above are used for reference only and do not represent the true color of the light.



120V RSD Regressed Slim Downlight

90+ CRI, Wet Location and IC Rated

Easy to install with an included junction box that is connected via a modular jack, these 3", 4" and 6" slim mount, regressed downlights feature superior optics along with Energy Star rating in a streamlined, shallow mount design.

KEY FEATURES

- 120V
- Wet location
- · IC rating for insulated ceilings
- Edge-Lit technology for diode free illumination
- Dimmable (Triac)
- Shallow mount

ELECTRICAL

- 120V (remote power supply not required)
- Rated life: 50,000 hrs.

OPTICS

- 90+ CRI
- 120° beam angle

CERTIFICATION

- ETL
- Title 24
- Energy Star
- WARRANTY
- 5 year warranty

















ORDERING INFORMATION

Catalog Number	Dimensions	Wattage	Lumens	CRI	Color Temp.*	Finish
RSD-3-27-WH	3-3/4" Dia. Trim	6W	300	90+	2700K	White
RSD-3-30-WH	3-3/4" Dia. Trim	6W	325	90+	3000K	White
RSD-3-40-WH	3-3/4" Dia. Trim	6W	355	90+	4000K	White
RSD-4-27-WH	5-1/8" Dia. Trim	9W	500	90+	2700K	White
RSD-4-30-WH	5-1/8" Dia. Trim	9W	525	90+	3000K	White
RSD-4-40-WH	5-1/8" Dia. Trim	9W	550	90+	4000K	White
RSD-6-27-WH	6-7/8" Dia. Trim	12W	700	90+	2700K	White
RSD-6-30-WH	6-7/8" Dia. Trim	12W	725	90+	3000K	White
RSD-6-40-WH	6-7/8" Dia. Trim	12W	750	90+	4000K	White


^{*} Kelvin temperature (color) ±200K

ACCESSORIES

Catalog Number	Description
RSD-5FT-EXT	5' extension cord for RSD Series downlights
RSD-10FT-EXT	10' extension cord for RSD Series downlights
RSD-20FT-EXT	20' extension cord for RSD Series downlights

CUT-OUT DIMENSIONS

RSD-3: 3" DIA. RSD-4: 4-1/8" DIA. RSD-6: 6-1/8" DIA.





24VDC LEDTask™ Dry Location GMEXT LED Tape

60' Max. Runs! 60' / 120' Reels

GM Lighting's 24VDC GMEXT Series enables extremely long runs from a single lead in a dry or wet location flexible LED tape. Available in 2700K, 3000K, 3500K and 4000K. **Field cuttable and connectable for dry location only.**

KEY FEATURES

- 24VDC
- Mounts with 3M VHB[™] double stick tape
- Sure-Tite flexible tape to tape and tape to power supply connectors available (see below).
- Dimmable (Triac)
- Available also as wet location (see page 7)
- Maximum run on a given lead is 60'
- Available in 60' and 120' reels.
- Cuttable in the field every 2"

ELECTRICAL

- 24VDC remote power supply required
- Rated at 1.5W per foot
- Rated life: 50,000 hrs.

OPTICS


- 2700K, 3000K, 3500K, 4000K
- 120° viewing angle

CERTIFICATION

• ETL

WARRANTY

• 5 year warranty















ORDERING INFORMATION

Catalog Number	Location	Length	Wattage	Lumens	CRI	Color Temp.*
GMEXT-24-60-27	Dry	60'	1.5W / ft.	113 / ft.	90+	2700K
GMEXT-24-60-30	Dry	60'	1.5W / ft.	120 / ft.	90+	3000K
GMEXT-24-60-35	Dry	60'	1.5W / ft.	128 / ft.	90+	3500K
GMEXT-24-60-40	Dry	60'	1.5W / ft.	130 / ft.	90+	4000K
GMEXT-24-120-27	Dry	120	1.5W / ft.	113 / ft.	90+	2700K
GMEXT-24-120-30	Dry	120	1.5W / ft.	120 / ft.	90+	3000K
GMEXT-24-120-35	Dry	120	1.5W / ft.	128 / ft.	90+	3500K
GMEXT-24-120-40	Dry	120	1.5W / ft.	130 / ft.	90+	4000K

Each 60' reel comes with one 24" lead affixed at start of ree

Each 120' reel comes with two 24" leads affixed at each end of reel and four ESTW-60 connectors.

* Kelvin temperature (color) ±200K

Wet Location Available! See Page 9 This LED Tape will fit into the following mounting channels:

Mounting Channels

LED-CHL*
LED-CHL-D*
LED-CHL-XD
LED-CHL-XD-F
LED-CHL-45
LED-CHL-W
LED-CHL-BND*


Note: When using the above channels, use only SureTite™ connectors.

* Use soldered lead for these channels


See www.gmlighting.net for more information.

CONNECTORS

Catalog Number	Description
ESTC-1	Tape to tape SureTite™ connector
ESTLK-60	60" tape to tape SureTite $^{\text{\tiny ™}}$ connector
ESTW-60	60" tape to power supply SureTite $\it ^{\tiny TM}$ connector







24VDC LEDTask™ Wet Location GMEXT LED Tape

60' Max. Runs! Order by length!

GM Lighting's 24VDC GMEXT Series enables extremely long runs from a single lead in a wet location flexible LED tape. Available in 2700K, 3000K, 3500K and 4000K. **Comes in custom cut lengths (maximum 60' on one lead). See ordering example below.**

KEY FEATURES

- 24VDC
- Mounts with silicone mounting clips and screws (supplied)
- Dimmable (Triac)
- Cuttable every 2"
- Maximum run on a given lead is 60'

ELECTRICAL

- 24VDC remote power supply required
- · Rated at 1.5W per foot
- Rated life: 50,000 hrs.

OPTICS

- 2700K, 3000K, 3500K, 4000K
- 120° viewing angle

CERTIFICATION

• ETL

WARRANTY

• 5 year warranty














ORDERING INFORMATION


Catalog Number	Location	Length	Wattage	Lumens	CRI	Color Temp.*	Mounting Channels
GMEXT-24-WP-27-XX-XX	Wet	Custom	1.5W / ft.	113 / ft.	90+	2700K	
GMEXT-24-WP-30-XX-XX	Wet	Custom	1.5W / ft.	120 / ft.	90+	3000K	This LED Tape will fit into the following
GMEXT-24-WP-35-XX-XX	Wet	Custom	1.5W / ft.	128 / ft.	90+	3500K	mounting channels:
GMEXT-24-WP-40-XX-XX	Wet	Custom	1.5W / ft.	130 / ft.	90+	4000K	LED-CHL-W
Each GMEXT-24-WP custom cut comes with one 60" lead affixed at start of tape and silicone mounting clips and screws.				Dry Location		LED-CHL-XD LED-CHL-XD-F LED-CHL-45-1200	
* Kelvin temperature (color) ±2	200K				See Pag	je 7	See www.gmlighting.net for more information.

TO CREATE A CATALOG NUMBER FOR A CUSTOM LENGTH OF GMEXT-24-WP TAPE, SIMPLY SUBSTITUTE 'XX-XX' WITH 'FEET - INCHES'. PLEASE KEEP IN MIND THAT TAPE CAN ONLY BE CUT IN 2" INCREMENTS.

EXAMPLE: TO ORDER A 37' LENGTH OF 2700K WET LOCATION GMEXT TAPE, SPECIFY: GMEXT-24-WP-27-37 EXAMPLE: TO ORDER A 37'-8" LENGTH OF 4000K WET LOCATION GMEXT TAPE, SPECIFY: GMEXT-24-WP-40-37-8







24VDC LEDTask™ High Density LED Tape

90+ CRI Standard and High Output

GM Lighting's LEDTask 24VDC High Density Standard Output Flexible LED Tape features a tightly arranged diode placement that produces an even 'line of light'. Perfect for areas that demand a strong and energy efficient linear light source in low profile channels. Available in 2700K, 3000K, 3500K or 4000K.

KEY FEATURES

- 24VDC
- NEW! Standard output (high output also available)
- Mounts with 3M VHB[™] double stick tape
- Sure-Tite flexible tape to tape and tape to power supply connectors available (see below).
- Dimmable (Triac)
- Dry location
- Maximum run on a given lead is 16'-4"
- Field cuttable every 7 diodes (1")

FI FCTRICAL

- 24VDC remote power supply required
- Rated life: 50,000 hrs.

OPTICS

- 2700K, 3000K, 3500K, 4000K
- 120° viewing angle
- 90+ CRI

CERTIFICATION

- ETL
- Class 2

WARRANTY

5 year warranty

Even line of light-



Diode-Free Imaging From High Density Placement











1300LS1



3STOO.

ORDERING INFORMATION


Custom lengths available - consult factory.

Catalog Number	Length	Output	Wattage	Lumens	CRI	Color Temp.*	Mounting Channels
HDT-28024-S0-27	16'-4" / 5M	Standard	2.5W / ft.	215	90+	2700K	
HDT-28024-S0-30	16'-4" / 5M	Standard	2.5W / ft.	220	90+	3000K	
HDT-28024-S0-35	16'-4" / 5M	Standard	2.5W / ft.	228	90+	3500K	This LED Tape
HDT-28024-S0-40	16'-4" / 5M	Standard	2.5W / ft.	238	90+	4000K	will fit into the
HDT-28024-S0-100-27	100' / 30.48M	Standard	2.5W / ft.	215	90+	2700K	following mounting channels:
HDT-28024-S0-100-30	100' / 30.48M	Standard	2.5W / ft.	220	90+	3000K	LED-CHL-45-1200 LED-CHL-XD
HDT-28024-SO-100-35	100' / 30.48M	Standard	2.5W / ft.	228	90+	3500K	LED-CHL-XD-F
HDT-28024-SO-100-40	100' / 30.48M	Standard	2.5W / ft.	238	90+	4000K	LED-CHL-BND
HDT-28024-HO-27	16'-4" / 5M	High	5.8W / ft.	500	90+	2700K	
HDT-28024-HO-30	16'-4" / 5M	High	5.8W / ft.	510	90+	3000K	
HDT-28024-HO-35	16'-4" / 5M	High	5.8W / ft.	520	90+	3500K	
HDT-28024-H0-40	16'-4" / 5M	High	5.8W / ft.	580	90+	4000K	
Each 16'-4" (5M) reel comes y	with one 24" lead affixe	ed at start of reel an	d three ESTW-60 con	nectors, 100' (38,4M)	reel comes with one 24	" lead affixed at start of reel and e	aht ESTW-60 connectors.

* Kelvin temperature (color) ±200K

CONNECTORS

Catalog Number	Description
ESTC-1	Tape to tape SureTite™ connector
ESTLK-60	60" tape to tape SureTite™ connector
ESTW-60	60" tape to power supply SureTite™ connector



90+ CRI Surface Mount Lighting

GeoTask™ inspires a world of applications through nature's most elemental forms. Our new 12" round and square formats joins our 4", 6" square and 5", 8" round (nominal) versions of GeoTask. Perfect for hospitality lighting, task lighting, light mosaics, kitchen, bath and vanity, residential and commercial lighting applications.

KEY FEATURES

- 3000K / 4000K
- 25W
- Wet location
- Mounts directly to junction box by others
- Edge-Lit technology for diode free illumination
- 1500 lumens
- Dimmable (Triac)
- Shallow 5/8" depth
 See www.gmlighting.net for other
 GeoTask sizes.

ELECTRICAL

- 120V (remote power supply not required)
- Rated life: 50,000 hrs.

OPTICS

- 90+ CRI
- 3000K, 4000K

CERTIFICATION

• ETL

WARRANTY

• 5 year warranty














ORDERING INFORMATION


Catalog Number	Dimensions	Wattage	Lumens	CRI	Color Temp.*	Finish
GM-RND12-30-WH	12" Dia. x 5/8"D	25W	1500	90+	3000K	White
GM-RND12-40-WH	12" Dia. x 5/8"D	25W	1550	90+	4000K	White
GM-SLD12-30-WH	12" Sq. x 5/8"D	25W	1500	90+	3000K	White
GM-SLD12-40-WH	12" Sq. x 5/8"D	25W	1550	90+	4000K	White

^{*} Kelvin temperature (color) ± 200 K

NOTE: Mounts to 2-3/4" or 3-1/2" standard junction boxes (by others)









Aluminum Architectural LED Tape Channels

NEW! 8' Lengths

GM Lightings aluminum channels accepts all GM Lighting LEDTask™ flexible LED linear tape. Perfect for installations that require a rigid extruded channel that the LED tape can be mounted into. Each channel and lens can be cut in the field to the desired length needed.

KEY FEATURES

- High grade extruded aluminum construction
- Includes snap-in frosted lens
- Can be cut in field to any length needed
- · Available in a variety of widths, depths and styles
- Optional end caps and accessories available

LED-CHL-W-8



LED-CHL-BND-8 Bendable channel

with lens

LED-CHL-8 with optional End Cap








ORDERING INFORMATION

Catalog Number	Description	Length	For LEDTask™ Tape Series	Finish
LED-CHL-8	Extruded recessed channel. Includes snap-on frosted lens with mounting screws.	8'	LTR60, LTR300 Dry Location, GM100-24	Aluminum
LED-CHL-BND-8	Bendable channel with frosted lens.	8'	LTR300 Dry Location, ESR Series, CTK Series, HDT Series,. GMEXT Series	Aluminum
LED-CHL-W-8	Extruded wide recessed channel. Includes snap-on frosted lens with mounting screws.	8'	LTR150-RGB, LTR150WP-RGB. LTR1200, LTR30024-90, ESR Series, CTK-24024 Series, HDT-28024 Series, GMEXT Series, all Wet Location	Aluminum
LED-CHL-XD-8	Extruded extra deep and wide recessed channel with lens.	8'	All GM Lighting LED linear tape and Sure-Tite™ connectors.	Aluminum

LED-CHL-XD-8

OPTIONAL END CAPS and ACCESSORIES

Catalog Number	Description
LED-CHL-EC	End caps (2) for LED-CHL-4/8
LED-CHL-W-EC	End caps (2) for LED-CHL-W-8
LED-CHL-XD-EC	End caps (2) for LED-CHL-XD-8
LED-CHL-BND-EC	End caps (2) for LED-CHL-BND-8
LED-CHL-AMC	Adjustable brackets (2) for LED-CHL-8
LED-CHL-AMC-W	Adjustable brackets (2) for LED-CHL-W-8
LED-CHL-AMC-XD	Adjustable brackets (2) for LED-CHL-XD-8
LED-CHL-XD-F-DC	Drywall mounting brackets (2) for LED-CHL-XD-F-8









GMLighting®

"Lighting Enhanced by Design"

9830 W. 190th Street • Unit F Mokena, IL 60448
Toll-Free: (866) 671-0811
FAX: (708) 478-2640
www.gmlighting.net

Printed in the U.S.A. June 2018

©2018 GM Lighting, LLC Specifications are subject to change without notice