

Telephone and Coaxial Outlet Plates

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number
 1-Gang, 1-Tel Nylon .406 in. (10.3) Hole, Box Mount	Almond	NP11AL	NPJ11AL	Aluminum	①
	Black	NP11BK	—	Brass	①
	Brown	NP11	NPJ11	Brass Plated	①
	Gray	NP11GY	—	Chrome	①
	Ivory	NP11I	NPJ11I	S/S 302/304	SS11*
	Light Almond	NP11LA	NPJ11LA	S/S 430	SS11L*
	Red	NP11R	—		
	White	NP11W	NPJ11W		
 1-Gang, 1-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Strap Mount	Black	NP12BK	—	Aluminum	①
	Brown	NP12	—	Brass	SB12*
	Gray	NP12GY	—	Brass Plated	SBP12*
	Ivory	NP12I	—	Chrome	SCH12*
	White	NP12W	—	S/S 302/304	SS12*
				S/S 430	—
 1-Gang, 1-Tel .625 in. (15.9) Hole, Box Mount	Almond	NP737AL	—	Aluminum	—
	Brown	NP737	—	Brass	—
	Ivory	NP737I	—	Brass Plated	—
	White	NP737W	—	Chrome	—
				S/S 302/304	—
				S/S 430	—
 1-Gang, 1-Tel .625 in. (15.9) Hole, Strap Mount	Brown	NP730	—	Aluminum	—
	Ivory	NP730I	—	Brass	—
	White	NP730W	—	Brass Plated	—
				Chrome	—
				S/S 302/304	—
				S/S 430	—
 1-Gang, 1-Tel .380 in. (9.7) Hole, Box Mount or Strap Mount	Black	—	—	Aluminum	①
	Gray	—	—	Brass	①
	Ivory	—	—	Brass Plated	①
	White	—	—	Chrome	①
				S/S 302/304	SS739
				S/S 302/304, Strap Mount	SS738
				S/S 430	—
 2-Gang, 2-Tel Nylon .406 in. (10.3) Hole, Metal .640 in. (16.3) Hole, Box Mount	Black	NP21BK	—	Aluminum	①
	Brown	NP21	—	Brass	①
	Gray	NP21GY	—	Brass Plated	①
	Ivory	NP21I	—	Chrome	①
	White	NP21W	—	S/S 302/304, Strap Mount	SS22*
				S/S 430	—
 2-Gang, 1-Tel .640 in. (16.3) Hole, Box Mount	Black	—	—	Aluminum	—
	Gray	—	—	Brass	—
	Ivory	—	—	Brass Plated	—
	White	—	—	Chrome	—
				S/S 302/304	SS741*
				S/S 430	—

Note: All nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate, see pages O-31 to O-34. Consult custom wallplates section for additional openings and combinations.

* .50" (12.7) I.D. nylon bushing provided.

Dimensions in Inches (mm)