



## Hospital Products

# Heavy Duty GFCI Receptacles with Auto Grounding and SNAPConnect® GFCI LED Receptacles

15 and 20 Ampere, 125 Volts AC

2 Pole, 3 Wire Grounding



GFR8200HOWLA

## 10kA Short Circuit Current Rating

### Comprehensive diagnostics

- When test button is actuated, both the electronic components and mechanical trip mechanism are functionally tested

### Ground fault indicator

- Flashing **RED** indicates device has lost capability to provide protection

### No power at face if reverse wired

- Open circuit condition eliminates false assumption of protection at face

### Installation ease

- Internal back wiring
- Automatic grounding clip
- Captive mounting screws

15A 125V  
NEMA 5-15R  
UL CSA  
0.5 HP20A 125V  
NEMA 5-20R  
UL CSA  
1 HP



## Hospital Grade ● Circuit Guard® GFCI Receptacles

Description	Rating	Color	Catalog Number	
Flush, nylon face, back and side wired, multiple drive screws, automatic grounding clip.	15 and 20A 125V AC	Almond	GFR8200HALLA	GFR8300HALLA
		Black	GFR8200HBKLA	GFR8300HBKLA
		Brown	GFR8200HLA	GFR8300HLA
		Gray	GFR8200HGYLA	GFR8300HGYLA
		Ivory	GFR8200HILA	GFR8300HILA
		Light Almond	GFR8200HLAA	GFR8300HLAA
		Office White	GFR8200HOWLA	GFR8300HOWLA
		Red	GFR8200HRLA	GFR8300HRLA
		White	GFR8200HWLA	GFR8300HWLA

Note: GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with a matching color nylon wallplate. 20 amp feedthrough capability.

15A 125V  
NEMA 5-15R  
UL CSA  
0.5 HP20A 125V  
NEMA 5-20R  
UL CSA  
1 HP

## Hospital Grade ● SNAPConnect® GFCI LED Tamper and Weather Resistant "Buy American" Compliant

Description	Rating	Color	Catalog Number	
 Hospital Grade ●  Tamper and Weather Resistant, impact resistant flush nylon face, SNAPConnect® modular GFCI requires pigtailed terminal below, sold separately. Assembled in the U.S.A.	15 and 20A 125VAC	Almond	GFR8200SNAPAL	GFR8300SNAPAL
		Black	GFR8200SNAPBK	GFR8300SNAPBK
		Brown	GFR8200SNAP	GFR8300SNAP
		Gray	GFR8200SNAPGY	GFR8300SNAPGY
		Ivory	GFR8200SNAPI	GFR8300SNAPI
		Light Almond	GFR8200SNAPLA	GFR8300SNAPLA
		Red	GFR8200SNAPR	GFR8300SNAPR
		White	GFR8200SNAPW	GFR8300SNAPW

Note: \* See Section X, page X-10 for TR and WR descriptions.

## SNAPConnect® Right Angle Pigtailed Terminal "Buy American" Compliant

Description	Catalog Number
Clear terminal with 6-inch leads solid wire.	SNAP1RNA
Clear terminal with 6-inch leads stranded wire.	SNAP2RNA

GFR8200HOWLA

GFR8300SNAPW

SNAP1RNA