

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.

FREEPORT™

Olde Penny **FINISH**
Etched Seedy **GLASS**



FREEPORT Olde Penny (OP)

ITEM	WIDTH/ DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	BULBS	ECO-OPTIONS			AVAILABLE FINISHES
								GU24 Energy efficient socket accepts LED, Dark Sky and Fluorescent lamps.	LED Includes integrated high efficiency LED light source.	LED LIGHT ENGINE	
1800 OP	6" W	9¼"	7"	2½"	4½" W, 6" H Back Plate		1-75w Med.	1800 OP-GU24	1800 OP-LED	UNI-60	BK, OP, OZ
1801 OP	10" Dia.	20¼"			3" Dia. Post Fitter		1-100w Med.	1801 OP-GU24			BK, OP, OZ
1802 OP	10" Dia.	14"			4¼" Dia. Canopy	6', 5'	1-100w Med.	1802 OP-GU24	1802 OP-LED	UNI-100	BK, OP, OZ
1804 OP	8" W	12¼"	9"	3"	5" W, 8" H Back Plate		1-100w Med.	1804 OP-GU24	1804 OP-LED	UNI-100	BK, OP, OZ
1805 OP	10" W	15¼"	11¼"	3¼"	5¾" W, 9½" H Back Plate		1-100w Med.	1805 OP-GU24	1805 OP-LED	UNI-100	BK, OP, OZ

For posts and pier mounts, see pages 613-614. For Fluorescent/GU24 lamps and LED specifications, see pages 412-413.