CWH1000 SERIES

COMMERCIAL FAN-FORCED WALL HEATER



IDEAL SPACES

- Vestibules
- Entrance Ways
- Lobbies
- Hallways
- Stairwells
- Restaurants
- Conference Rooms
- Offices
- Basements
- Family Rooms
- Bedrooms

COLORS

White

DIMENSIONS

• Grille: 12-1/8"H x 10-5/8"W x 7/8"D

Back Box: 11"H x 9-1/4"W x 4"D

TEMP RANGE

■ 40°-85°F

CFM

65









- Contemporary, commercial-grade steel grille, designed to provide comfort through optimized airflow
- Power on/off switch for added safety during maintenance
- Manual reset thermal overheat protector disconnects power in the event of accidental blockage
- Automatic fan delay eliminates cold drafts on start-up and discharges residual heat from the heater body during shut down
- Integral thermostat allows for easy adjustment of room temperature to maintain desired comfort level
- All units have a permanently lubricated fan motor, which creates long life and low maintenance, and gently distributes warmth throughout the area
- Tamper-proof plug for thermostat hole



CWH1000 SERIES

COMMERCIAL FAN-FORCED WALL HEATER

MODELS & SPECIFICATIONS								
CATALOG NO.	UPC	VOLTS	WATTS	AMPS	PHASE	BTU/HR.	SHIP WT. (LBS.)	
CWH1101DSF	6 85360 16296 6	120	1000/500	8.4/4.2	1	3413/1706	12	
CWH1151DSF	6 85360 16298 0	120	1500/750	12.5/6.25	1	5120/2560	12	
CWH1201DSF	6 85360 16302 4	120	1800	15	1	6143	12	
CWH1202DSF	6 85360 16306 2	240	2000/1000	8.3/4.2	1	6826/3413	12	
		208	1500/750	7.2/3.61		5120/2560		
CWH1157DSF	6 85360 16300 0	277	1500/750	5.5/2.75	1	5120/2560	12	
		240	1125/562	4.7/2.35		3840/1920		
CWH1207DSF	6 85360 16308 6	277	2000/1000	7.2/3.61	1	6826/3413	- 12	
		240	1500/750	6.25/3.2		5120/2560		
CWH1208DSF	6 85360 16304 8	208	2000/1000	9.6/4.8	1	6826/3413	12	

ACCESSORIES							
CATALOG NO.	UPC	DESCRIPTION	SHIP WT. (LBS)				
CWHSM	6 85360 13947 0	Surface Mounting Frame. Order Separately. 12-1/2"H x 10-3/8"W x 4"D. White	3				
CWHS1	6 85360 13948 7	1 in. Recess Mounting Frame (Accessory) Order Separately, White	3				
CWHS2	6 85360 13949 4	2 in. Recess Mounting Frame (Accessory) Order Separately, White	3				
SRAFCTPF	6 85360 13950 0	Tamper-Resistant Front Cover, White	1				





