



AMERICAN FITTINGS Corporation


Made in the USA Since 1946

Heavy Duty Industrial
Specification Grade
Locknuts 1/2" to 2"
Solid Steel Construction


"TURN ON" with AMFICO's Next Generation SPEC-grade LOCKnuts™

Heavy Duty Industrial
Specification Grade Locknuts

Solid Steel Construction
Machined from Bar Stock
Electro Plated Zinc, Will Not Flake When Installed
Made in the USA



Patent Pending



The Most Severe Vibrations Will NOT Loosen This Locknut's "Cutting Edge" Grip

SPEC-grade LOCKnuts™

Our solid steel industrial grade locknuts feature AMFICO's uniformed and uniquely designed machine cut serrations. This assures you the capability of cutting through protective coatings on boxes or enclosures to guarantee a positive lock for bonding and grounding.

Unique beveled tangs provide the easiest means to tighten the locknut.

Fully machined ID threads provide the fastest and an ultra-secure threading to pipe or AMIFCO fittings.

Patent Pending

Solid Steel Fully Machined Industrial Specification Grade Locknuts

Cat. #	Trade Size	A	B Thickness
LN 50US	1/2"	1.13"	.13"
LN 75US	3/4"	1.39"	.13"
LN100US	1"	1.69"	.17"
LN125US	1-1/4"	2.06"	.17"
LN150US	1-1/2"	2.28"	.17"
LN200US	2"	2.78"	.17"

Better Ideas, Better Products, Made in the USA

amftgs.com

t: 800.221.5268

e: info@amftgs.com

AMERICAN FITTINGS Corporation



Made in the USA Since 1946

RIGID - IMC CONDUIT
Conduit Locknuts (UL & CSA Listed)
SIZE RANGE: 1/4" - 6"

Conduit Locknuts (UL & CSA listed)

- Industrial specification grade steel
- Heavier steel construction
- Electro zinc plated for corrosion protection
- Fastens threaded conduit to unthreaded opening in a box or enclosure
- Superior clean threads for tightening without distortion
- Rugged tangs for extensive reach and ensured bonding




E93605



LR61799

SPEC-grade



Dimensional Table

Cat. #	A Diameter	B Thickness
LN25	.80	.11
LN38	.98	.12
LN50	1.13	.13
LN75	1.38	.14
LN100	1.72	.18
LN125	2.06	.19
LN150	2.38	.18
LN200	2.89	.19
LN250	3.54	.39
LN300	4.23	.39
LN350	4.75	.39
LN400	5.29	.39
LN500	6.68	.50
LN600	7.34	.56

Cat. #	Size	Unit Ctn	Std Pkg	WT/ 100
LN25	1/4"	200	2000	1
LN38	3/8"	200	2000	1
LN50	1/2"	200	2000	1
LN75	3/4"	100	1000	2
LN100	1"	50	500	4
LN125	1-1/4"	50	500	7
LN150	1-1/2"	25	250	8
LN200	2"	25	250	9
LN250	2 1/2"	-	30	29
LN300	3"	-	25	42
LN350	3 1/2"	-	25	48
LN400	4"	-	25	52
LN500	5"	-	10	95
LN600	6"	-	10	106

* Malleable Iron

Rigid IMC Conduit Fittings

AMFTGS.com

t: 800-221-5268

e: info@amftgs.com

© Copyright 2013 AMERICAN FITTINGS Corporation, Fair Lawn, NJ • Specifications Subject to Change without Notice

AMERICAN FITTINGS Corporation



Made in the USA Since 1946


RIGID - IMC CONDUIT
Sealing Locknuts
Size Range: 1/2" to 6"

Sealing Locknuts

- Zinc plated with PVC Molded Gasket



SPEC-grade



Steel - Sealing Locknuts

Cat. #	Size	Unit Ctn	Std Pkg	WT/ 100
SL1*	1/2"	100	1000	2
SL2*	3/4"	100	1000	3
SL3*	1"	50	500	2
SL4*	1-1/4"	25	250	8
SL5*	1-1/2"	25	250	8
SL6*	2"	10	100	12
SL7	2-1/2"	-	25	20
SL8	3"	-	25	20
SL9	3-1/2"	-	10	24
SL10	4"	-	10	24
SL11	5"	-	5	95
SL12	6"	-	5	125

Dimensional Table

Cat. #	A Diameter	B Thickness
SL1	1.12	.26
SL2	1.37	.27
SL3	1.75	.28
SL4	2.06	.32
SL5	2.37	.32
SL6	2.87	.32
SL7	3.43	.32
SL8	4.12	.32
SL9	4.62	.32
SL10	5.18	.32

*UL & CSA Listed

Rigid IMC Conduit Fittings

AMFTGS.com

t: 800-221-5268

e: info@amftgs.com

© Copyright 2013 AMERICAN FITTINGS Corporation, Fair Lawn, NJ • Specifications Subject to Change without Notice



Grounding Locknuts

- Threaded for Rigid/IMC conduit
- Used to insure positive bonding and fastening to a box or enclosure
- Required for installations where severe vibration is encountered
- Solid steel construction
- Zinc plated for corrosion protection



SPEC-grade



Grounding Locknuts

Cat. #	Size	Unit Ctn	Std Pkg	WT/ 100
GRL50	1/2"	100	1000	3
GRL75	3/4"	100	1000	3
GRL100	1"	50	500	5
GRL125	1-1/4"	50	250	6
GRL150	1-1/2"	25	250	9
GRL200	2"	20	200	14
GRL250	2-1/2"	-	25	16
GRL300	3"	-	20	28
GRL350	3-1/2"	-	10	36
GRL400	4"	-	10	40

Dimensional Table

Cat. #	A Diameter	B Thickness
GRL50	1.340	.170
GRL75	1.575	.170
GRL100	1.890	.170
GRL125	2.300	.170
GRL150	2.600	.170
GRL200	3.100	.187
GRL250	3.562	.375
GRL300	4.250	.375
GRL350	4.803	.375
GRL400	5.402	.375