



**Commercial
Indoor Lighting
Portfolio**



Everyday Lighting Done Right™

Contractor Select™ products are simply our most popular products for the most common projects—perfect for those everyday lighting jobs. They are readily available and have the right combination of features, performance and efficiency to get the job done right.



The nLight® platform of products is the go-to digital lighting controls platform for specifiers, contractors, and building owners. With both wired and wireless solutions you can easily connect luminaires, sensors, and other control devices to create a digital network that is easy to specify, install and own.



Coming Summer 2020

Designed with contractors in mind, the Sensor Switch® JOT enabled wireless solution offers a straightforward approach to the installation and pairing of lighting fixtures and controls. Absolutely no 0-10V control wires and no mobile apps are needed with JOT enabled products, allowing for lightning speed installation right out of the box.

From everyday jobs to specification opportunities, Lithonia Lighting® has you covered across multiple applications!



Retail



Education



Healthcare



Office

Panels

The Lithonia Lighting® portfolio of LED panels are problem solvers. Whether you need a simple replacement of outdated fixtures, or a highly configurable panel with unique lens designs, Lithonia Lighting has you covered! Our LED panels offer a variety of mounting options, sizes and controls options to meet your needs.



	CPX*	CPANL*	EPANL	SPANL
	Stock	Stock, Spec	Stock, Spec	Spec
				
Applications	Schools, Retail, Convenience Stores and other Commercial Spaces	Schools, Offices, Retail and Healthcare Applications	Schools, Offices, Retail and Healthcare Applications	Class A Office Spaces, High-End Retail and other Commercial Spaces seeking modern design
Sizes by Feet	2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4
Lumen Range	3,200 - 4,000	2,400 - 6,000	1,500 - 7,200	2,000 - 8,000
LPW (MAX)	114	121	150	150
CCT	3500/4000/5000K	3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K
CRI (MAX)	80	80	80	90
Listings	DLC, ETL, IC Rated, IP5X	CSA, Damp Listed, DLC, IC Rated	CSA, Damp Listed, DLC, DLC Premium, IC Rated, IP5X	CSA, Damp Listed, DLC, DLC Premium, IC Rated, IP5X
Optics	Standard Matte White	Standard Matte White	Standard Matte White	360° Volumetric, 3D Frame, 3D Center Basket
Controls	N/A	Lumen/Wattage Switchable Driver	nLight®, nLight® AIR, JOT	nLight®, nLight® AIR
Mounting Options	Recessed, Surface Box	Recessed, Surface Box, Direct Ceiling, Suspended	Recessed, Surface Box, Suspended	Recessed, Surface Box, Suspended
Colors/Finish	Glossy White	Glossy White	Glossy White	Matte White, Natural Aluminum, Matte Black
Emergency Options	Remote Mount	Field Installable, Remote Mount	Factory Installed, Field Installable, Remote Mount	Factory Installed, Field Installable, Remote Mount

*Some versions are part of the Contractor Select™ Program and In Stock
Please visit our website to see specification sheets for up to date information.

Lay-Ins

Lithonia Lighting® offers a range of highly configurable recessed solutions to meet all of your general ambient lighting needs. Lensed and center basket recessed lay-ins offer a great one-for-one replacement for fluorescent fixtures and our ambient lay-ins meet specifiers expectations for quality of light with ease.



	BLC*	BLT	VTL	Avante	ENVEX®	ALL
	Stock	Stock, Spec	Spec	Spec	Spec	Spec
	 					
Applications	Schools, Offices, Retail and other Commercial Spaces	Office, Retail, Education, Healthcare and any Commercial Space	Offices, Education, Healthcare and Retail Applications	Large Spaces including Open Offices, Circulation Areas, Classrooms, Libraries, Cafeterias, Airport Ticketing and Wait Areas	Office, Retail, Education, Healthcare and any Commercial Spaces	Office, Retail, Education, Healthcare and any Commercial Spaces
Sizes by Feet	2x2, 2x4	1x4, 2x2, 2x4 *Metric Sizes Available	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4
Lumen Range	3,300 - 5,000	1,000 - 12,000	1,500 - 12,000	1,800 - 5,000	1,500 - 7,200	2,000 - 7,200
LPW (MAX)	128	154	139	105	125	128
CCT	3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K
CRI (MAX)	80	90	90	80	90	90
Listings	CSA, DLC, IC	CSA, DLC, IC	CSA, DLC, IC	CSA, DLC, IC	CSA, DLC, IC, IP5X	CSA, DLC, IC
Style Options	Curved, Smooth Lens Square, Smooth Lens	Curved, Ribbed Lens Curved, Smooth Lens Square, Ribbed Lens Square, Smooth Lens	Acrylic Liner Prismatic Lens, Acrylic Liner Prismatic Lens with Diffuser Trim Rings	Metal Diffuser, Round Holes, Straight Louver, Round Holes, Acrylic Diffuser, Linear Prismatic Lens	Hourglass Design Hourglass with Center Spine Design	Translucent Center Element Design
Controls	JOT	Sensor Switch® Individual Control, nLight®, nLight® AIR, JOT	Sensor Switch® Individual Control, nLight®, nLight® AIR	nLight®, nLight® AIR	Sensor Switch® Individual Control, nLight®, nLight® AIR	nLight®
Emergency Options	Factory installed	Factory installed battery packs and generator devices	Factory installed battery packs and transfer devices	Factory installed battery packs	Factory installed battery packs and transfer devices	Factory installed battery packs and transfer devices

*Some versions are part of the Contractor Select™ Program and In Stock

Please visit our website to see specification sheets for up to date information.

Linear Wraparounds

Lithonia Lighting® wraparounds are engineered to deliver long-life LEDs, low-maintenance and high-quality illumination. Our wraparounds come in a variety of sizes, lumen packages, mounting and controls options to give you the ideal fixture for any direct mount or open ceiling project.



	FMLWL*	SBL*	LBL*	BLWP	STL	LL
	Stock	Stock, Spec	Stock, Spec	Stock, Spec	Spec	Spec
						
Applications	Closets, Foyers, Hallways, Corridors, Offices, Utility Work Areas	Closets, Storage Rooms, Offices	Educational Spaces, Offices, Storage Rooms, Hallways or Closets	Schools, Offices, Stairwells and Other Commercial Spaces	Gym, Hallways, Office	Retail, Open Office, Hospitality, Education
Sizes by Feet	2, 4'	1x2, 1x4	2, 4, 4W, 8'	2, 4, 8'	2, 4'	8, 16'
Lumen Range	1,400 - 4,600	2,000 - 7,200	2,000 - 14,400	800 - 20,000	2,000 - 6,000	6,000 - 20,000
LPW (MAX)	120	121	136	144	110	120
CCT	2700/3000/3500/4000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K
CRI (MAX)	80	80	80	90	80	80
Listings	UL, Damp Listed, DLC	CSA, Damp Listed	CSA, Damp Listed, DLC, DLC Premium	CSA, DLC Premium	CSA, Damp Listed, DLC, DLC Premium	CSA, DLC
Diffuser Style	Diffuse Polycarbonate	Prismatic Acrylic	Prismatic Acrylic	Curved, Ribbed Lens Curved, Smooth Lens Square, Ribbed Lens Square, Smooth Lens Curved, Smooth Polycarbonate	Diffuse Polycarbonate	Diffuse Polycarbonate
Controls	N/A	nLight®, Sensor Switch®	Sensor Switch® LSXR, nLight®	JOT, Sensor Switch® Individual Control, nLight®, nLight® Air	nLight®	Sensor Switch® VERTEX
Emergency Options	Factory installed battery packs and transfer devices	Factory installed battery packs	Factory installed battery packs and transfer devices			
Mounting Options	Surface	Surface, Suspended	Surface, Suspended	Surface, Suspended	Surface, Suspended	Suspended
Colors/Finish	Matte White	Matte White	Matte White	Matte White, Natural Aluminum, Matte Black	Matte White, Natural Aluminum, Matte Black	Matte White, Natural Aluminum, Matte Black

*Some versions are part of the Contractor Select™ Program and In Stock
Please visit our website to see specification sheets for up to date information.



Visit www.lithonia.com for more information

One Lithonia Way | Conyers, Georgia 30012 | Phone: 800-705-7378 | www.acuitybrands.com
©2020 Acuity Brands Lighting, Inc. All rights reserved. | LL_426266_0120

AcuityBrands