

**Great new look for Landscape Lighting! Features 2 level cutoff protection.** 

Rugged die cast aluminum housing with durable powder coating.

Socket with all copper electrical parts and 20" leads

Quick and secure installation with one corrosionproof screw

Threaded, gasketed globes for durable weatherproofing and easy relamping

12" color matched mounting stem with 1/2" threads available

Includes easy mounting 1/2" threaded nipple



ST12VG

### 2 Level Light Cutoff



Wide light spread for wider walkways & parking lots where maximum light is required



Full Cutoff for narrow walkways & glare free lighting in garden areas

### **Quick and Easy Adjustment**



### **Product Information**

#### Incandescent (120 volt)

Lamp not supplied

Compact Fluorescent (120 volt)
Lamp supplied with fixture.
Minimum operating temperature 32°
NPF 120 volt ballast

.amp Natts			Initial Lumens		
75	A-19	Med	1220	750	
100	A-19	Med	1650	750	
13	Quad	GX23-2	860	10 000	

# CFL

## Specifications : Wus

#### **UL Listing:**

Suitable for wet locations. Suitable for mounting within 4 feet of the ground.

#### Socket:

Medium base porcelain with all copper electrical parts and 20" leads, including a ground lead.

#### Lamps:

Incandescent- (not supplied)
Medium base A-19 lamps, 120V.
4-tier - 100 watt max.
3-tier - 75 watt max.
Fluorescent- (supplied)
13 watt quad tube
NPF 120v ballast

#### RAB 1000 FAX 888 RAB 1232 www.rabweb.com

#### Globes:

Threaded, gasketed globe protects against weather, garden sprinklers and insects. Clear glass GL100 globes standard for 4 Tier. Clear glass GL60 globes standard for 3 Tier. GL100 white globes also available for attractive appearance and glare reduction.

#### Housing:

Die cast aluminum housing with powder coat finish.

### Voltage:

120 volts AC

#### Patents:

The designs of RAB fixtures are protected under U.S. and international intellectual property laws.

#### Replacement Parts:

Part	Catalog #
Socket	SLL
Globe for 4 tier -clear	GL100 (clear)
Globe for 4 tier -white	GL100W
Globe for 3 tier - clear	GL60
Globe for 3 tier - white	GL60W

#### **Mounting Stem:**

Accessory 12" mounting stem with 1/2" threads on both ends available Part Catalog # 12" Stem Verde Green ST12VG 12" Stem Black ST12B

#### Mighty Post Mounting:

See page 110.

### Info Online 24/7

Spec Sheets

www.rabweb.com > click "PRODUCTS"

Rugged die cast aluminum housings. Threaded, gasketed clear glass globe for durable weatherproofing and easy relamping. 1" long, 1/2" threaded nipple included for easy mounting. 75 watt max. incandescent, 13 watt fluorescent.

## Three Tier DomeTop

Rugged die cast aluminum housings. Threaded, gasketed clear glass globe for durable weatherproofing and easy relamping. 1" long, 1/2" threaded nipple included for easy mounting. 75 -100 watt max., 13 watt fluorescent.

Finish:





Finish:

New!

Black Verde Green

Four Tier DomeTop



### **Mounting Options**



**Mighty Post** Mighty Post in lengths from 17" - 25" with a sturdy ground stabilizer



**Turtle Power Post** 19" Mighty Post with **Turtle In-Use Cover for** outlets & switches

### **Catalog Numbers**

Verde Green	Black
LLD3VG	LLD3B
LLD3VG/F13	LLD3B/F13

Verde Green	Black	
LLD4VG	LLD4B	
	LLD46	
LLD4VG/F13	LLD4B/F13	

### **Dimensions**



