

WYNBERG™

BRUSHED NICKEL WITH ALABASTER SWIRL GLASS,
OLDE BRONZE® OR TANNERY BRONZE™ FINISH
WITH UMBER GLASS



A | 1770 NI, TZ
Mini Chandelier



B | 3293 NI, NIA, OZ, OZU
Chandelier/Dinette



C | 2022 NI, TZ
Chandelier



D | 2093 NI, OZ
Chandelier

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Inverted Pendant or Semi Flush.



Shown as
Inverted Pendant - 15.25" H.



Shown as
Semi Flush - 13.5" H.

E | 3694 NI, OZ



F | 2693 NI, OZ
Mini Pendant



G | 2807 NI
Mini Pendant



H | 5294 NI, OZ
Wall Sconce

WYNBERG™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	1770	NI, TZ	(5) 60W (C)	17	12.75	87		25	72			Additional chain 2996 NI, TZ.
B	3293	NI, NIA, OZ, OZU	(3) 100W (M)	21.75	13.25	88	---	64	72	---	---	Ⓜ (9-13W CFL) Add. chain 2996 NI, NIA, OZ, OZU.
C	2022	NI, TZ	(5) 100W (M)	23	14	98	---	30	72	---	---	Add. chain 2996 NI, TZ. Satin Etched Seeded Glass.
D	2093	NI, OZ	(5) 100W (M)	24.5	13.75	88	---	25	72	---	---	Ⓜ (23-30W CFL) Add. chain 2996 NI, OZ.
E	3694	NI, OZ	(2) 100W (M)	15	15.25	90	---	30	72	---	---	Ⓜ (23-30W CFL) Add. chain 2996 NI, OZ.
F	2693	NI, OZ	(1) 100W (M)	6	12	44	90°	64	36	---	---	Add. stem 2999 (12") NI, OZ, and/or add. stem 2997 (24") NI, OZ. Satin Etched Glass. Height includes one 6" stem.
G	2807	NI	(1) 100W (M)	7	12.25	45	45°	68	---	---	---	Add. stem 2999 (12") NI and/or 2997 (24") NI. G Type lamp rec. Satin Etched Glass. Height includes one 6" stem.
H	5294	NI, OZ	(1) 100W (M)	6	7.5	---	---	---	---	8.5	3.5	Ⓜ May be installed with glass up or down. Satin Etched Glass.

Measurements shown in inches.

AB
Antique Brass

CH
Polished Chrome

NI
Brushed Nickel

OZ
Olde Bronze®

PB
Polished Brass

SC
Stucco White

TZ
Tannery Bronze™