

FLEXIBLE AND PORTABLE CORD

Bus Drop Cable

60°C - 600 Volt - UL



CONSTRUCTION	
Conductor	• Bare Stranded copper
Insulation	• Color coded Polyvinyl Chloride
Filler	• Suitable fillers are Used to make the cable round
Ground Wires	• Stranded, placed in spaces between individual Conductors
Jacket	• Gray PVC

Applications:

- Connection of stationary equipment
- PVC Jacket offers excellent resistance to grease, lubricants, oils and other fluids which are Used with various types of machinery

Standards:

- NEC 364-8, as branch wiring from busways
- UL Listed

COLOR CODE CHART	
Cond. #	Color
1	Red
2	Black
3	White
4	Blue

Part #	AWG	Conductors	Ground No. x AWG	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
A81403	14	3	3 X 18	.030"	.045"	.400"	111
A81404	14	4	3 X 18	.030"	.045"	.425"	140
A81203	12	3	3 X 16	.030"	.045"	.441"	150
A81204	12	4	3 X 16	.030"	.045"	.462"	159
A81003	10	3	3 X 14	.030"	.045"	.501"	224
A81004	10	4	3 X 14	.030"	.045"	.500"	238
A80803	8	3	3 X 14	.045"	.060"	.665"	334
A80804	8	4	3 X 14	.045"	.060"	.698"	379
A80603	6	3	3 X 14	.060"	.060"	.815"	483
A80604	6	4	3 X 14	.060"	.060"	.855"	571
A80403	4	3	3 X 12	.060"	.080"	.965"	721
A80404	4	4	3 X 12	.060"	.060"	.990"	841
A80203	2	3	3 X 12	.060"	.080"	1.10"	1034
A80204	2	4	3 X 12	.060"	.060"	1.28"	1130

*Fittings are available for these products.

Note: The data shown are approximate and subject to standard industry and manufacturer tolerances.