

# MIGHTYLITE

## HEAVY DUTY PORTABLE LED WORK LIGHTS



Super Bright



**Mightylites LED Job Light is compact and lightweight with an extremely tough polycarbonate casing. This work light utilizes the latest bright LEDs, making it perfect for use in all working environments.**

Manufactured out of polycarbonate with an aluminium substrate allowing it to withstand being drop tested from 2 meters. Adjustable light level on the rechargeable model (50% light level, switch on and off again to reduce to 25%).

### ✓ Easy to use

With LED lifespan of up to 50,000 hrs

### ✓ Uses the latest powerful LEDs

Generates 82 Lumens per Watt

### ✓ Weatherproof

IP65 rating & works in temperatures from -22°F to +176°F

### ✓ 5700K colour temperature

Gives wide, even spread of light

### ✓ Epistar LED array

Mono switch brightness control

### SPECIFICATIONS

Model No:	MITY13066/7/7AH	MITY65/6
Voltage:	110V Rechargeable	110V Mains Power
Lumens:	2300Lm	2300Lm
Wattage:	28W	28W
Power Factor:	>0.9	>0.9
Color Temp:	5700K	5700K
Efficiency:	<80%	<80%
Tripod Size:	40" x 27"	n/a
LED Array:	24 LEDs	24 LEDs
Cable Length:	n/a	2m
Lens:	Clear	Clear
Operating Temp:	-22°F to +176°F	-22°F to +176°F
IP Rating:	IP65	IP65
Product Size:	4.3"(h) x 6.3"(w) x 4.9"(d)	4.3"(h) x 6.3"(w) x 4.9"(d)

### BATTERY CHARGE for MITY13066/7/7AH

High Power 100%	Medium Power 50%	Low Power 25%
1.5hrs	3hrs	6hrs