



#### IDEACENTER BATH



#### THE SCOOP ON SCONCES

Sconces are the go-to choice for vanity lighting, producing a soft, warm radiance that evenly distributes the light on either side of your face, right where you need it most. As a general guideline, install at eye level or approximately 66" from the floor and typically 28"-40" apart, so the light beams overlap and produce an even glow.

An endless range of styles means you can allow your creativity to flow but pay special attention to the shades, which can influence both form and function. Look for light-filtering materials such as opal, etched linen, rain or piastra glass that provide a stylish solution to gently minimize any glare while still allowing the light to gently wash over the face and hair. When there are multiple sinks, be sure to provide each area with its own light source.

"SCONCE LIGHTING PROVIDES, IN MY VIEW, A FEELING OF INTIMACY AND WARMTH YOU SIMPLY CAN'T GET WITH OVERHEAD LIGHTING."

HEATHER GARRETT HEATHER GARRETT INTERIOR DESIGN DURHAM, NC

#### delightful DIMMERS

One of the top tips for maximizing your bathroom lighting is to install dimmers. Don't think of this as a luxury but a necessity! Often considered a designer's best friend, dimmers afford absolute control over the mood of the space, providing you the opportunity to morph the bathroom into a cocoon of relaxation or a brightly lit beacon for the morning rush.



#### styling a T R A D I T I O N A L B A T H







COLETTE 58783OZ, PAGE 492

#### *create a* CLASSIC OASIS

elegant lighting with details like handlathed finials and softly curved glass

#### brushed metallic hardware & accents

soft towels in layers of similar-hued solids, stitching and patterns

choose warm earthy elements such as rich wood and shell-toned stone

showcase classic feminine style with a stylistic display of signature scents and chic cosmetics

complement with candlelight for an added element of tranquility

#### "USE WHITE, PALE PINK AND BRASS FOR CASUAL GLAMOUR AND WARMTH."

SARAH SWANSON | SARAH SWANSON DESIGN CALGARY, ALBERTA

# the FAB FOUR

In order to function properly, bathrooms require a well-designed lighting plan, especially when you have multiple areas to light and numerous tasks to accomplish. Here's a quick primer on what you need to know to create a series of lighting layers, whether you are renovating or building from scratch. **Bottom line: one light source won't do** *in an environment this industrious!*  **TASK** Flattery is everything! To achieve the ultimate cross illumination, install vertical sconces on either side of the mirror. When side lighting is impractical due to space constraints, mount a fixture that is at least 24" wide over the mirror and about 75"-80" from the floor. Opt for LED bath lighting for maximum light output.

**AMBIENT** Overall illumination mimics natural light and is supplied by a central overhead installation. This fixture allows light to bounce off the ceiling and fill the perimeter of the room with a warm glow. Controlling the intensity of this light with a dimmer is suggested.

**ACCENT** For a sophisticated setting, choose accent lighting to illuminate the special details that relax and recharge you. Architectural elements or a cozy seating area will appear even more calming and spa-like when lit properly.

**DECORATIVE** For a dash of panache, get creative by hanging an eyecatching chandelier or pendant from the ceiling to create a living room-like feel, raising the luxury factor.

# WHO fairest

If traditional lighting applications in the bath aren't your cup of tea and you are looking to make a dramatic statement, try installing a fixture directly onto a mirror. "I actually have done this in my own home! I love it because of the impact the oversized mirror has on the overall space...and it's a fun take on a classic," says designer Sarah Swanson. Just because this is a more modern interpretation of bath lighting doesn't mean the style of the fixture or even the space itself has to reflect a contemporary look. Classic bath fixtures develop a dashing new edginess simply by placing them in a unique position.

> "It creates a wonderful glimmer when the light and fixture reflect back into the mirror."

PLANE

LISA MCDENNON I LISA MCDENNON DESIGN LAGUNA BEACH, CA

AL IC



# MAKE A *splash*

Whether it's a petite powder room or a massive master bath, consider the ultra-chic combination of decorative sconces with a chandelier to inject a dramatic element. Elements of elegance and personal panache shouldn't be relegated to the "main" rooms of your home: our bathrooms deserve design love too! Make this important sanctuary a place to relax, recharge and renew as you start and end your day bathed in luxurious lighting.

"I LOVE TAKING AN INTIMATE 'LIVING ROOM' APPROACH TO INTERIOR SPACES NOT USUALLY THOUGHT OF IN THAT WAY... YOUR CLOSET, YOUR HALLWAY, YOUR BATHROOM ARE ALL INTEGRATED INTO THE WAY YOU LIVE IN YOUR HOME. HOW YOU ILLUMINATE A BATHROOM CAN ENTIRELY DETERMINE ITS FEEL. MAKE EVERY INCH OF IT FEEL GREAT!"

HEATHER GARRETT HEATHER GARRETT INTERIOR DESIGN DURHAM, NC





**CHROME** conveys a crisp, clean freshness with a modern flair



NICKEL imparts a sense of traditional elegance

KATIA 50202CM PAGE 450 | REESE 56322AN PAGE 501 | CONGRESS 5002107 PAGE 484 | LANZA 5102RR PAGE 471



BRONZE makes a classic statement in bold, rich tones



BRASS is back, creating a warm, cozy modernism

<image><image>

THE MAKINGS OF A

sleek, minimalist lighting in chrome and brushed nickel *white and wood accessories textured knits and striped patterns* nostalgic accents with retro flair

# create the ultimate **MODERN** BATH ...





SEARCH FOR HINKLEY'S LED BATH OFFERINGS AND BE AT THE FOREFRONT OF CUTTING EDGE

DESIGN AND TECHNOLOGY



FIXTURES ABOVE, TOP TO BOTTOM: DOMINO 56422BN, PAGE 446 I CHLOE 52403BN, PAGE 430 LATITUDE 5650BN, PAGE 433

#### MOD-IFY YOUR BATH WITH...

bold lighting with unique glass and silhouettes geometric patterns • graphic botanicals a neutral palette of gray, white, cream and chrome naturally refined materials like slate, horn and agate rich woods • streamlined hardware



It goes without saying but the amount of light required in a bathroom is critical. We recommend a bare minimum of light output equivalent to 150 watts of incandescent light be used when lighting the vanity. This ensures that there

JULES 53240BN, PAGE 429

will be adequate light for grooming, applying makeup, shaving or helping the kids brush their teeth. If you are worried about too much wattage, simply switch to a lower wattage bulb or install a dimmer. Play it safe: once the light fixture is installed, it can be challenging to increase the amount of light you need but quite simple to reduce it, so plan ahead.



#### BATH COLLECTIONS

ABBIE	496	PINNACLE
ADELE	453	PLANTATION
AINSLEY	482	PLYMOUTH
ALICE	494	REESE
ANNETTE	486	SAN SIMEON
ASHLEY	487	SHELLY
AVON	479	SKYLAR
BIANCA	451	STOWE
BLAIRE	449	TAYLOR
BOLLA	461	TORY
BRANTLEY	504	UNION
BROOKE	502	WINTON
CASA	509	YORKTOWN
CHLOE	430	ZINA
CLAIRE	488	
COLETTE	490	
CONGRESS	483	
CONSTANCE	493	
DAPHNE	439	
DARBY	476	
DARIA	444	
DOMINO	446	
DUET	431	
FRANCOISE	512	
ISABELLA	510	
JORDAN	457	
JOSIE	460	
JULES	429	
KATIA	450	
KYLIE	464	
LANZA	470	
LATITUDE	433	
LOLA	448	
MASON	473	
MERIDIAN	474	
MILA	447	
MILEY	454	
MIRA FIZZ	428	
MIRAGE	443	
NOVA	442	
осно	466	
		I

# MIRA FIZZ<sup>\*\*</sup>

FINISH POLISHED CHROME GLASS ETCHED GLASS SHADE; CLEAR SEEDY GLASS PANEL

Mira Fizz is a sleek design in a brilliant Polished Chrome finish featuring bubble patterned shades lined with etched glass and a raceway back plate accented with clear seedy glass.

Mira Fizz sconces can be mounted horizontally or vertically.



THE Look for fixtures that can be mounted horizontally or vertically to best fit your space.



FR55452PCM 16¼" W, 6" H E



FR55452PCM (mounted vertically) E.



FR55450PCM 6" W, 16¼" H F



FR55453PCM 24¾" W, 6" H E.



FR55454PCM 331/2" W, 6" H E.

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	INV
FR55450PCM	1-60w G9*	31⁄2"	8¼"	6" W, 16¼" H	•
FR55452PCM	2-60w G9*	31⁄2"	3"	16¼" W, 6" H	•
FR55453PCM	3-60w G9*	31⁄2"	3"	24¾" W, 6" H	•
FR55454PCM	4-60w G9*	3½"	3"	33½" W, 6" H	•



BRUSHED NICKEL FINISH ETCHED OPAL GLASS

Jules is a chic design with a soft wave screen façade. The repeating stamped oval pattern in a Brushed Nickel finish is an excellent complement to today's transitional interiors.



53241 BN 53241 BN-GU24 53241 BN-LED 15" DIA., 8¼" H



53240 BN 5" W, 15½" H

53243 BN

231⁄2" W, 6" H



53240 BN (side view)



**53242 BN** 15½" W, 6" H



53244 BN 31¼" W, 6" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	INV
53240 BN	1-100w Med.					6"	7¾"	5" W, 151/2" H Back Plate	•
53241 BN	3-60w Med.	53241 BN-GU24	3-26w GU24	53241 BN-LED	1-32w FSI 200			5¾" Dia. Canopy	
53242 BN	2-100w Med.					5½"	2¾"	15½" W, 5" H Back Plate	•
53243 BN	3-100w Med.					5½"	2¾"	231/2" W, 5" H Back Plate	•
53244 BN	4-100w Med.					5½"	2¾"	31¼" W, 5" H Back Plate	•



FINISH BRUSHED NICKEL GLASS PIASTRA Chloe is a dramatic modern design with stunning Piastra glass as its focal point. A slender Brushed Nickel frame securely captures the glass allowing this versatile collection to be mounted horizontally or vertically.



52402 BN (mounted vertically)





52402 BN 17" W, 8" H



52403 BN 24¾" W, 8" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	INV
52400 BN	1-60w G9*	4"	4"	6½" W, 4¾" H	•
52402 BN	2-60w G9*	4"	4"	14¼" W, 4¾" H	•
52403 BN	3-60w G9*	4"	4"	22" W, 4¾" H	٠



BRUSHED NICKEL FINISH ETCHED LINEN AND RAIN GLASS

Duet is a unique, contemporary bath design that features bent linen glass that simultaneously frames and complements its clear rain glass. Both pieces of glass are secured to the raceway back plate with two Brushed Nickel knobs.

Duet sconces can be mounted horizontally or vertically.



ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
5612 BN	2-60w G9*	5612 BN-LED	2-6.6w LESG-60	5"	2¾"	12¼" W, 4½" H
5613 BN	3-60w G9*	5613 BN-LED	3-6.6w LESG-60	5"	2¾"	18" W, 4½" H
5614 BN	4-60w G9*	5614 BN-LED	4-6.6w LESG-60	5"	2¾"	24" W, 4½" H
5615 BN	5-60w G9*	5615 BN-LED	5-6.6w LESG-60	5"	2¾"	261⁄2" W, 41⁄2" H

# $U N I O N^{M}$

FINISHBRUSHED NICKELGLASSCLEAR INSIDE ETCHED

Union offers an understated yet clearly modern design of gracefully intersecting geometry. Its contemporary lines are softened by the U channel glass cradled in forged brackets.

Union sconces can be mounted horizontally or vertically.



52374 BN 34" W, 5¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
52370 BN	1-100w Med.	5½"	6"	5¾" W, 8" H
52372 BN	2-60w G9*	5½"	3"	10" W, 5¾" H
52373 BN	3-60w G9*	51/2"	3"	16¼" W, 5¾" H
52374 BN	4-60w G9*	51⁄2"	3"	26½" W, 5¾" H



BRUSHED NICKEL FINISH CLEAR BEVELED INSIDE ETCHED GLASS



5650 BN 5650 BN-LED

5" W, 8" H

😯 🔃 🕭

Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the subtle, split fork frames add understated architectural style.

5652 BN

5652 BN-LED 18" W, 5¾" H

⊗ 🔃 と





5654 BN

5654 BN-LED

26" W, 5¾" H







ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5650 BN	1-60w G9*	5650 BN-LED	1-6.6w LESG-60	4"	4"	5" W, 8" H	CM, OZ	•
5651 BN	2-100w Med.			5½"	10¾"	51⁄2" W, 211⁄2" H	CM, OZ	
5652 BN	2-60w G9*	5652 BN-LED	2-6.6w LESG-60	4"	3¼"	17" W, 4¾" H	CM, OZ	•
5654 BN	4-60w G9*	5654 BN-LED	4-6.6w LESG-60	4"	3¼"	25" W, 4¾" H	CM, OZ	•
5656 BN	6-60w G9*	5656 BN-LED	6-6.6w LESG-60	4"	3¼"	36¼" W, 4¾" H	CM, OZ	•

# L A T I T U D E<sup>™</sup>

FINISH CHROME GLASS CLEAR BEVELED INSIDE ETCHED



Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the subtle, split for  $% \mathcal{A}(\mathcal{A})$ frames add understated architectural style.



5651 CM 51/2" W, 211/2" H





26" W, 5¾" H 😯 🔃 🕭



😯 🔃 🕭

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5650 CM	1-60w G9*	5650 CM-LED	1-6.6w LESG-60	4"	4"	5" W, 8" H	BN, OZ	•
5651 CM	2-100w Med.			5½"	10¾"	51⁄2" W, 211⁄2" H	BN, OZ	
5652 CM	2-60w G9*	5652 CM-LED	2-6.6w LESG-60	4"	31⁄4"	17" W, 4¾" H	BN, OZ	•
5654 CM	4-60w G9*	5654 CM-LED	4-6.6w LESG-60	4"	31⁄4"	25" W, 4¾" H	BN, OZ	•
5656 CM	6-60w G9*	5656 CM-LED	6-6.6w LESG-60	4"	31⁄4"	36¼" W, 4¾" H	BN, OZ	•



OIL RUBBED BRONZE FINISH CLEAR BEVELED INSIDE ETCHED GLASS



Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the subtle, split fork frames add understated architectural style.





ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5650 OZ	1-60w G9*	5650 OZ-LED	1-6.6w LESG-60	4"	4"	5" W, 8" H	BN, CM	•
5651 OZ	2-100w Med.			5½"	10¾"	51⁄2" W, 211⁄2" H	BN, CM	
5652 OZ	2-60w G9*	5652 OZ-LED	2-6.6w LESG-60	4"	31⁄4"	17" W, 4¾" H	BN, CM	•
5654 OZ	4-60w G9*	5654 OZ-LED	4-6.6w LESG-60	4"	31⁄4"	25" W, 4¾" H	BN, CM	•
5656 OZ	6-60w G9*	5656 OZ-LED	6-6.6w LESG-60	4"	3¼"	36¼" W, 4¾" H	BN, CM	•

### WINTON™

FINISHBRUSHED NICKELGLASSINSIDE WHITE ETCHED PANELS

Winton is a retro-inspired design updated for today's contemporary decors. The heavy, rectangular tube construction has forged details and a unique fitted glass panel design.



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5232 BN	2-100w Med.	5232 BN-GU24	2-26w GU24	5232 BN-LED	2-15w LESM-100	5"	21⁄2"	14½" W, 4¾" H	СМ	•
5234 BN	4-100w Med.	5234 BN-GU24	4-26w GU24	5234 BN-LED	4-15w LESM-100	5"	21⁄2"	24¾" W, 4¾" H	СМ	•
5236 BN	6-100w Med.	5236 BN-GU24	6-26w GU24	5236 BN-LED	6-15w LESM-100	5"	21⁄2"	36" W, 4¾" H	СМ	•
5421 BN*	3-60w Med.	5421 BN-GU24	3-26w GU24	5421 BN-LED	1-32w FSI-200				BR, CM	

\*Recommended companion flush mount. For additional options, see pages 24-28.

### WINTON™

CHROME FINISH INSIDE WHITE ETCHED PANELS GLASS

Winton is a retro-inspired design updated for today's contemporary decors. The heavy, rectangular tube construction has forged details and a unique fitted glass panel design.



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5232 CM	2-100w Med.	5232 CM-GU24	2-26w GU24	5232 CM-LED	2-15w LESM-100	5"	21⁄2"	14½" W, 4¾" H	BN	•
5234 CM	4-100w Med.	5234 CM-GU24	4-26w GU24	5234 CM-LED	4-15w LESM-100	5"	21⁄2"	24¾" W, 4¾" H	BN	•
5236 CM	6-100w Med.	5236 CM-GU24	6-26w GU24	5236 CM-LED	6-15w LESM-100	5"	21⁄2"	36" W, 4¾" H	BN	•
5421 CM*	3-60w Med.	5421 CM-GU24	3-26w GU24	5421 CM-LED	1-32w FSI-200				BN, BR	

\*Recommended companion flush mount. For additional options, see pages 24-28.

















"For a relaxing spa-like effect, using light fixtures that provide indirect and diffused lighting is always the best. Find fixtures with frosted glass and up-lighting."

LISA MCDENNON I LISA MCDENNON DESIGN LAGUNA BEACH, CA

# IT'S A long STORY

With bathrooms expanding and gaining additional square footage, this trend has naturally influenced other important elements. Luxe vanities have become elongated to accommodate chic, narrow vessel sinks and extra-long tubs encourage spalike soaks. In these situations, it's wise to invest in lighting that is up to the task of illuminating larger areas. Look for extended bath bars (such as 40" in width) that can offer up to 6 lamps. This ensures your lighting plan is delivering the appropriate light output across a broader spectrum as well as meshing seamlessly with the overall design.

D A P H N E™

CHROME FINISH ETCHED BUBBLE ART GLASS

Daphne features contemporary pocket style bubble art glass set against a sleek raceway back plate in chic Chrome, Brushed Nickel or Brushed Bronze finishes. The etched bottom lens conceals the light source.







5923 CM 5923 CM-LED 24" W, 5" H











5925 CM 5925 CM-LED 40" W, 5" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRĂTED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5920 CM	1-75w Med.	5920 CM-GU24	1-18w GU24	5920 CM-LED	1-15w LESM-100	4"	41⁄2"	8½" W, 9" H	BN, BR
5922 CM	2-60w G9*			5922 CM-LED	2-6.6w LESG-60	3¾"	21⁄2"	16" W, 5" H	BN, BR
5923 CM	3-60w G9*			5923 CM-LED	3-6.6w LESG-60	3¾"	21⁄2"	24" W, 5" H	BN, BR
5924 CM	4-60w G9*			5924 CM-LED	4-6.6w LESG-60	3¾"	21⁄2"	32" W, 5" H	BN, BR
5925 CM	5-60w G9*			5925 CM-LED	5-6.6w LESG-60	3¾"	21⁄2"	40" W, 5" H	BN, BR



FINISHBRUSHED NICKELGLASSETCHED BUBBLE ART

Daphne features contemporary pocket style bubble art glass set against a sleek raceway back plate in chic Chrome, Brushed Nickel or Brushed Bronze finishes. The etched bottom lens conceals the light source.



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5920 BN	1-75w Med.	5920 BN-GU24	1-18w GU24	5920 BN-LED	1-15w LESM-100	4"	41⁄2"	81⁄2" W, 9" H	BR, CM
5922 BN	2-60w G9*			5922 BN-LED	2-6.6w LESG-60	3¾"	21⁄2"	16" W, 5" H	BR, CM
5923 BN	3-60w G9*			5923 BN-LED	3-6.6w LESG-60	3¾"	21⁄2"	24" W, 5" H	BR, CM
5924 BN	4-60w G9*			5924 BN-LED	4-6.6w LESG-60	3¾"	21/2"	32" W, 5" H	BR, CM
5925 BN	5-60w G9*			5925 BN-LED	5-6.6w LESG-60	3¾"	21⁄2"	40" W, 5" H	BR, CM



BRUSHED BRONZE FINISH ETCHED AMBER BUBBLE ART GLASS

Daphne features contemporary pocket style bubble art glass set against a sleek raceway back plate in chic Chrome, Brushed Nickel or Brushed Bronze finishes. The etched bottom lens conceals the light source.



5922 BR 5922 BR-LED 16" W, 5" H



5923 BR 5923 BR-LED 24" W, 5" H











5925 BR 5925 BR-LED 40" W, 5" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5920 BR	1-75w Med.	5920 BR-GU24	1-18w GU24	5920 BR-LED	1-15w LESM-100	4"	41⁄2"	81⁄2" W, 9" H	BN, CM
5922 BR	2-60w G9*			5922 BR-LED	2-6.6w LESG-60	3¾"	21⁄2"	16" W, 5" H	BN, CM
5923 BR	3-60w G9*			5923 BR-LED	3-6.6w LESG-60	3¾"	21⁄2"	24" W, 5" H	BN, CM
5924 BR	4-60w G9*			5924 BR-LED	4-6.6w LESG-60	3¾"	21⁄2"	32" W, 5" H	BN, CM
5925 BR	5-60w G9*			5925 BR-LED	5-6.6w LESG-60	3¾"	21⁄2"	40" W, 5" H	BN, CM



FINISH CHROME GLASS ETCHED OPAL Nova's sleek design centers on modern etched glass spheres bound by flowing strips of highly polished Chrome. The sleek mirror-like finish on the floating back plate reinforces its contemporary chic attitude.



50102 CM 12½" W, 5" H



50100 CM 5½" W, 9¾" H



50103 CM 19" W, 5" H



50104 CM 25½" W, 5" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	INV
50100 CM	1-60w G9*	4¾"	5"	4¾" W, 9" H	•
50102 CM	2-60w G9*	4¾"	2¾"	11¾" W, 4¼" H	•
50103 CM	3-60w G9*	4¾"	2¾"	18¼" W, 4¼" H	•
50104 CM	4-60w G9*	4¾"	2¾"	24¾" W, 4¼" H	•



BRUSHED NICKEL FINISH ETCHED OPAL GLASS

Mirage features a unique finish of Brushed Nickel and Chrome square accents that appear to float off the back plate between each cube shaped glass. Adding to its versatility, Mirage can be mounted in the horizontal or vertical position.



3852 BN 16" DIA., 5" H



53352 BN 15" W, 5" H



53350 BN 5" W, 10¼" H



53352 BN (mounted vertically)



53353 BN 24" W, 5" H



53354 BN 32" W, 5" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
53350 BN	1-60w G9*	4¾"	5¼"	5" W, 10¼" H		•
53352 BN	2-60w G9*	4¾"	21⁄2"	15" W, 5" H		•
53353 BN	3-60w G9*	4¾"	21⁄2"	24" W, 5" H		•
53354 BN	4-60w G9*	4¾"	21⁄2"	32" W, 5" H		•
3852 BN**	3-100w Med.				CM, OZ	

\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additonal options, see pages 24-28.





BRUSHED NICKEL FINISH ETCHED OPAL GLASS



Daria cast detail and glass profile.

Daria is a soft contemporary design, making this the perfect complement to any décor. The Brushed Nickel finish allows the prominent, etched opal glass shade to create a minimalist style statement.

Daria sconces can be mounted horizontally or vertically.





FINISH BRUSHED NICKEL GLASS ETCHED OPAL Domino creates a bold contemporary statement with minimalist rectangular shades softened by tapered edges. A floating Chrome layered "belt" sets off the Brushed Nickel back plate creating dimension and drama.



5421 CM 5421 CM-GU24 5421 CM-LED 17" DIA., 7" H



**56422 BN** 14" W, 4½" H



56423 BN 21½" W, 4½" H



56424 BN 29" W, 4½" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
56422 BN	2-60w G9*					4¾"	2¼"	13" W, 4½" H		•
56423 BN	3-60w G9*					4¾"	2¼"	201⁄2" W, 41⁄2" H		•
56424 BN	4-60w G9*					43⁄4"	2¼"	28" W, 4½" H		•
5421 CM	3-60w Cand.	5421 CM-GU24	2-26w GU24	5421 CM-LED	1-32w FSI-200				BN, BR	

# $MILA^{TM}$

BRUSHED NICKEL FINISH ETCHED OPAL GLASS



Top view of Mila glass showing oval shape.

Mila's modern design captivates with sleek symmetry as the elongated shades appear to float next to angled panel transitions to create a seamless form.





FINISHBRUSHED NICKELGLASS¼" THICK CLEAR INSIDE ETCHED

Lola's sleek contemporary design features thick ice glass that is cradled in a square cast bracket and floats off a clean sheet of Brushed Nickel.



5421 BN 5421 BN-GU24 5421 BN-LED 17" DIA., 7" H



**5772 BN** 14" W, 5½" H





**5770 BN** 5½" W, 10" H

**5773 BN** 23" W, 5½" H



**5774 BN** 32" W, 5½" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5770 BN	1-60w G9*					5¼"	5"	41⁄2" W, 9" H	
5772 BN	2-60w G9*					5¼"	2¾"	11" W, 4½" H	
5773 BN	3-60w G9*					5¼"	2¾"	20" W, 4½" H	
5774 BN	4-60w G9*					5¼"	2¾"	29¼" W, 4½" H	
5421 BN**	3-60w Cand.	5421 BN-GU24	3-26w GU24	5421 BN-LED	1-32w FSI-200				BR, CM

\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additional options, see pages 24-28.

Blaire's contemporary silhouette highlights the unique wedge shaped glass gracefully angled between the front support arm and back plate.

## BLAIRE™

BRUSHED NICKEL FINISH ETCHED OPAL GLASS



50652 BN 14" W, 6" H



5421 BN 5421 BN-GU24 5421 BN-LED 17" DIA., 7" H



50653 BN 21¼" W, 6" H



50650 BN 7" W, 6" H



50654 BN 28¼" W, 6" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
50650 BN	1-60w G9*					5¼"	3"	6¼" W, 6" H	
50652 BN	2-60w G9*					5¼"	3"	14" W, 6" H	
50653 BN	3-60w G9*					5¼"	3"	21¼" W, 6" H	
50654 BN	4-60w G9*					5¼"	3"	28¼" W, 6" H	
5421 BN**	3-60w Cand.	5421 BN-GU24	3-26w GU24	5421 BN-LED	1-32w FSI-200				BR, CM

\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additional options, see pages 24-28.



FINISH CHROME GLASS CLEAR AND ETCHED Katia's modern silhouette has a unique layered glass effect, with an etched shade captured inside clear. A floating Chrome back plate with chic, rounded edges completes the contemporary design.



50202 CM 18" W, 6¾" H



50200 CM 6" W, 6¾" H 50203 CM 24" W, 6¾" H



50204 CM 30" W, 6¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	INV
50200 CM	1-60w G9*	7¼"	4¼"	5¼" W, 4½" H	•
50202 CM	2-60w G9*	7¼"	4¼"	18" W, 4½" H	•
50203 CM	3-60w G9*	7¼"	4¼"	24" W, 4½" H	•
50204 CM	4-60w G9*	7¼"	4¼"	30" W, 4½" H	•



CHROME FINISH ETCHED OPAL GLASS

Bianca's mid-century modern style blends with contemporary elements. A clean cast metal arm supports the chic tapered etched opal glass shade while a raceway back plate in a sparkling finish adds to its sleek appeal.



55752 CM 14¾" W, 6" H





55750 CM 6¼" W, 7¼" H





55754 CM 313⁄4" W, 6" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	INV
55750 CM	1-60w G9*	7½"	3¾"	4½" W, 7¼" H	•
55752 CM	2-60w G9*	7½"	3¾	12¼" W, 4½" H	•
55753 CM	3-60w G9*	7½"	3¾"	21¼" W, 4½" H	•
55754 CM	4-60w G9*	7½"	3¾"	30" W, 4½" H	•

# $ZINA^{M}$

FINISH BRUSHED NICKEL GLASS CLEAR INSIDE ETCHED Zina features clean, sleek lines in a two-tone Brushed Nickel/Chrome finish. The petite, tapered ice glass adds another layer of modernity to complement this crisp design.



**51562 BN** 13" W, 7½" H



51560 BN 5" W, 7½" H



51563 BN 20¾" W, 7½" H



51564 BN 28¾" W, 7½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	INV
51560 BN	1-60w G9*	5¼"	5¼"	41⁄2" W, 41⁄2" H	•
51562 BN	2-60w G9*	51⁄4"	5¼"	121⁄2" W, 41⁄2" H	•
51563 BN	3-60w G9*	5¼"	5¼"	20½" W, 4½" H	•
51564 BN	4-60w G9*	5¼"	5¼"	28½" W, 4½" H	•



BRUSHED NICKEL FINISH ETCHED OPAL GLASS

Adele's transitional style features an eye-catching etched opal glass shade floating inside a unique double forged ring design. The smooth mounting plate adds an elegant finishing touch.



**52704 BN** 30½" W, 6½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
52700 BN	1-100w Med.	5"	41⁄2"	4¾" W, 7¾" H		•
52702 BN	2-100w Med.	5"	3¼"	7¾" W, 4¾" H		•
52703 BN	3-100w Med.	5"	3¼"	7¾" W, 4¾" H		•
52704 BN	4-100w Med.	5"	31⁄4"	7¾" W, 4¾" H		•
3852 BN*	3-100w Med.				CM, OZ	

\*Recommended companion flush mount. For additional options, see pages 24-28.



FINISH CHROME GLASS CASED OPAL Miley's chic design complements a variety of decors with its sleek lines and elegant glass shape. The cast stepped back plate and cast glass holders in Chrome or Brushed Nickel finishes add to its beauty.



BOLBS	G024 11 LW	G024 B0LB3		SOURCE	EAI.	OUILEI	BACKPLATE	FINISHES
1-60w G9*					5¼"	3¼"	4½" W, 6½" H	BN
2-60w G9*					51⁄2"	3¾"	6½" W, 4½" H	BN
3-60w G9*					51⁄2"	3¾"	6½" W, 4½" H	BN
4-60w G9*					51⁄2"	3¾"	61⁄2" W, 41⁄2" H	BN
3-60w Med.	5421 CM-GU24	3-26w GU24	5421 CM-LED	1-32w FSI-200				BN, BR
	2-60w G9* 3-60w G9* 4-60w G9*	1-60w G9* 2-60w G9* 3-60w G9* 4-60w G9*	1-60w G9* 2-60w G9* 3-60w G9* 4-60w G9*	1-60w G9*   2-60w G9*   3-60w G9*   4-60w G9*	1-60w G9*   2-60w G9*   3-60w G9*   4-60w G9*	1-60w G9* 5½"   2-60w G9* 5½"   3-60w G9* 5½"   4-60w G9* 5½"	1-60w G9* 5¼" 3¼"   2-60w G9* 5½" 3¾"   3-60w G9* 5½" 3¾"   4-60w G9* 5½" 3¾"	1-60w G9*   5¼"   3¼"   4½" W, 6½" H     2-60w G9*   5½"   3¾"   6½" W, 4½" H     3-60w G9*   5½"   3¾"   6½" W, 4½" H     4-60w G9*   5½"   3¾"   6½" W, 4½" H

\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additional options, see pages 24-28.

ITEM

# MILEY

BRUSHED NICKEL FINISH WHITE ETCHED GLASS

Miley's chic design complements a variety of decors with its sleek lines and elegant glass shape. The cast stepped back plate and cast glass holders in Chrome or Brushed Nickel finishes add to its beauty.







5052 BN 13" W, 6" H







5053 BN 21½" W, 6" H



5054 BN 30" W, 6" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5050 BN	1-60w G9*					5¼"	3¼"	4½" W, 6½" H	СМ
5052 BN	2-60w G9*					5½"	3¾"	6½" W, 4½" H	СМ
5053 BN	3-60w G9*					51⁄2"	3¾"	6½" W, 4½" H	СМ
5054 BN	4-60w G9*					51⁄2"	3¾"	6½" W, 4½" H	СМ
5421 BN**	3-60w Med.	5421 BN-GU24	3-26w GU24	5421 BN-LED	1-32w FSI-200				BR, CM

\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additional options, see pages 24-28.



FINISHBRUSHED NICKELGLASSETCHED OPAL

Skylar offers a soft contemporary style that easily complements any interior environment. A chic cast transition is accented by a mitered edge while the arm supports a prominent, softly rounded shade.



5421 BN 5421 BN-GU24 5421 BN-LED 17" DIA., 7" H



54132 BN 12½" W, 8" H



54130 BN 4½" W, 8" H



54133 BN 22" W, 8" H



**54134 BN** 30" W, 8" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
54130 BN	1-100w Med.					6"	41⁄2"	4½" W, 7¼" H		•
54132 BN	2-100w Med.					6"	5¾"	12¼" W, 4½" H		•
54133 BN	3-100w Med.					6"	5¾"	22" W, 4½" H		•
54134 BN	4-100w Med.					6"	5¾"	30" W, 4½" H		•
5421 BN*	2-60w Med.	5421 BN-GU24	3-26w GU24	5421 BN-LED	1-32w FSI-200				BR, CM	



BRUSHED NICKEL FINISH ETCHED OPAL GLASS

Jordan's simple, soft contemporary lines of Brushed Nickel allow the unique glass to be the focus. The conical fitters are perched upon cast metal rectangular brackets, while the tapered etched opal shades transition from round to a soft square.



**51354 BN** 29½" W, 6¾" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
51350 BN	1-100w Med.					6"	4"	4½" W, 7" H		•
51352 BN	2-100w Med.					6¼"	41⁄2"	7" W, 4½" H		•
51353 BN	3-100w Med.					6¼"	41⁄2"	7" W, 4½" H		•
51354 BN	4-100w Med.					6¼"	41⁄2"	7" W, 4½" H		•
5421 BN*	2-60w Med.	5421 BN-GU24	3-26w GU24	5421 BN-LED	1-32w FSI-200				BR, CM	

### $\mathsf{PINNACLE}^{\scriptscriptstyle{\mathrm{M}}}$





Pinnacle mounting bars are curved in shape.

Pinnacle features softly curved mounting bars with cast square decorative medallions in a Chrome finish with Antique Nickel accents and etched opal glass.



5255 CM 37" W, 8" H

5250 CM 5" W, 9" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5250 CM	1-100w Med.	7"	41⁄2"	4½" W, 9" H	AN
5251 CM	3-60w Med.				AN
5252 CM	2-100w Med.	6"	5¾"	7" W, 4½" H	AN
5253 CM	3-100w Med.	7"	5¾"	9" W, 4½" H	AN
5254 CM	4-100w Med.	7"	5¾"	9" W, 4½" H	AN
5255 CM	5-100w Med.	7"	5¾"	9" W, 4½" H	AN

### $\mathsf{PINNACLE}^{\scriptscriptstyle{\mathsf{M}}}$

ANTIQUE NICKEL FINISH CLEAR ETCHED GLASS



Pinnacle mounting bars are curved in shape.


Pinnacle features softly curved mounting bars with cast square decorative medallions in an Antique Nickel finish with clear etched glass.



©2015 Hinkley Lighting, Inc. | hinkleylighting.com | BATH | **459** 

# J O S I E™

FINISH BRUSHED NICKEL GLASS ETCHED OPAL Josie's delicate transitional style features a one inch rectangular wave element as the centerpiece of the design, along with etched opal glass that transitions from round on the bottom to square on the top. The Brushed Nickel finish and invisi-mount raceway back plate add to its clean look.



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5370 BN	1-100w Med.					6¼"	5"	4½" W, 7" H		•
5372 BN	2-100w Med.					6"	5"	7" W, 4½" H		•
5373 BN	3-100w Med.					6"	5¾"	18" W, 4½" H		•
5375 BN	5-100w Med.					6"	6¼"	18" W, 4½" H		•
5551 BN*	2-60w Med.	5551 BN-GU24	2-26w GU24	5551 BN-LED	1-32w FSI-200				BR, CM	



BRUSHED NICKEL FINISH ETCHED OPAL GLASS



Bolla Chandeliers, pages 106-119

The graceful lines of Bolla create a soft elegance, while heavy cast ball transition detail add to its innovative style. The strong proportions of the design contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Outdoor, pages 654-657



5894 BN-LED

4-15w LESM-100

6¾"

6¾"

61⁄2"

61⁄2"

4-18w GU24

5894 BN

5895 BN

4-100w Med.

5-100w Med.

5894 BN-GU24

181/4" W, 41/2" H Back Plate OB, OB-OPAL

OB, OB-OPAL

9¼" W, 4½" H Back Plate




FINISH OLDE BRONZE GLASS ETCHED OPAL



The graceful lines of Bolla create a soft elegance, while heavy cast ball transition detail add to its innovative style. The strong proportions of the design contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Outdoor, pages 654-657



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	SOURCE	EXT.	OUTLET	BACK PLATE/CANOPY	FINISHES
4650 OB-OPAL	1-100w Med.	4650 OB-OP-GU24	1-18w GU24	4650 OB-OP-LED	1-15w LESM-100	8¾"	31⁄2"	6" W, 7½" H Back Plate	BN, OB
4660 OB-OPAL	2-75w Med.	4660 OB-OP-GU24	2-18w GU24	4660 OB-OP-LED	1-32w FSI-200			5" Dia. Canopy	BN, OB
5892 OB-OPAL	2-100w Med.	5892 OB-OP-GU24	2-18w GU24	5892 OB-OP-LED	2-15w LESM-100	6¾"	61⁄2"	9¼" W, 4½" H Back Plate	BN, OB
5893 OB-OPAL	3-100w Med.	5893 OB-OP-GU24	3-18w GU24	5893 OB-OP-LED	3-15w LESM-100	6¾"	61⁄2"	9¼" W, 4½" H Back Plate	BN, OB
5894 OB-OPAL	4-100w Med.	5894 OB-OP-GU24	4-18w GU24	5894 OB-OP-LED	4-15w LESM-100	6¾"	61⁄2"	9¼" W, 4½" H Back Plate	BN, OB
5895 OB-OPAL	5-100w Med.					6¾"	6½"	18¼" W, 4½" H Back Plate	BN, OB



OLDE BRONZE FINISH LIGHT AMBER SEEDY GLASS



The graceful lines of Bolla create a soft elegance, while heavy cast ball transition detail add to its innovative style. The strong proportions of the design contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Outdoor, pages 654-657





FINISH CHROME GLASS ETCHED OPAL Kylie's confident, transitional style features a crisp, clean aesthetic with bold cast zinc details including half-round end caps and stepped, arced cups that support the sleek, etched opal glass shade.



**3903 CM** 16½" DIA., 6¼" H



55212 CM 14¼" W, 6¼" H



55210 CM 5¼" W, 8½" H



55213 CM 23" W, 6¼" H



55214 CM 31¾" W, 6¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
55210 CM	1-100w Med.	6"	4¼"	4½" W, 6¾" H	BN	•
55212 CM	2-100w Med.	6"	3¾"	6¾" W, 4¼" H	BN	•
55213 CM	3-100w Med.	6"	3¾"	6¾" W, 4¼" H	BN	•
55214 CM	4-100w Med.	6"	3¾"	6¾" W, 4¼" H	BN	•
3903 CM*	3-60w Med.				AN, KZ	

## $K Y L I E^{TM}$

BRUSHED NICKEL FINISH ETCHED OPAL GLASS

Kylie's confident, transitional style features a crisp, clean aesthetic with bold cast zinc details including half-round end caps and stepped, arced cups that support the sleek, etched opal glass shade.



55212 BN 14¼" W, 6¼" H



55213 BN 23" W, 6¼" H



55210 BN 5¼" W, 8½" H



55214 BN 31¾" W, 6¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	<b>BACK PLATE</b>	ADDITIONAL FINISHES	INV
55210 BN	1-100w Med.	6"	41⁄4"	4¼" W, 6¾" H	СМ	•
55212 BN	2-100w Med.	6"	3¾"	6¾" W, 4¼" H	СМ	•
55213 BN	3-100w Med.	6"	3¾"	6¾" W, 4¼" H	CM	•
55214 BN	4-100w Med.	6"	3¾"	6¾" W, 4¼" H	CM	•

For flush mount options, see pages 24-28.



FINISH CHROME GLASS ETCHED OPAL Ocho's clean, transitional design complements a variety of interiors. Its sophisticated, oval shaped glass in etched opal is complemented by the elegant Chrome finish.



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5420 CM	1-60w G9*					5¼"	4¼"	6" W, 5¼" H		•
5421 CM	3-60w Med.	5421 CM-GU24	3-26w GU24	5421 CM-LED	1-32w FSI-200				BN, BR	
5422 CM	2-60w G9*					5¼"	41⁄2"	6" W, 5¼" H		•
5423 CM	3-60w G9*					5¼"	41⁄2"	6" W, 5¼" H		•
5424 CM	4-60w G9*					5¼"	41⁄2"	6" W, 5¼" H		•

\*G9 halogen bulbs included.



CHROME FINISH ETCHED WHITE GLASS

Taylor's modern silhouette highlights its tapered rectangular etched white glass in Chrome, Brushed Nickel or Buckeye Bronze finishes.





5020 CM 7¾" W, 6" H

5025 CM 45" W, 7" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5020 CM	1-60w G9*					5¼"	3¾"	7¾" W, 4¾" H	BN, KZ
5022 CM	2-60w G9*					5½"	3¾"	7¾" W, 4¾" H	BN, KZ
5023 CM	3-60w G9*					5½"	3¾"	7¾" W, 4¾" H	BN, KZ
5024 CM	4-60w G9*					5½"	3¾"	7¾" W, 4¾" H	BN, KZ
5025 CM	5-60w G9*					5½"	5"	12" W, 4¾" H	BN, KZ
5551 CM**	2-60w Med.	5551 CM-GU24	4 2-26w GU24	5551 CM-LED	1-32w FSI-200				BN, BR

\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additional options, see pages 24-28.



FINISH BRUSHED NICKEL GLASS ETCHED WHITE Taylor's modern silhouette highlights its tapered rectangular etched white glass in Chrome, Brushed Nickel or Buckeye Bronze finishes.



\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additional options, see pages 24-28.



BUCKEYE BRONZE FINISH ETCHED WHITE GLASS

Taylor's modern silhouette highlights its tapered rectangular etched white glass in Chrome, Brushed Nickel or Buckeye Bronze finishes.



5022 KZ 18¾" W, 6" H



5023 KZ 27½" W, 6" H



5024 KZ 36¼" W, 6" H



5020 KZ 7¾" W, 6" H



5025 KZ 45" W, 7" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5020 KZ	1-60w G9*	51⁄4"	3¾"	7¾" W, 4¾" H	BN, CM
5022 KZ	2-60w G9*	51⁄2"	3¾"	7¾" W, 4¾" H	BN, CM
5023 KZ	3-60w G9*	51⁄2"	3¾"	7¾" W, 4¾" H	BN, CM
5024 KZ	4-60w G9*	51⁄2"	3¾"	7¾" W, 4¾" H	BN, CM
5025 KZ	5-60w G9*	51⁄2"	5"	12" W, 4¾" H	BN, CM

\*G9 halogen bulbs included. For flush mount options, see pages 24-28.



FINISH ANTIQUE NICKEL GLASS ETCHED OPAL



Lanza features contemporary styling with geometric patterns that are emphasized in Antique Nickel, Brushed Bronze and Buckeye Bronze finishes. The elongated oval, etched opal glass reinforces its sleek design.




\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additional options, see pages 24-28.



BRUSHED BRONZE FINISH ETCHED OPAL GLASS



Lanza features contemporary styling with geometric patterns that are emphasized in Antique Nickel, Brushed Bronze and Buckeye Bronze finishes. The elongated oval, etched opal glass reinforces its sleek design.



43" W, 6¾" H

INTEGRATED LED LIGHT SOURCE TOP TO OUTLET ADDITIONAL FINISHES INV LED ITEM ITEM BULBS GU24 ITEM GU24 BULBS BACK PLATE EXT. 5100 BR 1-60w G9\* 5100 BR-LED 1-6.6w LESG-60 5" 6½" 4¾" W, 12" H BN, KZ 2-60w G9\* 9" W, 4¾" H 5102 BR 5" 4" BN, KZ • 5103 BR 3-60w G9\* 5103 BR-LED 3-6.6w LESG-60 5" 4" 12" W, 43/4" H BN, KZ • 5104 BR 4-60w G9\* 5" 4" 12" W, 4¾" H • BN, KZ 5105 BR 5-60w G9\* 5" 4" 12" W, 4¾" H BN, KZ • 1-32w FSI-200 BN, CM 5421 BR\*\* 3-60w Med. 5421 BR-GU24 3-26w GU24 5421 BR-LED

\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additional options, see pages 24-28.



FINISH BUCKEYE BRONZE GLASS ETCHED OPAL



Lanza features contemporary styling with geometric patterns that are emphasized in Antique Nickel, Brushed Bronze and Buckeye Bronze finishes. The elongated oval, etched opal glass reinforces its sleek design.



5100 KZ 7¼" W, 12" H



5103 KZ 25" W, 6¾" H



**5102 KZ** 16½" W, 6¾" H



5104 KZ 34" W, 6¾" H



5105 KZ 43" W, 6¾" H


ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5100 KZ	1-60w G9*	5"	6½"	4¾" W, 12" H	AN, BR	
5102 KZ	2-60w G9*	5"	4"	9" W, 4¾" H	AN, BR	•
5103 KZ	3-60w G9*	5"	4"	12" W, 4¾" H	AN, BR	•
5104 KZ	4-60w G9*	5"	4"	12" W, 4¾" H	AN, BR	•
5105 KZ	5-60w G9*	5"	4"	12" W, 4¾" H	AN, BR	•

\*G9 halogen bulbs included. For flush mount options, see pages 24-28.



TEXTURED BLACK FINISH ETCHED OPAL GLASS

Mason has a bold, masculine feel with a strong double line decorative accent in forged iron construction. The rectangular glass appears to be floating and adds a softness to the design with rounded edges.



251/2" W, 41/2" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5692 TB	2-60w G9*			5½"	2¼"	7¼" W, 4½" H		•
5693 TB	3-60w G9*			5½"	2¼"	7¼" W, 4½" H		•
4631 TB**	3-60w Med.	4631 TB-LED	1-32w FSI-200				BN, OZ	

\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additional options, see pages 24-28.

### MERIDIAN<sup>™</sup>

FINISH CHROME GLASS THICK FACETED CLEAR INSIDE ETCHED



Chandeliers,



Top view of Meridian glass showing 1/2" pages 232-234 thickness.

Meridian features minimal transitional styling with clean lines and low-profile faceted  $^{1\!/\!2"}$ thick glass. Over scaled barrel knob detailing completes this simplistic design.



29" W, 6" H  $\bigcirc \mathbb{Z}$ 

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	ADDITIONAL FINISHES
3871 CM	3-60w G9*					5½" Dia. Canopy	BN
5590 CM	1-60w G9*	5590 CM-LED	1-6.6w LESG-60	6½"	4"	41/2" W, 8" H Back Plate	BN
5592 CM	2-60w G9*	5592 CM-LED	2-6.6w LESG-60	6¼"	3¾"	8" W, 41/2" H Back Plate	BN
5593 CM	3-60w G9*	5593 CM-LED	3-6.6w LESG-60	6¼"	3¾"	8" W, 41/2" H Back Plate	BN
5594 CM	4-60w G9*	5594 CM-LED	4-6.6w LESG-60	6¼"	3¾"	8" W, 41/2" H Back Plate	BN

\*G9 halogen bulbs included. For flush mount options, see pages 24-28.



BRUSHED NICKEL FINISH THICK FACETED CLEAR INSIDE ETCHED GLASS



Meridian features minimal transitional styling with clean lines and low-profile faceted ½" thick glass. Over scaled barrel knob detailing completes this simplistic design.

Meridian Chandeliers, pages 232-234

Top view of Meridian glass showing ½" C thickness. pa



5592 BN 5592 BN-LED 14" W, 6" H



3871 BN

16" DIA., 12¼" H

5593 BN 5593 BN-LED 21" W, 6" H



5590 BN 5590 BN-LED 5" W, 8" H



5594 BN 5594 BN-LED 29" W, 6" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	ADDITIONAL FINISHES
3871 BN	3-60w G9*					5½" Dia. Canopy	СМ
5590 BN	1-60w G9*	5590 BN-LED	1-6.6w LESG-60	6½"	4"	41/2" W, 8" H Back Plate	СМ
5592 BN	2-60w G9*	5592 BN-LED	2-6.6w LESG-60	6¼"	3¾"	8" W, 41/2" H Back Plate	СМ
5593 BN	3-60w G9*	5593 BN-LED	3-6.6w LESG-60	6¼"	3¾"	8" W, 41/2" H Back Plate	СМ
5594 BN	4-60w G9*	5594 BN-LED	4-6.6w LESG-60	61⁄4"	3¾"	8" W, 4½" H Back Plate	СМ

\*G9 halogen bulbs included. For flush mount options, see pages 24-28.



FINISH BRUSHED CARAMEL GLASS ETCHED OPAL Darby's traditional flair will complement any décor with a precision die-cast zinc back plate, arm, cup and end caps in a flawless Polished Nickel or Brushed Caramel finish. A thin reeded "bar" effortlessly balances tapered square etched opal shades for an alluring effect.



53013 BC 23" W, 8" H



53012 BC 14" W, 8" H



53014 BC 32" W, 8" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
53012 BC	2-100w Med.	5"	5½"	7½" W, 5" H	PN	•
53013 BC	3-100w Med.	5"	51/2"	71⁄2" W, 5" H	PN	•
53014 BC	4-100w Med.	5"	5½"	7½" W, 5" H	PN	•

For flush mount options, see pages 24-28.



POLISHED NICKEL FINISH ETCHED OPAL GLASS

Darby's traditional flair will complement any décor with a precision die-cast zinc back plate, arm, cup and end caps in a flawless Polished Nickel or Brushed Caramel finish. A thin reeded "bar" effortlessly balances tapered square etched opal shades for an alluring effect.



53014 PN 32" W, 8" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
53012 PN	2-100w Med.	5"	51⁄2"	7½" W, 5" H	BC	•
53013 PN	3-100w Med.	5"	5½"	7½" W, 5" H	BC	•
53014 PN	4-100w Med.	5"	5½"	7½" W, 5" H	BC	•

For flush mount options, see pages 24-28.



FINISH BRUSHED NICKEL GLASS ETCHED OPAL



Tory features soft rectangular tapered glass. Tory's unique tiered design features a softly bent bar with the soothing contours repeated in a graphic wave pattern embossed on the glass.



5204 BN 32¾" W, 7¾" H

INTEGRATED LED LIGHT SOURCE TOP TO OUTLET ADDITIONAL FINISHES ITEM BULBS GU24 ITEM LED ITEM BACK PLATE GU24 BULBS EXT. 1-60w G9\* 4¾" 41⁄2" W, 91⁄4" H 5200 BN 4¾" 5202 BN 2-60w G9\* 4¾" 41⁄2" 9¼" W, 4½" H 5203 BN 3-60w G9\* 4¾" 41⁄2" 9¼" W, 4½" H 5204 BN 4-60w G9\* 4¾" 41⁄2" 9¼" W, 4½" H 5551 BN\*\* 5551 BN-GU24 2-26w GU24 5551 BN-LED 1-32w FSI-200 BR, CM 2-60w Med.

\*G9 halogen bulbs included. \*\*Recommended companion flush mount. For additional options, see pages 24-28.

Avon's updated traditional style features a clean, minimalist design with cast detailing. Available in Chrome, Brushed Nickel and Buckeye Bronze finishes.

### $AVON^{M}$

CHROME FINISH CASED OPAL GLASS



48" W, 8" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5550 CM	1-100w Med.	5550 CM-GU24	1-18w GU24	5550 CM-LED	1-15w LESM-100	6¼"	5¼"	7¼" W, 4½"	BN, KZ
5551 CM	2-60w Med.	5551 CM- GU24	2-26w GU24	5551 CM-LED	1-32w FSI-200				BN, BR
5552 CM	2-100w Med.	5552 CM-GU24	2-18w GU24	5552 CM-LED	2-15w LESM-100	6¼"	5¾"	7¼" W, 4½"	BN, KZ
5553 CM	3-100w Med.	5553 CM- GU24	3-18w GU24	5553 CM-LED	3-15w LESM-100	6¼"	5¾"	7¼" W, 4½"	BN, KZ
5554 CM	4-100w Med.	5554 CM-GU24	4-18w GU24	5554 CM-LED	4-15w LESM-100	6¼"	5¾"	7¼" W, 4½"	BN, KZ
5555 CM	5-100w Med.					6¼"	5¾"	18¼" W, 4½"	BN, KZ
5556 CM	6-100w Med.					6¼"	5¾"	18¼" W, 4½"	BN, KZ



FINISH BRUSHED NICKEL GLASS ETCHED OPAL Avon's updated traditional style features a clean, minimalist design with cast detailing. Available in Chrome, Brushed Nickel and Buckeye Bronze finishes.



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5550 BN	1-100w Med.	5550 BN-GU24	1-18w GU24	5550 BN-LED	1-15w LESM-100	6¼"	5¼"	7¼" W, 4½"	CM, KZ
5551 BN	2-60w Med.	5551 BN- GU24	2-26w GU24	5551 BN-LED	1-32w FSI-200				CM, BR
5552 BN	2-100w Med.	5552 BN-GU24	2-18w GU24	5552 BN-LED	2-15w LESM-100	6¼"	5¾"	7¼" W, 4½"	CM, KZ
5553 BN	3-100w Med.	5553 BN- GU24	3-18w GU24	5553 BN-LED	3-15w LESM-100	6¼"	5¾"	7¼" W, 4½"	CM, KZ
5554 BN	4-100w Med.	5554 BN-GU24	4-18w GU24	5554 BN-LED	4-15w LESM-100	6¼"	5¾"	7¼" W, 4½"	CM, KZ
5555 BN	5-100w Med.					6¼"	5¾"	18¼" W, 4½"	CM, KZ
5556 BN	6-100w Med.					6¼"	5¾"	18¼" W, 4½"	CM, KZ

Avon's updated traditional style features a clean, minimalist design with cast detailing. Available in Chrome, Brushed Nickel and Buckeye Bronze finishes.



BUCKEYE BRONZE FINISH ETCHED OPAL GLASS





5556 KZ 48" W, 8" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5550 KZ	1-100w Med.	5550 KZ-GU24	1-18w GU24	5550 KZ-LED	1-15w LESM-100	6¼"	5¼"	7¼" W, 4½"	BN, CM
5552 KZ	2-100w Med.	5552 KZ-GU24	2-18w GU24	5552 KZ-LED	2-15w LESM-100	6¼"	5¾"	7¼" W, 4½"	CM, KZ
5553 KZ	3-100w Med.	5553 KZ- GU24	3-18w GU24	5553 KZ-LED	3-15w LESM-100	6¼"	5¾"	7¼" W, 4½"	CM, KZ
5554 KZ	4-100w Med.	5554 KZ-GU24	4-18w GU24	5554 KZ-LED	4-15w LESM-100	6¼"	5¾"	7¼" W, 4½"	CM, KZ
5555 KZ	5-100w Med.					6¼"	5¾"	18¼" W, 4½"	CM, KZ
5556 KZ	6-100w Med.					6¼"	5¾"	18¼" W, 4½"	CM, KZ

For flush mount options, see pages 24-28.



FINISH BRUSHED NICKEL GLASS CASED OPAL Ainsley's traditional silhouette charms with distinctive details like retro-modern turned cups. Cased opal glass shades are accented with an elegant Brushed Nickel trim ring.



33" W, 9¼" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
56550 BN	1-100w Med.					8¼"	4"	6" Dia.	
56552 BN	2-100w Med.					8¼"	5"	6" Dia.	
56553 BN	3-100w Med.					81⁄4"	5"	6" Dia.	
56554 BN	4-100w Med.					81⁄4"	5"	6" Dia.	
5551 BN**	2-60w Med.	5551 BN-GU24	2-26w GU24	5551 BN-LED	1-32w FSI-200				BR, CM

 $C \cap N G R E S S^{*}$ 

ANTIQUE NICKEL, CHROME, OIL RUBBED BRONZE FINISH METAL SHADE



Congress Chandeliers, pages 263-273

Congress is a traditional design that combines both hip and historical elements. This chic-retro glass, mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.



50038 AN (shown) 50038 CM 50038 OZ 31" W, 10½" H



3178 AN (shown) 3178 CM 3178 OZ 9¾" W, 12¾" H



50038 AN 50038 CM (shown) 50038 OZ 31" W, 10½" H

50028 AN

50028 CM

50028 OZ (shown)


21" W, 101/2" H



50028 AN 50028 CM (shown) 50028 OZ 21" W, 10½" H



3178 AN 3178 CM 3178 OZ (shown) 9¾" W, 12¾" H



For flush mount options, see pages 24-28.

# $C \cap N G R E S S^{*}$

FINISH ANTIQUE NICKEL, CHROME, OIL RUBBED BRONZE GLASS CLEAR OR ETCHED OPAL Congress Chandeliers, pages 263-273

Congress is a traditional design that combines both hip and historical elements. This chic retro glass, mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

### CHOOSE A STYLE 2 CHOOSE A FINISH 3 CHOOSE A GLASS

3 FINISH OPTIONS • 4 CLEAR GLASS OPTIONS • 4 ETCHED OPAL GLASS OPTIONS 3 METAL SHADE OPTIONS (P. 483)



3174 AN 3174 CM (shown) 3174 OZ 17" W, 13½" H 50030 AN 50030 CM 50030 OZ (shown) 29½" W, 9¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	INV
3174 AN, CM, OZ	1-100w Med.	9¼"	4¾"	4¾" Dia.	
50021 AN, CM, OZ	2-100w Med.	10¼"	31⁄2"	4¾" Dia.	•
50022 AN, CM, OZ	2-100w Med.	9¾"	31⁄2"	4¾" Dia.	•
50030 AN, CM, OZ	3-100w Med.	9¾"	31⁄2"	4¾" Dia.	•

For flush mount options, see pages 24-28.

### **CONGRESS ORDERING GUIDE** SCONCES, 2 LIGHT & 3 LIGHT BATH

Outfit your space in retro-chic style! Use the chart below to determine item numbers and specs for each Congress sconce, two light and three light with clear or etched opal glass in three finish options.

0			CLEAR	GLASS		ETCHED OPAL GLASS			
choose a style	FINISH	Teardrop	Globe	Hurricane	Retro	Teardrop	Globe	Hurricane	Retro
2 choose a finish		~		_					
3 choose a glass									

SINGLE LIGHT SCONCE

Antique Nickel	<b>3177 AN</b> 6" W 14" H	<b>3174 AN</b> 7" W 13½" H	<b>3171 AN</b> 8¾" W 13" H	<b>3176 AN</b> 8" W 11¼" H	<b>3172 AN</b> 6" W 14" H	<b>3173 AN</b> 7" W 13½" H	<b>3175 AN</b> 8¾" W 13" H	<b>3170 AN</b> 8" W 11¼" H
Chrome	<b>3177 CM</b> 6" W 14" H	<b>3174 CM</b> 7" W 13½" H	<b>3171 CM</b> 8¾" W 13" H	<b>3176 CM</b> 8" W 11¼" H	3172 CM 6" W 14" H	<b>3173 CM</b> 7" W 13½" H	<b>3175 CM</b> 8¾" W 13" H	<b>3170 CM</b> 8" W 11¼" H
Oil Rubbed Bronze	<b>3177 OZ</b> 6" W 14" H	<b>3174 OZ</b> 7" W 13½" H	<b>3171 OZ</b> 8¾" W 13" H	<b>3176 OZ</b> 8" W 11¼" H	<b>3172 OZ</b> 6" W 14" H	<b>3173 OZ</b> 7" W 13½" H	<b>3175 OZ</b> 8¾" W 13" H	<b>3170 OZ</b> 8" W 11¼" H

#### TWO LIGHT BAR

	Antique Nickel	<b>50027 AN</b> 19¼" W 12" H	<b>50024 AN</b> 19¼" W 11½" H	<b>50021 AN</b> 20" W 11" H	50026 AN 19¼" W 9¼" H	<b>50022 AN</b> 19¼" W 12" H	50023 AN 19¼" W 11½" H	<b>50025 AN</b> 20" W 11" H	50020 AN 19¼" W 9¼" H
	Chrome	50027 CM 19¼" W 12" H	<b>50024 CM</b> 19¼" W 11½" H	50021 CM 20" W 11" H	50026 CM 19¼" W 9¼" H	50022 CM 19¼" W 12" H	50023 CM 19¼" W 11½" H	50025 CM 20" W 11" H	50020 CM 19¼" W 9¼" H
- <del>↓ ● ↓</del>	Oil Rubbed Bronze	50027 OZ 19¼" W 12" H	50024 OZ 19¼" W 11½" H	50021 OZ 20" W 11" H	50026 OZ 19¼" W 9¼" H	50022 OZ 19¼" W 12" H	50023 OZ 19¼" W 11½" H	<b>50025 OZ</b> 20" W 11" H	50020 OZ 19¼" W 9¼" H

### THREE LIGHT BAR

	Antique Nickel	50037 AN 29½" W 12" H	50034 AN 29½" W 11½" H	<b>50031 AN</b> 30" W 11" H	50036 AN 29½" W 9¼" H	50032 AN 29½" W 12" H	50033 AN 29½" W 11½" H	<b>50035 AN</b> 30" W 11" H	50030 AN 29½" W 9¼" H
	Chrome	50037 CM 29½" W 12" H	50034 CM 29½" W 11½" H	50031 CM 30" W 11" H	50036 CM 29½" W 9¼" H	50032 CM 29½" W 12" H	50033 CM 29½" W 11½" H	<b>50035 CM</b> 30" W 11" H	50030 CM 29½" W 9¼" H
- <b>+</b> - <b>+</b> -	Oil Rubbed Bronze	50037 OZ 29½" W 12" H	50034 OZ 29½" W 11½" H	50031 OZ 30" W 11" H	50036 OZ 29½" W 9¼" H	50032 OZ 29½" W 12" H	50033 OZ 29½" W 11½" H	<b>50035 OZ</b> 30" W 11" H	50030 OZ 29½" W 9¼" H



FINISH POLISHED ANTIQUE NICKEL GLASS ETCHED OPAL Annette's traditional elegance is captured in subtle design elements including cast scrolled ends, a traditionally detailed cast back plate and a ribbed, etched opal shade.



**3782 AN** 13¾" DIA., 5" H



53322 PL 15" W, 7¾" H



53320 PL 4¾" W, 7¾" H



**53323 PL** 24" W, 7¾" H



**53324 PL** 33¾" W, 7¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
53320 PL	1-100w Med.	6¾"	4"	4½" W, 7" H	
53322 PL	2-100w Med.	6¾"	51⁄2"	7" W, 4½" H	
53323 PL	3-100w Med.	6¾"	51⁄2"	7" W, 4½" H	
53324 PL	4-100w Med.	6¾"	5½"	7" W, 4½" H	
3782 AN*	2-60w Med.				HB, OZ

### $\mathsf{A} \mathsf{S} \mathsf{H} \mathsf{L} \mathsf{E} \mathsf{Y}^{\scriptscriptstyle \mathsf{\tiny M}}$

CHROME FINISH ETCHED OPAL; STEPPED TRIM DETAIL GLASS

Ashley's chic, transitional style highlights its distinctive cast perforated glass holders and stepped trim detail in a crisp Chrome finish.



5192 CM 12¾" W, 7¼" H



5191 CM 15¾" DIA., 7" H



5193 CM 19¼" W, 7¼" H



5190 CM 5" W, 8½" H



5194 CM 26¾" W, 7¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
5190 CM	1-100w Med.	6¼"	41⁄4"	5" W, 8½" H
5191 CM	3-60w Med.			
5192 CM	2-100w Med.	6¼"	4¾"	8½" W, 5" H
5193 CM	3-100w Med.	6¼"	4¾"	8½" W, 5" H
5194 CM	4-100w Med.	6¼"	4¾"	8½" W, 5" H

### $CLAIRE^{M}$

FINISH ANTIQUE NICKEL GLASS ETCHED OPAL Claire's traditional style is given a chic update with minimalist spun metal cups and cast finial transitions. The modernized metal work remains classically elegant when combined with the subtle curves of the etched opal glass shades.



**3782 AN** 13¾" DIA., 5" H



53582 AN 14" W, 7¼" H



53580 AN 5¼" W, 9¼" H



**53583 AN** 24" W, 7¼" H



**53584 AN** 30" W, 7¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
53580 AN	1-100w Med.	7¼"	4"	4½" W, 8" H	OZ
53582 AN	2-100w Med.	7¼"	3¼"	14" W, 4½" H	OZ
53583 AN	3-100w Med.	7¼"	3¼"	24" W, 4½" H	OZ
53584 AN	4-100w Med.	7¼"	31⁄4"	30" W, 4½" H	OZ
3782 AN*	2-60w Med.				HB, OZ

### C L A I R E™

OIL RUBBED BRONZE FINISH ETCHED OPAL GLASS

Claire's traditional style is given a chic update with minimalist spun metal cups and cast finial transitions. The modernized metal work remains classically elegant when combined with the subtle curves of the etched opal glass shades.



**3782 AN** 13¾" DIA., 5" H



53582 OZ 14" W, 7¼" H







53583 OZ 24" W, 7¼" H



ADDITIONAL FINISHES TOP TO OUTLET ITEM BULBS EXT. BACK PLATE 1-100w Med. 53580 OZ 7¼" 4" 41⁄2" W, 8" H AN 53582 OZ 2-100w Med. 7¼" 3¼" 14" W, 4½" H AN 53583 OZ 3-100w Med. 7¼" 3¼" 24" W, 4½" H AN 53584 OZ 4-100w Med. 7¼" 3¼" 30" W, 41/2" H AN 3782 OZ\* 2-60w Med. AN, HB



FINISH CHROME GLASS WHITE ETCHED Colette defines classic elegance. This traditional style features thick, pressed white etched glass paired with hand-lathed finials and transition detailing.



3852 CM 16" DIA., 5" H



58782 CM 16¾" W, 7¾" H



58780 CM 6" W, 8¼" H



58783 CM 26¼" W, 7¾" H



58784 CM 33¼" W, 7¾" H





BRUSHED NICKEL FINISH WHITE ETCHED GLASS

Colette defines classic elegance. This traditional style features thick, pressed white etched glass paired with hand-lathed finials and transition detailing.



3852 BN 16" DIA., 5" H



**58782 BN** 16¾" W, 7¾" H



58783 BN 26¼" W, 7¾" H



58780 BN 6" W, 8¼" H



58784 BN 33¼" W, 7¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
58780 BN	1-100w Med.	7½"	4¾"	4½" W, 7¼" H	CM, OZ
58782 BN	2-100w Med.	7½"	4¾"	7¼" W, 4½" H	CM, OZ
58783 BN	3-100w Med.	7½"	4¾"	9" W, 4½" H	CM, OZ
58784 BN	4-100w Med.	7½"	4¾"	111⁄2" W, 41⁄2" H	CM, OZ
3852 BN*	3-100w Med.				CM, OZ



FINISH OIL RUBBED BRONZE GLASS WHITE ETCHED Colette defines classic elegance. This traditional style features thick, pressed white etched glass paired with hand-lathed finials and transition detailing.



3852 OZ 16" DIA., 5" H



58782 OZ 16¾" W, 7¾" H



58780 OZ 6" W, 8¼" H



58783 OZ 26¼" W, 7¾" H



58784 OZ 33¼" W, 7¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
58780 OZ	1-100w Med.	7½"	4¾"	41⁄2" W, 71⁄4" H	BN, CM
58782 OZ	2-100w Med.	7½"	4¾"	7¼" W, 4½" H	BN, CM
58783 OZ	3-100w Med.	7½"	4¾"	9" W, 4½" H	BN, CM
58784 OZ	4-100w Med.	7½"	4¾"	111⁄2" W, 41⁄2" H	BN, CM
3852 OZ*	3-100w Med.				BN, CM

### $C \cap N S T A N C E^{T}$

CHROME FINISH ETCHED OPAL GLASS

Constance puts a spin on tradition with bell shaped shades and unique sweeping arms imparting a distinctive style that seamlessly combines current and classic design elements.



50012 CM 15¾" W, 7¼" H



50010 CM 5" W, 7½" H



50013 CM 23" W, 7¼" H



50014 CM 32" W, 7¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	INV
50010 CM	1-100w Med.	7"	4"	41⁄2" W, 71⁄4" H	
50012 CM	2-100w Med.	7"	5"	7¼" W, 4½" H	•
50013 CM	3-100w Med.	7"	5"	7¼" W, 4½" H	•
50014 CM	4-100w Med.	7"	5"	7¼" W, 4½" H	•

# ALICE"

FINISH ANTIQUE NICKEL GLASS ETCHED OPAL Alice's classic design features decorative half round turnings and coordinating cast end caps. Available in Antique Nickel and Brushed Bronze finishes to complement the elegant etched opal glass, this style will add beauty to any décor.



5830 AN	1-100w Med.					7½"	4"	5¼" W, 8" H	BR	•
5832 AN	2-100w Med.					7½"	3¼"	8" W, 5¼" H	BR	•
5833 AN	3-100w Med.					7½"	3¼"	8" W, 5¼" H	BR	•
5834 AN	4-100w Med.					7½"	3¼"	8" W, 5¼" H	BR	•
5551 BN*	2-60w Med.	5551 BN-GU24	2-26w GU24	5551 BN-LED	1-32w FSI-200				BR, CM	


\*Recommended companion flush mount. For additional options, see pages 24-28.

INV

# ALICE"

BRUSHED BRONZE FINISH ETCHED OPAL GLASS


Alice's classic design features decorative half round turnings and coordinating cast end caps. Available in Antique Nickel and Brushed Bronze finishes to complement the elegant etched opal glass, this style will add beauty to any décor.



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
5830 BR	1-100w Med.					7½"	4"	5¼" W, 8" H	AN	•
5832 BR	2-100w Med.					7½"	31⁄4"	8" W, 5¼" H	AN	•
5833 BR	3-100w Med.					7½"	31⁄4"	8" W, 5¼" H	AN	•
5834 BR	4-100w Med.					7½"	3¼"	8" W, 5¼" H	AN	•
5551 BR*	2-60w Med.	5551 BR-GU24	2-26w GU24	5551 BR-LED	1-32w FSI-200				BN, CM	



FINISH BRUSHED NICKEL, CHROME GLASS ETCHED Abbie's elegant design features robust square tube construction enhanced by bold decorative cast finials. The six-sided glass shades are ribbed and flared, adding additional sophistication.





BRUSHED NICKEL, CHROME FINISH ETCHED OPAL GLASS

Shelly offers a sophisticated style statement with sixsided, etched opal fluted glass and decorative cast finials in either Brushed Nickel or Chrome finishes.



5012 BN (shown) 5012 CM 16" W, 8¼" H



5013 BN (shown) 5013 CM 24" W, 81⁄4" H



5010 BN 5010 CM (shown) 5½" W, 9½" H



5014 BN 5014 CM (shown) 32¼" W, 8¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
5010 BN, 5010CM	1-100w Med.	7½"	5"	4¾" W, 9" H
5012 BN, 5012 CM	2-100w Med.	7¾"	41⁄4"	9" W, 4¾" H
5013 BN, 5013 CM	3-100w Med.	7¾"	41⁄4"	9" W, 4¾" H
5014 BN, 5014 CM	4-100w Med.	7¾"	4¼"	9" W, 4¾" H



FINISH ANTIQUE NICKEL GLASS ETCHED OPAL



The elegant Yorktown collection offers updated traditional styling with cast detailing for an authentic touch. The cast back plate, detailed finials, bar ends and transition balls combine to make this classic design perfect for any décor.



**5742 AN** 15½" W, 9½" H



**5740 AN** 4¾" W, 11" H



**5743 AN** 23¾" W, 9½" H



**5744 AN** 32¾" W, 9½"

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5740 AN	1-100w Med.	5¾"	5"	41⁄2" W, 10" H	BR
5742 AN	2-100w Med.	6¾"	7¼"	10" W, 4½" H	BR
5743 AN	3-100w Med.	6¾"	7¼"	10" W, 4½" H	BR
5744 AN	4-100w Med.	7"	7¼"	10" W, 4½" H	BR

The elegant Yorktown collection offers updated traditional styling with cast detailing for an authentic touch. The cast back plate, detailed finials, bar ends and transition balls combine to make this classic design perfect for any décor.

Yorktown mounting

bars are curved in shape.



# $\mathsf{Y} \mathsf{O} \mathsf{R} \mathsf{K} \mathsf{T} \mathsf{O} \mathsf{W} \mathsf{N}^{\text{\tiny TM}}$

BRUSHED BRONZE FINISH ETCHED OPAL GLASS



**5742 BR** 15½" W, 9½" H



5743 BR 23¾" W, 9½" H



5740 BR 4¾" W, 11" H



32¾" W, 9½"

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5740 BR	1-100w Med.	5¾"	5"	41⁄2" W, 10" H	AN
5742 BR	2-100w Med.	6¾"	7¼"	10" W, 4½" H	AN
5743 BR	3-100w Med.	6¾"	7¼"	10" W, 4½" H	AN
5744 BR	4-100w Med.	7"	7¼"	10" W, 4½" H	AN

# $SAN SIMEON^{TM}$

FINISHSILVER LEAFGLASSHAND-PAINTED FAWN

The San Simeon collection combines angular lines with traditional forms featuring an authentic handapplied Silver Leaf finish and beautifully painted fawn colored glass.



ITEM	BULBS	EXT.	OUTLET	BACK PLATE	
FR49190SLF	1-100w Med.	81⁄2"	11½"	6" Square	
FR59192SLF	2-100w Med.	6¾"	6¾"	13" W, 5" H	
FR59193SLF	3-100w Med.	6¾"	6¾"	13" W, 5" H	
FR59194SLF	4-100w Med.	6¾"	6¾"	13" W, 5" H	



ANTIQUE NICKEL FINISH ETCHED OPAL GLASS

Reese features a traditional design with boutique details. The etched opal glass and Antique Nickel finish is updated with elegant, laser cut scrolls for a modern touch.






56323 AN 25¼" W, 9" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES	INV
56320 AN	1-100w Med.	6¾"	9¾"	5" Dia.		
56322 AN	2-100w Med.	7"	6¾"	5" Dia.		•
56323 AN	3-100w Med.	7"	6¾"	5" Dia.		•
3782 AN*	2-60w Med.				HB, OZ	



FINISH ANTIQUE NICKEL GLASS ETCHED OPAL Brooke's updated traditional look features a minimalist forged scroll design in Antique Nickel that elegantly complements its etched opal glass.





OLDE BRONZE FINISH ETCHED OPAL GLASS

Brooke's updated traditional look features a minimalist forged scroll design in Olde Bronze that elegantly complements its etched opal glass.



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5000 OB	1-100w Med.	5000 OB-GU24	1-18w GU24	5000 OB-LED	1-15w LESM-100	51⁄2"	8"	41⁄2" W, 7" H	AN
5002 OB	2-100w Med.	5002 OB-GU24	2-18w GU24	5002 OB-LED	2-15w LESM-100	6"	61⁄2"	9" W, 4½" H	AN
5003 OB	3-100w Med.	5003 OB-GU24	3-18w GU24	5003 OB-LED	3-15w LESM-100	6"	7¼"	9" W, 4½" H	AN
5004 OB	4-100w Med.	5004 OB-GU24	4-18w GU24	5004 OB-LED	4-15w LESM-100	6"	7"	9" W, 4½" H	AN
3782 OZ*	2-60w Med.								AN, HB



FINISH BRUSHED NICKEL GLASS ETCHED OPAL



Brantley Chandeliers, pages 80-85 Brantley's transitional design features bold arms that sweep outward, creating a dramatic yet elegant effect. Its unique geometric castings and decorative arm construction add to its beauty, making this collection a perfect complement to any décor.



4631 BN 4631 BN-LED 17" DIA., 7" H



5362 BN 14½" W, 7¼" H



**4630 BN** 4¾" W, 12¼" H



5363 BN 24¼" W, 7¼" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
4630 BN	1-100w Med.			81⁄2"	7"	4¾" W, 10" H	OB
4631 BN	3-60w Med.	4631 BN-LED	1-32w FSI-200				OB
5362 BN	2-100w Med.			8"	41⁄2"	10" W, 4¾" H	OB
5363 BN	3-100w Med.			81⁄2"	41⁄2"	10" W, 4¾" H	OB

Brantley bath fixtures can be mounted facing up or down.

 $\mathsf{BRANTLEY}^{\scriptscriptstyle \rm M}$ 

OLDE BRONZE FINISH ETCHED OPAL GLASS



Brantley's transitional design features bold arms that sweep outward, creating a dramatic yet elegant effect. Its unique geometric castings and decorative arm construction add to its beauty, making this collection a perfect complement to any décor.



5362 OB 14½" W, 7¼" H



5363 OB 24¼" W, 7¼" H



**4630 OB** 4¾" W, 12¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
4630 OB	1-100w Med.	81⁄2"	7"	4¾" W, 10" H	BN
5362 OB	2-100w Med.	8"	41⁄2"	10" W, 4¾" H	BN
5363 OB	3-100w Med.	81⁄2"	41⁄2"	10" W, 4¾" H	BN

Brantley bath fixtures can be mounted facing up or down. For flush mount options, see pages 24-28.

### PLYMOUTH<sup>™</sup>

FINISH POLISHED ANTIQUE NICKEL GLASS ETCHED OPAL



Plymouth Chandeliers, pages 132-139

Classic never goes out of style. Plymouth's fine details include sweeping arms, cast stepped back plate and cast detailing in hand-rubbed Olde Bronze or Polished Antique Nickel finish options, both complemented by etched opal glass shades.



**4241 PL** 17½" DIA., 8¼" H



54262 PL 13½" W, 8" H



**54260 PL** 5½" W, 9½" H



54263 PL 21½" W, 8" H



54264 PL 29½" W, 8" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
4241 PL	3-60w Med.				OB
54260 PL	1-100w Med.	7¾"	4¾"	41⁄2" W, 91⁄4" H	OB
54262 PL	2-100w Med.	7¾"	41⁄4"	9¼" W, 4¼" H	OB
54263 PL	3-100w Med.	7¾"	41⁄4"	9¼" W, 4¼" H	OB
54264 PL	4-100w Med.	7¾"	41⁄4"	9¼" W, 4¼" H	OB

#### $\mathsf{PLYMOUTH}^{\scriptscriptstyle{\mathsf{M}}}$

OLDE BRONZE FINISH ETCHED OPAL GLASS



Plymouth Chandeliers, pages 132-139

Classic never goes out of style. Plymouth's fine details include sweeping arms, cast stepped back plate and cast detailing in hand-rubbed Olde Bronze or Polished Antique Nickel finish options, both complemented by etched opal glass shades.



54261 OB 17½" DIA., 8¼" H



**54262 OB** 13½" W, 8" H



54263 OB 21½" W, 8" H



54260 OB 5½" W, 9½" H



54264 OB 29½" W, 8" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
54260 OB	1-100w Med.	7¾"	4¾"	41⁄2" W, 91⁄4" H	PL
54261 OB	3-60w Med.				
54262 OB	2-100w Med.	7¾"	4¼"	9¼" W, 4¼" H	PL
54263 OB	3-100w Med.	7¾"	4¼"	9¼" W, 4¼" H	PL
54264 OB	4-100w Med.	7¾"	41⁄4"	9¼" W, 4¼" H	PL

### STOWE<sup>m</sup>

FINISH METRO COPPER GLASS ANTIQUE LIGHT SCAVO



Stowe features hand-forged iron work in a unique Metro Copper finish with subtle red copper hues that complement the antique light scavo glass. This transitional style creates an elegant yet modern look.



27½" W, 8" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
4720 MC	1-100w Med.	6½"	63⁄4"	4" W, 7" H
4721 MC	2-75w Med.			
5732 MC	2-100w Med.	6½"	4¼"	8" W, 4¼" H
5733 MC	3-100w Med.	6½"	4¼"	8" W, 4¼" H
5734 MC	4-100w Med.	6½"	41⁄4"	8" W, 4¼" H



ANTIQUE SCAVO GLASS



Casa makes the most of its fine details: individually unique antique scavo glass, twisted wrought iron and hand-forged scrollwork in an Olde Black finish complete its rustic-chic appeal with a Southwestern flair.

Casa Outdoor, pages 690-691



5543 OL 22¾" W, 8¾" H



5542 OL 15¾" W, 8¾" H



5544 OL 29¾" W, 8¾" H



4010 OL 5" W, 10¾" H



5545 OL 35¾" W, 8¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
4010 OL	1-100w Med.	6"	6¾"	5" W, 7¾" H
5542 OL	2-100w Med.	7"	3¼"	7½" W, 5" H
5543 OL	3-100w Med.	7"	3¼"	7½" W, 5" H
5544 OL	4-100w Med.	7"	31⁄4"	7½" W, 5" H
5545 OL	5-100w Med.	7"	31⁄4"	7½" W, 5" H

Casa bath fixtures can be mounted facing up or down. For flush mount options, see pages 24-28.

# $\mathsf{ISABELLA}^{\scriptscriptstyle{\mathsf{M}}}$

FINISHPOLISHED ANTIQUE NICKELGLASSMARBLED ETCHED AMBER

Isabella's elegant details create a European flair with flourishing decorative cast detailing and scalloped marbled etched amber glass.



5391 PL 13" DIA., 9¾" H



5392 PL 16½" W, 9¼" H



5390 PL 5½" W, 10" H



5393 PL 21¼" W, 9¼" H



**5394 PL** 29" W, 9¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	ADDITIONAL FINISHES
5390 PL	1-100w Med.	8"	5¼"	5¼" W, 9½" H Back Plate	BB
5391 PL	3-60w Med.			5" Dia. Canopy	BB
5392 PL	2-100w Med.	8"	5¼"	16½" W, 5¼" H Back Plate	BB
5393 PL	3-100w Med.	8"	51⁄4"	161⁄2" W, 51⁄4" H Back Plate	BB
5394 PL	4-100w Med.	8"	5¼"	161/2" W, 51/4" H Back Plate	BB



BURNISHED BRASS FINISH MARBLED ETCHED AMBER GLASS

Isabella's elegant details create a European flair with flourishing decorative cast detailing and scalloped marbled etched amber glass.



5391 BB 13" DIA., 9¾" H



**5392 BB** 16½" W, 9¼" H



5393 BB 21¼" W, 9¼" H



5390 BB 5½" W, 10" H



**5394 BB** 29" W, 9¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	ADDITIONAL FINISHES
5390 BB	1-100w Med.	8"	5¼"	5¼" W, 9½" H Back Plate	PL
5391 BB	3-60w Med.			5" Dia. Canopy	PL
5392 BB	2-100w Med.	8"	5¼"	161⁄2" W, 51⁄4" H Back Plate	PL
5393 BB	3-100w Med.	8"	5¼"	161⁄2" W, 51⁄4" H Back Plate	PL
5394 BB	4-100w Med.	8"	5¼"	161⁄2" W, 51⁄4" H Back Plate	PL

# $FRANCOISE^{**}$

FINISH POLISHED ANTIQUE NICKEL GLASS FROSTED RIBBED Francoise offers a European elegance with decorative cast detailing in Polished Antique Nickel or Burnished Brass finish options. The frosted ribbed glass adds to its classical appeal.



**5582 PL** 15" W, 9½" H



5583 PL 25¼" W, 9½" H



5580 PL 6" W, 10¾" H 5584 PL 30½" W, 9½" H



5585 PL 37" W, 9½" H

BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
1-100w Med.	6¾"	6¼"	41⁄2" W, 91⁄4" H	BB
2-100w Med.	6¾"	7¼"	9¼" W, 4½" H	BB
3-100w Med.	6¾"	7¼"	9¼" W, 4½" H	BB
4-100w Med.	6¾"	7¼"	9¼" W, 4½" H	BB
5-100w Med.	6¾"	7¼"	9¼" W, 4½" H	BB
	1-100w Med. 2-100w Med. 3-100w Med. 4-100w Med.	1-100w Med.     6¾"       2-100w Med.     6¾"       3-100w Med.     6¾"       4-100w Med.     6¾"	BULBS     EXT.     OUTLET       1-100w Med.     634"     644"       2-100w Med.     634"     714"       3-100w Med.     634"     714"       4-100w Med.     634"     714"	BULBS     EXT.     OUTLET     BACK PLATE       1-100w Med.     634"     614"     4½" W, 9½" H       2-100w Med.     634"     7¼"     9¼" W, 4½" H       3-100w Med.     634"     7¼"     9½" W, 4½" H       4-100w Med.     634"     7¼"     9½" W, 4½" H

### $FRANCIOSE^{**}$

BURNISHED BRASS FINISH FROSTED RIBBED GLASS

Francoise offers a European elegance with decorative cast detailing in Polished Antique Nickel or Burnished Brass finish options. The frosted ribbed glass adds to its classical appeal.



5582 BB 15" W, 9½" H



5583 BB 25¼" W, 9½" H



5584 BB 30½" W, 9½" H



5580 BB 6" W, 10¾" H



**5585 BB** 37" W, 9½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
5580 BB	1-100w Med.	6¾"	6¼"	41⁄2" W, 91⁄4" H	PL
5582 BB	2-100w Med.	6¾"	7¼"	9¼" W, 4½" H	PL
5583 BB	3-100w Med.	6¾"	7¼"	9¼" W, 4½" H	PL
5584 BB	4-100w Med.	6¾"	7¼"	9¼" W, 4½" H	PL
5585 BB	5-100w Med.	6¾"	7¼"	9¼" W, 4½" H	PL

### PLANTATION<sup>™</sup>

FINISH POLISHED ANTIQUE NICKEL GLASS CLEAR OPTIC



Plantation Chandeliers, pages 140-147

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped, clear optic glass that makes a noble statement. The elaborate, decorative cast detailing is accentuated by its lush finish.

Plantation Outdoor, pages 694-697



4102 PL 12" DIA., 8" H



4881 PL 16" DIA., 8¾" H



5312 PL 13" W, 8¼" H



5313 PL 21" W, 8¼" H



5314 PL 29" W, 8¼" H





5310 PL 5" W, 8¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
4102 PL	2-60w Med.				BB, CB, PZ
4881 PL	3-60w Med.				BB, CB, PZ
5310 PL	1-100w Med.	6½"	4¾"	4¾" W, 8" H	BB, PZ
5312 PL	2-100w Med.	6¾"	4¾"	8" W, 4¾" H	BB
5313 PL	3-100w Med.	6¾"	4¾"	8" W, 4¾" H	BB
5314 PL	4-100w Med.	6¾"	4¾"	8" W, 4¾" H	BB

Plantation bath fixtures can be mounted facing up or down.

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped, clear optic glass that makes a noble statement. The elaborate, decorative cast detailing is accentuated by its lush finish.

Plantation Outdoor, pages 694-697



Plantation Chandeliers, pages 140-147



BURNISHED BRASS FINISH CLEAR OPTIC GLASS



**4881 BB** 16" DIA., 8¾" H



4102 BB 12" DIA., 8" H



5313 BB 21" W, 8¼" H



5312 BB 13" W, 8¼" H



5310 BB 5" W, 8¾" H



**5314 BB** 29" W, 8¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
4102 BB	2-60w Med.				CB, PL, PZ
4881 BB	3-60w Med.				CB, PL, PZ
5310 BB	1-100w Med.	6½"	43⁄4"	4¾" W, 8" H	PL, PZ
5312 BB	2-100w Med.	6¾"	4¾"	8" W, 4¾" H	PL
5313 BB	3-100w Med.	6¾"	4¾"	8" W, 4¾" H	PL
5314 BB	4-100w Med.	6¾"	4¾"	8" W, 4¾" H	PL

Plantation bath fixtures can be mounted facing up or down.