

Beacons Flashing LED 125 Class



Edwards 125 Class standard flashing LED beacons are NEMA Type 4X signaling devices, suitable for use in indoor or outdoor applications where an intermittent (flashing) light source is required. Base material is gray or black, manufactured from a 33% glass filled nylon, providing a high resistance to heat and chemicals. The lens is made of shatter-resistant polycarbonate.

Features and Specifications

- LED light source
- Flash rate 65 fpm
- Shatter-resistant polycarbonate lens
- Gray or black glass filled nylon base
- Option for panel or conduit mounting
- Suitable for indoor or outdoor applications
- For outdoor use, lens should face up
- NEMA Type 4X enclosure
- Operating temperature range: -31°F to 150°F (-35°C to 66°C)



3.25"



Ordering Information						
Description	Cat. No.	Operating Voltage ¹	Current	LED Colors	Lamp Ratings	Replacement Lens
Flashing Beacon LED Gray Base	125LEDFA120A	120V AC	0.097 A	Amber	100,000 hours	125LA
	125LEDFB120A	120V AC	0.097 A	Blue	100,000 hours	125LB
	125LEDFG120A	120V AC	0.097 A	Green	100,000 hours	125LG
	125LEDFR120A	120V AC	0.097 A	Red	100,000 hours	125LR
	125LEDFA24D	24V DC	0.060 A	Amber	100,000 hours	125LA
	125LEDFB24D	24V DC	0.060 A	Blue	100,000 hours	125LB
	125LEDFG24D	24V DC	0.060 A	Green	100,000 hours	125LG
	125LEDFR24D	24V DC	0.060 A	Red	100,000 hours	125LR
Flashing Beacon LED Black Base	125LEDFA120AB	120V AC	0.097 A	Amber	100,000 hours	125LA
	125LEDFB120AB	120V AC	0.097 A	Blue	100,000 hours	125LB
	125LEDFG120AB	120V AC	0.097 A	Green	100,000 hours	125LG
	125LEDFR120AB	120V AC	0.097 A	Red	100,000 hours	125LR
	125LEDFA24DB	24V DC	0.060 A	Amber	100,000 hours	125LA
	125LEDFB24DB	24V DC	0.060 A	Blue	100,000 hours	125LB
	125LEDFG24DB	24V DC	0.060 A	Green	100,000 hours	125LG
	125LEDFR24DB	24V DC	0.060 A	Red	100,000 hours	125LR

¹AC voltage frequency is 50/60 Hz

Accessories	
Description	Cat. No.
Protective Wire Guard	125GRD
Corner Mount Bracket	CBR
Wall Mount Bracket	WBR



125GRD
Protective Wire Guard



CBR
Corner Mount Bracket



WBR
Wall Mount Bracket



Beacons

Flashing LED

125 Class

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
125LEDF*120A	0.25	0.50
125LEDF*24D	0.25	0.50
125LEDF*120AB	0.25	0.50
125LEDF*24DB	0.25	0.50
125GRD	0.61	0.77
CBR	4.00	4.20
WBR	2.30	2.50

*Letter in this position designates LED color: A - amber, B - blue, G - green, R - red

