

LONGER motor life.
BETTER run-time.
MORE power.

EXPERIENCE the MILWAUKEE difference.

The Milwaukee® M12™ cordless system delivers industry-leading durability and power in a size that outperforms the competition in the tightest places. M12™ defines cordless tool innovation, transforming inefficient manual tools—such as cable and copper tubing cutters—into advanced workhorses powered by Milwaukee's REDLITHIUM™ battery technology.

Driven to Outperform.

M12 FUEL™ is engineered for the most demanding jobs. It delivers unrivaled performance in a compact structure and features three Milwaukee® exclusive innovations: the POWERSTATE™ Brushless Motor, REDLITHIUM™ Battery Pack and REDLINK PLUS™ Intelligence Hardware and Software—that deliver unmatched power, run-time and durability.

- » POWERSTATE Brushless Motor outperforms with up to 10X longer motor life.
- » REDLINK PLUS Intelligence includes total system communication with overload protection, increasing tool life.
- » REDLITHIUM 2.0 and XC4.0 battery packs allow for up to 4X more run-time and 20 percent more power.

M12 FUEL

THE M12 SERIES

Extreme-performance cordless power tools designed, engineered and built to deliver unmatched productivity. Milwaukee® affirms its industry leadership, integrating three ground-breaking technologies in a single package. M12 FUEL™ puts unrivaled durability, run-time and performance into the hands of professionals.





A CUT ABOVE
The power you want and
the portability you need.

M12™ 600 MCM Cable Cutter Kit

Simplify cable cutting with the one cordless tool that fits comfortably in crowded panels and generates 5,000 pounds of force. With an open jaw, breakthrough powered ratcheting mechanism and superior blade geometry, the 600 MCM Cable Cutter fits into tight spaces and cuts effortlessly through large-diameter cable, leaving a clean, installation-ready cut. Plus, it includes a built-in LED light to illuminate the line of cut.

What's included:

- M12™ 600 MCM Cable Cutter
- M12™ XC High Capacity REDLITHIUM™ Battery
- M18™ and M12™ Multivoltage Charger
- Carrying Case

Tool Specs:

Voltage	12 V
Battery Warranty	3 years
Length	10-1/2"
Weight	6.7 lb
Blade	600 MCM
Tool Warranty	5 years

BSE Part # 2840215

MFG Part # 2472-21XC



M12 FUEL™ HACKZALL® Recipricating Saw Kit

The M12 FUEL™ HACKZALL® is the fastest cutting and most powerful saw in its class, delivering over 4X more run-time, up to 70% faster cutting and up to 6X longer tool life than competitive saws. REDLINK PLUS™ Intelligence ensures optimized performance and protects your investment from overload, overheating and over-discharge. The dual gear counter balance mechanism significantly reduces vibration, providing faster starts in metal and reduced user fatigue.

What's included:

- M12 FUEL™ HACKZALL® Saw
- M12™ REDLITHIUM™ XC 4.0 Extended Capacity Battery Pack
- M12™ Lithium-ion Battery Charger
- Contractor Bag
- Multimaterial Blade



Tool Specs:

Voltage	12 V
Battery Warranty	3 years
Length	13-1/4"
Weight	4.1 lb
Stroke Length	5/8"
Tool Warranty	5 years
SPM	0-3,000

BSE Part # 3169757

MFG Part # 2520-21XC



M12 FUEL™ 1/2" Hammer Drill/Driver Kit

This lightweight, versatile hammer drill/driver provides up to 10X longer motor life, 2X more power and 4X more run-time. The M12 FUEL™ Hammer Drill/Driver's onboard fuel gauge helps you monitor the charge precisely, so there's less downtime on the job, and a built-in LED light illuminates the work surface. An all-metal ratcheting locking chuck provides maximum grip, bit retention and durability. A new contoured soft grip gives you ultimate comfort during prolonged use.

- What's included:**
- M12 FUEL™ 1/2" Hammer Drill/Driver
 - M12 REDLITHIUM™ 2.0 Compact Battery Pack
 - M12™ REDLITHIUM™ XC 4.0 Extended Capacity Battery Pack
 - M12™ Lithium-ion Battery Charger
 - Belt Clip and Carrying Case

Tool Specs:

Voltage	12 V
Battery Warranty	2 years
Length	7-3/4"
Peak Torque	350 in lb
Chuck Type	1/2"
BPM	0-450/0-1,700
Tool Warranty	5 years

BSE Part #	2899012
MFG Part #	2404-22



Hand tool
PORTABILITY

M12 FUEL™ 1/4" Hex Impact Driver Kit

This hex impact driver provides up to 3X longer motor life, up to 2X more run-time and features proprietary Milwaukee® 2-Mode DRIVE CONTROL™ for better control over the power and speed required for specific applications. The M12 FUEL™ 1/4" Hex Impact Driver offers fastening speed comparable to 18 V impact drivers with 1,200 in lb of torque.

- What's included:**
- M12 FUEL™ 1/4" Hex Impact Driver
 - Two-M12 REDLITHIUM™ 2.0 Compact Battery Packs
 - M12™ Lithium-ion Battery Charger
 - Belt Clip
 - Carrying Case

Tool Specs:

Voltage	12 V
Battery Warranty	2 years
Length	6"
Peak Torque	1,200 in lb
No Load Speed	0-2,650 RPM
No Load IPM	0-3,550
Tool Warranty	5 years

BSE Part #	2899014
MFG Part #	2453-22

Three industry-leading
technologies

IN ONE TOOL.

The **M18** **FUEL™** SERIES

M18 FUEL™ is engineered for the most demanding tradesmen in the world. Delivering unrivaled performance in a compact structure, all M18 FUEL™ products feature three Milwaukee® exclusive innovations—The POWERSTATE™ Brushless Motor, REDLITHIUM™ Battery Pack and REDLINK PLUS™ Intelligence Hardware and Software—that deliver unmatched power, run-time and durability on the jobsite. Simply put, M18 FUEL™ tools are the most powerful 18 V cordless tools in their class.

Powerstate™ Brushless Motor

Designed, engineered and built by Milwaukee®, POWERSTATE™ is the best-in-class brushless motor that works harder and lives longer. POWERSTATE™ brushless motors are ideal for professional tradesmen because they deliver more application speed, torque and durability in a smaller size.

M18 FUEL™





FASTER cuts.
REDUCED heat.
EXTENDED life.

M18 FUEL™ SAWZALL® Reciprocating Saw Kit

The M18 FUEL™ SAWZALL® Reciprocating Saw cuts faster than its corded counterparts and offers up to 2X more run-time and 5X longer tool life than competitive saws. The 18 V lithium-ion SAWZALL® features an adjustable shoe, integrated LED light and a hang hook for convenient storage on the job.

What's included:

M18 FUEL™ SAWZALL® Reciprocating Saw
M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Pack
M18™ and M12™ Multivoltage Charger
Blade
Carrying Case

Tool Specs:

Voltage	18 V
Battery Warranty	3 years
Length	18-1/2"
Weight	8.9 lb
Stroke Length	1-1/8"
SPM	0-3,000
Tool Warranty	5 years

BSE Part #	3074323
MFG Part #	2720-21



M18 FUEL™ Deep Cut Band Saw Kit

This band saw cuts faster than its corded counterparts, provides the same legendary durability of a Milwaukee corded band saw and delivers up to 2X more run-time than other cordless options. Equipped with Jobsite Armor Technology™, this tool is better protected from drops and debris with a proprietary composite material and crush zone barriers to absorb impacts. The M18 FUEL™ Deep Cut Band Saw also features a tool-free locking adjustable shoe that can adjust from an extended shoe to no shoe in seconds.

What's included:

M18 FUEL™ Deep Cut Band Saw
Two M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Pack
M18™ and M12™ Multivoltage Charger
Blade
Carrying Case

Tool Specs:

Voltage	18 V
Battery Warranty	3 years
Length	21"
Weight	15 lb
Capacity	5" x 5"
SFPM	0-380
Tool Warranty	5 years

BSE Part # 3167778

MFG Part # 2729-22



M18™ Cordless Lithium-Ion 5-3/8" Metal Saw Kit

This compact and lightweight metal cutting saw delivers the fastest cuts for the electrical, mechanical, plumbing, HVAC and general construction contractor. The 2682 utilizes an exclusive 4-Pole Frameless Motor for up to 35% more cutting power and best in class run-time with over 200 cuts of 3/4" EMT per charge. Features a METAL TECH™ 5-3/8" 30T Carbide-Tipped Metal Saw Blade for cool, burr-free cuts through EMT, strut, threaded rod, sheet metal, angle iron and other ferrous materials.

- What's included:**

- M18™ 5-3/8" Metal Saw
 - M18™ REDLITHIUM™ XC Extended Capacity Battery
 - M18™ and M12™ Multivoltage Charger
 - Contractor Bag

Tool Specs:

Voltage	18 V
Battery Warranty	3 years
Length	12"
Width	6.5"
Weight	4.3 lb
Arbor Size	20 mm
Tool Warranty	5 years

BSE Part #	2673671
MFG Part #	2682-22



M18 FUEL™ 1/4" Hex Impact Driver Kit

At 1,800 in lb of fastening torque, this tool drives screws faster but also provides greater control over power and speed. The 4-Mode DRIVE CONTROL™ provides greater control over output speed and power for greater versatility by delivering 0–850 RPM in Mode 1, 0–2,100 RPM in Mode 2, and 0–3,000 RPM in Mode 3. Self-tapping Screw Mode is designed to reduce walking when starting self-tapping screws as well as reduce overdriving, breaking and stripping out screws.

What's included:

M18 FUEL™ 1/4" Hex Impact Driver
Two M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs
M18™ and M12™ Multivoltage Charger
Belt Clip
Bit Holder and Carrying Case



Tool Specs:

Voltage	18 V
Battery Warranty	3 years
Length	5-1/4"
Weight	3.1 lb
No Load Speed	0–3,000 RPM
Torque	0–380
Tool Warranty	5 years

BSE Part # 3288198

MFG Part # 2753-22



M18 FUEL™ 1" SDS Plus Rotary Hammer

The rotary hammer delivers faster than corded speed, corded durability and all-day work on one charge. The Milwaukee POWERSTATE™ Brushless Motor Provides 1.7 ft lb of impact energy, 0–1,400 RPM and 0–4,900 BPM. REDLINK PLUS™ Intelligence integrates full-circle communication between tool, battery and charger to protect from overloading, overheating and over-discharging.

- What's included:**
- M18 FUEL™ 1" SDS Plus Rotary Hammer
 - M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Pack
 - M18™ and M12™ Multivoltage Charger
 - Depth Rod
 - Side Handle/Carrying Case

Tool Specs:

Voltage	18 V
Battery Warranty	3 years
Length	12-1/2"
Weight	8.5 lb
No Load Speed	0–1,400 RPM
BPM	0–4,900
Tool Warranty	5 years

BSE Part #	3205490
MFG Part #	2712-22



MAXIMUM
durability and
bit retention.

M18 FUEL™ Hole Hawg® 1/2" Right Angle Drill Kit

The M18 FUEL™ HOLE HAWG® 1/2" Right Angle Drill from Milwaukee drills faster than the original corded HOLE HAWG®, delivers over 150 7/8" holes per charge and is over 30% lighter weight than its corded predecessor. Optimized for electricians, the M18 FUEL™ HOLE HAWG® is the first cordless tool of its kind, delivering game-changing productivity for professionals drilling with augers up to 1-1/4" and self-feed bits up to 2".

What's included:

- M18 FUEL™ HOLE HAWG® 1/2" Right Angle Drill
- M18™ REDLITHIUM™ XC 5.0 Extended Capacity Battery Pack
- M18™ and M12™ Multivoltage Charger
- Chuck Key
- Contractor Bag

Tool Specs:

Voltage	18 V
Battery Warranty	3 years
Length	17"
Weight	9 lb
Speed	0-1,200 RPM
Chuck Size	1/2"
Tool Warranty	5 years

BSE Part # 3201372
MFG Part # 2707-22



M18 Fuel™ 1/2" Drill/Driver Kit

This powerful 18-volt cordless drill features the POWERSTATE™ Brushless Motor and delivers up to 1,200 in lb of torque and up to 2,000 RPM, providing faster drilling speed under heavy load to increase productivity. At only 7-1/2" in length, it is the most compact drill in its class, reducing fatigue when used for extended periods of time and allowing access to tight work spaces.

What's included:

M18 FUEL™ 1/2" Drill/Driver
Two M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs
M18™ and M12™ Multivoltage Charger
Belt Clip
Bit Holder and Carrying Case

Tool Specs:

Voltage	18 V
Battery Warranty	3 years
Length	7-1/2"
Weight	3.14 lb
No Load Speed	0–550/0–2,000 RPM
Peak Torque	1,200 in lb
Tool Warranty	5 years

BSE Part # 3288197

MFG Part # 2703-22



M18 Fuel™ 1/2" Hammer Drill Kit

This drill delivers up to 1,200 in lb of torque and up to 2,000 RPM, providing faster drilling speed under heavy load to increase productivity. The M18 FUEL™ Hammer Drill's all-metal ratcheting locking chuck provides maximum grip, bit retention and durability.

What's included:

M18 FUEL™ 1/2" Drill/Driver
Two M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs
M18™ and M12™ Multivoltage Charger
Belt Clip
Bit Holder
Carrying Case

BSE Part # 3187207

MFG Part # 2704-22



M18 Fuel™ 2-Tool Combo Kit

This 2-tool combo is a high performing Hammer Drill and Impact Driver Combo Kit. Included is the M18 FUEL™ Hammer Drill. Delivering up to 1,200 in lb of torque and up to 2,000 RPM, it provides faster drilling speed under heavy load to increase productivity. Also included is the M18 FUEL™ 1/4" Hex Impact Driver, at 1,800 in lb of fastening torque, this impact drives screws faster but also provides greater control over power and speed thanks to its proprietary 4-mode DRIVE CONTROL.

What's included:

M18 FUEL™ 1/2" Hammer Drill/Driver
M18 FUEL™ 1/4" Hex Impact Driver
Two M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs
M18™ and M12™ Multivoltage Charger
Two Belt Clips
Two Bit Holders
Side Handle and Carrying Case

BSE Part # 3262029

MFG Part # 2897-22



M18™ and M12™ Rapid Charger

The M18™ and M12™ Rapid Chargers charge packs up to 40% faster, reducing downtime and maximizing productivity. The charger accepts all M18™ and M12™ batteries, providing an upgrade for both systems. Featuring REDLINK™ Intelligence, it communicates directly with the battery to monitor cell voltage, temperature and charge status to optimize the performance and extend the life of the pack.

Not all lithium-ion batteries are created equal.

Milwaukee® is the world leader in cordless lithium-ion technology, offering the most advanced solutions to tradesmen around the globe. Our exclusive line of REDLITHIUM™ batteries provide up to 40% more run-time, 20% more power and 50% more recharges than conventional lithium-ion batteries.

Features:

Charges batteries up to 40% faster

Charges all M12™ and M18™ batteries

Sequential charging: automatically charges the second inserted pack once the first pack is fully charged

REDLINK™ Intelligence: charger communicates with the battery pack to ensure optimum performance and extend life

BSE Part # 3291549

MFG Part # 48-59-1808



M12™ REDLITHIUM™ Replacement Battery Packs

- Features:**
- REDLINK™ Intelligence:** Provides optimized performance and overload protection using total system communication between tool, battery and charger
 - Best-in-class construction:** Offers long-lasting performance and durability
 - All-weather performance:** Delivers fade-free power in extreme jobsite conditions
 - Versatility:** Powers all Milwaukee M12™ cordless power tools

2.0 Compact Battery Pack

BSE Part #	2899005
MFG Part #	48-11-2420

XC4.0 Extended Capacity Battery Pack

BSE Part #	2899006
MFG Part #	48-11-2440



M18™ REDLITHIUM™ Replacement Battery Packs

- Features:**
- REDLINK™ Intelligence:** Provides optimized performance and overload protection using total system communication between tool, battery and charger
 - Best-in-class construction:** Offers long-lasting performance and durability
 - Fuel gauge onboard:** Displays remaining run-time for less downtime on the job
 - All-weather performance:** Delivers fade free power in extreme jobsite conditions
 - Versatility:** Powers more than 60 Milwaukee® M18™ cordless power tools

2.0 Compact Battery Pack

BSE Part #	2898973
MFG Part #	48-11-1820

XC5.0 Extended Capacity Battery Pack

BSE Part #	3225529
MFG Part #	48-11-1850