



1 HOLE SAW PER BOX.  
 ARBOR NOT INCLUDED.

These High Quality Bi-Metal Hole Saws are made by a very special process. The cutting edge is electron beam welded to a tough alloy steel back. These hole saws are ideal for work where high performance & accuracy are needed. Saws have knock-out holes for easy core removal.

Made In



- ◆ Made In USA
- ◆ Bi-Metal Construction
- ◆ M3 Cutting Edge
- ◆ 4/6 Variable Pitch. Rc. 63-65
- ◆ Positive Rake
- ◆ 1-1/2" Cutting Depth
- ◆ Premium Quality
- ◆ Cuts Through 2" x 4"s
- ◆ Red Finish

- Wood
- Plastic
- Machinable Metal
- Nail Embedded Wood
- Plywood
- Pipes
- Stainless Steel

\* USE ARBORS 276AR0001 or 276AR0002.  
 \*\* USE ARBORS 276AR0003 or 276AR0035.

## Bi-Metal Hole Saws - Variable Pitch

Part #	Dia.		PIPE TAP SIZE		PIPE ENT. SIZE		Use	
	Inches	MM	Inches	MM	Inches	MM	Arbor	List
275HW0011	9/16"	14.3	3/8"				*	\$14.58
275HW0012	5/8"	15.5					*	\$11.07
275HW0112	16mm	16.0					*	\$12.17
275HW0013	11/16"	17.5					*	\$11.07
275HW0014	3/4"	19.0	1/2"	13 mm	3/8"	10 mm	*	\$11.07
275HW0114	20mm	20.0					*	\$12.17
275HW0015	13/16"	20.6					*	\$11.07
275HW0016	7/8"	22.2	3/4"	19 mm	1/2"	13 mm	*	\$11.07
275HW0017	15/16"	23.8					*	\$11.07
275HW0117	25mm	25.0					*	\$12.91
275HW0018	1"	25.4					*	\$11.74
275HW0185	1-1/16"	27.0					*	\$11.74
275HW0019	1-1/8"	28.8	1"	25 mm	3/4"	19 mm	*	\$11.74
275HW0118	30mm	30.0					*	\$12.91
275HW0020	1-3/16"	30.2					*	\$11.74
275HW0021	1-1/4"	31.8					**	\$11.74
275HW0121	32mm	32.0					**	\$12.91
275HW0022	1-5/16"	33.3					**	\$11.74
275HW0023	1-3/8"	34.9			1"	25 mm	**	\$12.45
275HW0122	35mm	35.0					**	\$13.70
275HW0123	1-7/16"	36.5					**	\$12.45
275HW0024	1-1/2"	38.1	1-1/4"	32 mm			**	\$12.69
275HW0124	1-9/16"	39.7					**	\$12.69
275HW0224	40mm	40.0					**	\$14.13
275HW0025	1-5/8"	41.2					**	\$12.84
275HW0125	1-11/16"	42.9					**	\$12.84
275HW0026	1-3/4"	44.5	1-1/2"	38 mm	1-1/4"	32 mm	**	\$15.55
275HW0226	45mm	45.0					**	\$17.11
275HW0126	1-13/16"	46.0					**	\$15.55
275HW0027	1-7/8"	47.6					**	\$15.78
275HW0127	50mm	50.0					**	\$17.61
275HW0028	2"	50.8			1-1/2"	38 mm	**	\$16.01
275HW0128	2-1/16"	52.4					**	\$19.13
275HW0029	2-1/8"	53.9					**	\$19.13
275HW0129	55mm	55.0					**	\$21.04
275HW0030	2-1/4"	57.2	2"	51 mm			**	\$19.28
275HW0031	2-5/16"	58.7					**	\$19.45
275HW0032	2-3/8"	60.3					**	\$19.55
275HW0033	2-1/2"	63.5			2"	51 mm	**	\$20.62
275HW0034	2-9/16"	65.1					**	\$20.74
275HW0134	2-5/8"	66.7	2-1/2"	64 mm			**	\$21.22
275HW0234	68mm	68.0					**	\$23.34
275HW0334	68.5mm	68.5					**	\$23.34
275HW0135	2-3/4"	69.9					**	\$21.22
275HW0136	2-7/8"	73.0					**	\$21.22
275HW0236	75mm	75.0					**	\$23.34
275HW0035	3"	76.2			2-1/2"	64 mm	**	\$21.22
275HW0137	3-1/8"	79.4					**	\$21.44
275HW0138	3-1/4"	82.6	3"	76 mm			**	\$21.44
275HW0139	3-3/8"	85.7					**	\$21.44
275HW0036	3-1/2"	88.9					**	\$21.44
275HW0140	3-5/8"	92.1					**	\$25.17
275HW0141	3-3/4"	95.3	3-1/2"	89 mm	3"	76 mm	**	\$29.57
275HW0142	3-7/8"	98.4					**	\$31.10
275HW0100	100mm	100.0					**	\$31.23
275HW0037	4"	101.6					**	\$32.44
275HW0143	4-1/8"	104.8			3-1/2"	89 mm	**	\$35.49
275HW0144	4-1/4"	108.0	4"	102 mm			**	\$46.19
275HW0038	4-1/2"	114.3			4"	102 mm	**	\$63.89
275HW0145	4-3/4"	120.7					**	\$74.03
275HW0039	5"	127.0					**	\$78.72
275HW0040	5-1/2"	139.7					**	\$93.93
275HW0146	5-3/4"	146.0					**	\$101.99
275HW0041	6"	152.4					**	\$110.04