

EVOKE

Evoke features an elliptical frame that gracefully supports a candelabra with clear glass shade. Mixed finishes highlight the unique shape and provide a hint of livable luxury to your home. Three-, five- and six-light options available.



P400117-020



P400024-020



P400026-020



P400024-020



P400117-020

FINISHES
● Antique Bronze - 020

THREE-LIGHT CHANDELIER
P400024-020 Antique Bronze
17-5/8" dia., 28-1/2" ht.
Overall ht. w/chain 103-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400025-020 Antique Bronze
24-5/8" dia., 35-3/8" ht.
Overall ht. w/chain 110-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P400026-020 Antique Bronze
28-1/2" dia., 39-1/2" ht.
Overall ht. w/chain 114-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400117-020 Antique Bronze
33-3/4" dia., 27-7/8" ht.
Overall ht. w/chain 103", wire 15'.
Five candelabra base lamps,
each 60w max.

*Fixtures shown with P7826-01
vintage lamps.*



P400117-104



P400024-104



P400026-104



P400025-104



P400117-104

EVOKE

FINISHES

- Polished Nickel - 104

THREE-LIGHT CHANDELIER

P400024-104 Polished Nickel
17-5/8" dia., 28-1/2" ht.
Overall ht. w/chain 103-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400025-104 Polished Nickel
24-5/8" dia., 35-3/8" ht.
Overall ht. w/chain 110-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400026-104 Polished Nickel
28-1/2" dia., 39-1/2" ht.
Overall ht. w/chain 114-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400117-104 Polished Nickel
33-3/4" dia., 27-7/8" ht.
Overall ht. w/chain 103"; wire 15'.
Five candelabra base lamps,
each 60w max.

*Fixtures shown with P7826-01
vintage lamps.*