

NONMETALLIC LIQUIDTIGHT STRAIN RELIEF CONNECTORS Cat. Nos. 2920NM & 4960NM Series

INSTALLING INSTRUCTIONS

TORQUE GLAND NUT TO BOTTOM OR TO A MAXIMUM VALUE AS FOLLOWS:
300 IN-LB FOR CABLE WITH OUTSIDE DIAMETER UP TO .750" AND 500 IN-LB
FOR CABLE UP TO .950" OUTSIDE DIAMETER.

CATALOG NUMBER	TRADE OR HUB SIZE	CABLE RANGE (INCHES)
2920NM	1/2"	.125 - .375
2921NM	1/2"	.310 - .560
2922NM	1/2"	.500 - .750
2930NM	3/4"	.125 - .375
2931NM	3/4"	.310 - .560
2932NM	3/4"	.500 - .750
2940NM	1"	.310 - .560
2941NM	1"	.500 - .750
2942NM	1"	.700 - .950
4960NM	1/2"	.125 - .375
4961NM	1/2"	.310 - .560
4970NM	3/4"	.125 - .375
4971NM	3/4"	.310 - .560
4972NM	3/4"	.500 - .750

WARRANTY: Thomas & Betts sells this product with the understanding that the user will perform all necessary tests to determine the suitability of this product for the user's intended application. Thomas & Betts warrants that this product will be free from defects in materials and workmanship for a period of two (2) years following the date of purchase. Upon prompt notification of any warranted defect, Thomas & Betts will, at its option, repair or replace the defective product or refund the purchase price. Proof of purchase is required. Misuse or unauthorized modification of the product voids all warranties.

Limitations and Exclusions: THE ABOVE WARRANTY IS THE SOLE WARRANTY CONCERNING THIS PRODUCT, AND IS IN LIEU OF ALL OTHER WARRANTIES EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, WHICH ARE SPECIFICALLY DISCLAIMED. LIABILITY FOR BREACH OF THE ABOVE WARRANTY IS LIMITED TO COST OF REPAIR OR REPLACEMENT OF THE PRODUCT, AND UNDER NO CIRCUMSTANCES WILL THOMAS & BETTS BE LIABLE FOR ANY INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES.

Thomas & Betts Corporation
Memphis, Tennessee
Website: www.tnb.com