

PENDANT MOUNT INSTALLATION INSTRUCTIONS

1. Run the White, Black and Green wires through the stem.
2. Tighten the stem to the cylinder by threading it into the lid.
3. Tighten the straight blade nylon screw or the 2.5mm allen screw on the strain relief on the cylinder lid to lock the stem into place.
4. Run the White, Black and Green wires through the sloped ceiling canopy hole.
5. Tighten the stem to the sloped ceiling canopy by threading it into the canopy.
6. Detach the mounting base from the canopy and install it to the junction box with included screws.
7. Connect the cylinder wires and the supply power wires from the junction box with included wire nuts (Black to Black, White to White, Green to Green).
8. Secure the canopy to the mounting base using the "L" shaped slots and tighten the Philips screws.
9. Insert the appropriate wattage lamp per the UL relamping label. For metal halide, use a lamp designed for open use applications.

IMPORTANT SAFETY INSTRUCTIONS:

- Read all the instructions before installation. Save the instructions for later use.
- Turn off the power at the fuse or circuit breaker box before installation or any maintenance work.
- Wear rubber-soled shoes and work on a sturdy wooden or other nonconductive ladder.
- Fixtures must be installed according to national electrical code and local building codes. For indoor use only.
- To avoid a hazard to any children, account for all parts and destroy all packing materials.
- Do not install any fixtures closer than 6" from any curtain or similar combustible material.
- **Warning:** Risk of fire. Most dwellings built before 1985 have supply wire rated at 60°C. Consult a qualified electrician before installation.
- Call the Technical Support department at ConTech Lighting if you have any installation questions. 800.728.0312

