

INSTALLATION INSTRUCTIONS

For Model 8766-L

READ AND SAVE THESE INSTRUCTIONS

WARNING! SHUT POWER OFF AT FUSE OR CIRCUIT BREAKER.

AVERTISSEMENT! COUPER LE COURANT AU NIVEAU DES FUSIBLES OU DU DISJONCTEUR.

HANGING THE FIXTURE (Fig. 1)

1. Shut off the power at the circuit breaker and remove the old fixture.
2. Carefully unpack your new fixture and lay out all the parts on a clear area. Take care not to lose any small parts necessary for installation.
3. Carefully remove screws (B) to separate top cover (A) from fixture body (C).

CONNECTING THE WIRES (Fig. 2)

4. While supporting the fixture, connect the electrical wires as shown in figure 2. If your post has a ground wire (green or bare copper), connect the fixture ground wire to it. If not, consult your electrician for proper grounding. After the wires are connected, tuck them carefully inside the post (E).

COMPLETING THE INSTALLATION (Fig.1)

5. Align the fixture (C) to post (E), and secure with mounting screws (D).
6. Align center glass (Z) onto heat sink (O). Re-attach top cover (A) to fixture body (C) with screws (B).
7. Bulb (G) information: (1 x AC LED 10W included.)

DO NOT EXCEED THE MAXIMUM WATTAGE RATING! (NE PAS DEPASSER LA PUISSANCE NOMINALE MAXIMALE!)

Replacing LED module (Fig. 3)

The LED module can be replaced by a qualified electrician without cutting of wire and without damage to any decorative element to which the fixture is attached. See installation steps for more details (Fig 3.)

- a. Carefully remove screws (B) to separate fixture body (C) from top cover (A) (Fig.1). Remove glass (Z). Next remove aluminum plate (O) from fixture body (C) by loosening screws (K).
- b. Remove wire nuts (L) hex-nuts (N) washers (M) and carefully remove the LED module (Q). Note: The LED module should be provided by a specified supplier.
- c. For better heat dissipation the LED module (Q) should be installed with the heat transfer material (P) when re-lamping

Your installation is now complete. Return power to the junction box and test the fixture

Fig.1




Fig. 2




Fig.3

