

Please go to www.quoizel.com for product cleaning tips. Go to the **Care + Maintenance** selection.

Tools Required: Flathead screwdriver, Phillips screwdriver, pliers, wire cutters, wire strippers, electrical tape, safety glasses.

Light Source: (4) A19 Medium Base 100W Maximum, Alternate bulb (4) 23W CFL.

Estimated Assembly Time: 30-45 minutes

Preparation: Identify and inspect all parts before beginning installation. Check package content list and diagrams below to be sure all parts are present. If any parts are missing or damaged, do not attempt to assemble, install, or operate the fixture. Contact customer service for replacement parts.

Note: This CONVERTIBLE fixture can be mounted as track light or island light. Refer to respective installation steps for installations.

⚠ Warnings and Cautions

Turn off electricity at circuit breaker or main fuse box before installation. Consult a licensed electrician if in doubt.

These instructions are provided for your safety. It is very important you read them completely before installing the fixture. We strongly recommend that a licensed, professional electrician perform the installation.

Disconnect fixture from power source before replacing bulbs. Make sure bulbs are given sufficient time to cool before removal. Do not subject glass parts to any shock while in operation or shattering may result.


⚠ Care of Tiffany Style Shade

A new tiffany lamp shade has an oil film applied to the shade that protects the tiffany shade from scratches during shipment. If the oil applied is too heavy you can remove the excess oil film with a paper towel. Gently wipe away the excess oil.

For general cleaning of tiffany shades use a gentle lemon oil-based furniture polish applied to a soft cloth and wipe gently.

If a white powder appears on the soldered joints of the tiffany shade this is a normal oxidation process. Use a small amount of lemon oil or mineral oil applied directly to oxidized areas and the soldered area will return to like new.

Package Contents




(Step 1A Continued)

- Remove nipple from the Rod with Label "C". Thread the nipple into the Fixture Body (K) and hand tighten until snug. And then thread the Rod with Label "C" onto the nipple and hand tighten until snug.
- Assemble other rods onto the Rod with Label "C" and make sure the Rod with Label "B" is on the top. Hand tighten until snug.
- Thread the Swivel (H) underside of the Ceiling Canopy (F) onto the top end of the Rod with Label "B" and hand tighten until snug.

Suggested rods for Ceiling height :

- 8' ceiling : use (1) 6" rod with Label "B" and (1) 12" rod with Label "C"
- 9' ceiling : use (1) 6" rod with Label "B" and (2) 12" rods
- 10' ceiling : use (2) 6" rods and (2) 12" rods




Assembly Instructions for Island Light (Step 1A - Step 6A)

STEP 1A - Install Ceiling Canopy, Rods and Socket Assembly together

- Thread Nipple (G) onto the Swivel (H). Place Ceiling Canopy (F) and Lock Washer (E) over the Nipple (G), secure by threading Hex Nut (D) onto the Nipple (G), tighten until snug.
- Determine the Rods (B/C) to be assembled to the Fixture Body (K) according to your hanging height.
- Pass the supply wires and ground wire through the chosen rods (B/C) and the Ceiling Canopy with Swivel.

STEP 2A - Install Crossbar Assembly


- Pass the supply wires through the Crossbar Assembly (A). Attach the Crossbar Assembly (A) to the Outlet Box with the head of the Green Ground Screw facing you. Secure it with Outlet Box Screws (not included). Tighten until snug.



Thank you for purchasing a Quoizel product.
Need assistance with parts or assembly? Call Quoizel customer service at 1-631-273-2700
or visit us on-line at www.quoizel.com

STEP 3A – Fit Ceiling Canopy to Crossbar Assembly

- A. Remove mounting balls from the Crossbar Assembly (A). Fit the Ceiling Canopy (F) to the Crossbar Assembly (A) and secure with mounting balls. Note: The Ceiling Canopy (F) should be snug against the ceiling and the mounting balls. If not, adjust the length of the nipple on the Crossbar Assembly (A) by unscrewing the preassembled hex nut and lock Washer and then screwing the mounting screws in or out of the crossbar until the correct length is achieved. Once the Ceiling Canopy (F) is secure, remove the mounting ball and Ceiling Canopy (F) and proceed to Step 4A.



(Step 1B continued)

- onto the Fixture Body (K). Place the Ceiling Canopy (F) and the Lock Washer (E) onto the Nipple (G). Secure by threading the Hex Nut (D) onto the Nipple (G). Hand tighten until snug. Cut the wires leaving approximately 6" of wire extending from the Ceiling Canopy.
- B. Optional Swivel: Install the swivel to the Fixture Body (K) and then attach Nipple (G) and the Ceiling Canopy (F) to the swivel using the Lock Washer (E) and the Hex Nut (D) as in step A.




Figure 1B

STEP 4A - Wire Connections

- A. Use standard wire connectors (not included) to make all wire connections. (Connectors are not included with fixture.) Twist connectors until wires are tightly joined together. Wrap each connection with approved electrical tape and carefully stuff all the connected wires into the Outlet Box.




Figure 4A

STEP 5A – Install Ceiling Canopy

- A. Carefully tuck all wires into the outlet box and position the Ceiling Canopy (F) over the outlet box. Align the holes in the Ceiling Canopy (F) with the mounting screws, then attach the Ceiling Canopy (F) using the previously removed mounting balls. Hand tighten until snug.




Figure 5A

STEP 6A - Install Shade and Bulb

- A. Place the Shade (I) over the Socket and secure with the Socket Collar (J). Hand tighten until snug.
- B. This fixture uses standard bulbs with standard screw bases. Maximum 100 watts. Insert bulb and screw snugly into place.





Figure 6A

Your fixture is now assembled and ready to use. Enjoy!

Assembly Instructions for Track Light (Step 1B - Step 6B)

Part B, Part C and Part H will not be used in the assembly of the Track Light fixture. Please set aside these parts.



STEP 1B – Install Ceiling Canopy to Socket Assembly

- A. Pass supply wires with ground wire through Nipple (G), Ceiling Canopy (F), Lock Washer (E) and Hex Nut (D). Thread Nipple (G)

STEP 4B - Wire Connections

- A. Use standard wire connectors (not included) to make all wire connections. (Connectors are not included with fixture.) Twist connectors until wires are tightly joined together. Wrap each connection with approved electrical tape and carefully stuff all the connected wires into the Outlet Box.




Figure 4B

STEP 5B – Install Ceiling Canopy

- A. Carefully tuck all wires into the outlet box and position the Ceiling Canopy (F) over the outlet box. Align the holes in the Ceiling Canopy (F) with the mounting screws, then attach the Ceiling Canopy (F) using the previously removed mounting balls. Hand tighten until snug.




Figure 5B

Thank you for purchasing a Quoizel product.
Need assistance with parts or assembly? Call Quoizel customer service at 1-631-273-2700
or visit us on-line at www.quoizel.com

STEP 6B - Install Shade and Bulb

- A. Place the Shade (I) over the Socket and secure with the Socket Collar (J). Hand tighten until snug.
- B. This fixture uses standard bulbs with standard screw bases. Maximum 100 watts. Insert bulb and screw snugly into place.

Your fixture is now assembled and ready to use. Enjoy!










Figure 6B

TFAS1404VA
FINISH: VALIANT BRONZE

ISLAND LIGHT



TRACK LIGHT



NOTE: ALL DIMENSIONS ARE ROUNDED UP TO THE NEAREST 1/4"

NO.	PART NUMBER	REPLACEMENT PART	REQ.
1	G3574SH	SHADE	4
2	9007EXVA	6" ROD	2
3	9008EXVA	12" ROD	2

Thank you for purchasing a Quoizel product.
Need assistance with parts or assembly? Call Quoizel customer service at 1-631-273-2700
or visit us on-line at www.quoise.com