SDP3 LED Single Installation Instructions

NOTE: Turn power off before wiring.


Recessed - Cut a 2-1/4" hole in a desired location. Remove puck light from surface mounting ring (Fig. 1). Push Puck Light up into hole where springs enable a snug fit (Fig. 2).

Surface Mount - Install surface mounting ring with 2 screws (supplied) in the desired location making sure that wires are routed through notch cut in surface mounting ring. Push recessed puck light up into surface mounting ring, enabling springs to secure a snug fit (Fig. 2).

Connect the red fixture leads to the positive leads or existing/ installer supplies leads to the power supply Connect the black fixture leads to the negative leads or existing/installer supplies leads to the power supply

DIMMING: Use dimmable magnetic 12 volt power supplies(LTHM series) and MLV switches.

For ELECTRONIC DIMMABLE POWER SUPPLIES (LTF series) use ELV type dimmer switches, I.E. lutron DVELV, MAELV type switches .



<u>GMLighting</u>

9830 W. 190th Street • Unit F • Mokena, IL 60448 Toll-Free (866) 671-0811 FAX: (708) 478-2640 www.gmlighting.net • Specifications subject to change without notice. SDPLED3Wpuckinst_0090415