

## INSTALLATION INSTRUCTIONS




Retrofit Device (Part No. EZDR200, EZDR400)



EZDR200 only: Rear Plate Adjustment





Optional Ground Attachment




Parts Included (Not to Scale)

## Sleeve Mounted Installation







Page 1 of 2 Warranty: www.stifirestop.com/legal/warranty Made in USA · Printed in USA ZIS1254 3478



Specified Technologies Inc. Somerville, NJ 08876 USA

T: (800) 992-1180 F: (908) 526-9623






## INSTALLATION INSTRUCTIONS

EZYPath FIRE-RATED PATHWAY

Retrofit Device (Part No. EZDR200, EZDR400)

## Surface Mounted Installation



Note: Cables are deliberately not shown in any of the images to clarify device installation. However, a visual cable loading of 50 to 100% is required. For cable types and sizes, refer to applicable UL Certified Systems.

For fastener types, consult the latest UL® fire resistance directory for permissible types and sizes.

Page 2 of 2
Warranty: www.stifirestop.com/legal/warranty
Made in USA • Printed in USA
ZIS1254 3478



Specified Technologies Inc. Somerville, NJ 08876 USA T: (800) 992-1180 F: (908) 526-9623 www.stifirestop.com



