



Representative

Catalog Number: B 940 2
Product ID: 7TAA004070R0024
UPC Number: 78599175831
Status: Active

Corner Brace, Overall Length 13-1/2 Inches, Length from Mounting Hole to Wall 12-3/4 Inches, Diagonal Length 16-5/8 Inches, Width 1-1/2 Inches, Steel with 9/16 Inch Holes

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	31162503 Braces
IGCC	3011 Braces
Brand Name	Kindorf
Type	Fittings & Hardware
Application	For use with Kindorf channels.
Material	Steel
Length	13-1/2 Inches
Width	1-1/2 Inch
Finish	Galv-Krom/Standard
Number Of Holes	2
Holes Per Leaf	1
Mounting Hole Size	9/16 Inch
Number Of Braces	1
Brace Type	Corner

European Specifications (ETIM)

ETIM	EC000482 Mounting element for support/profile rail
Suitable for	U-profile
Model	Mounting base
With screw accessories	N
Material	Steel

Packaging

Outer Quantity	10
Outer Dimensions (inches)	18.5x8.4x4.5
Weight Uom	203 lbs. per 100

Documents / Support Tools

Technical Data Sheet US Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com