



Representative Image

**Catalog No. THQMV200D**

**Description: 200A PMGOLD L/C MAIN BKR TOP 22K**

**UPC No 783164338508**

**Products > Load Centers > Residential Load Centers > Accessories/Parts**

PowerMark Gold Main Circuit Breakers for use with 150A-225A PowerMark Gold Load Centers (Includes mounting base). Main Circuit Breaker Kits 22,000 AIC. 60°C / 75°F Conductor Rating. Box Type Terminals. Quick-Make, Quick-Break. Multi-pole Breakers Incorporate Internal Common Trip. UL Listed.

**Descriptors**

Category	Accessories/Parts
GO Schedule	RM

**Specifications**

Amperage	200 A
GSA Compliance	No

## Publications

Title	Publication No.	Publication Type
<a href="#">Molded Case Circuit Breaker Q-Line Enclosure Compensated Long Time Delay and Instantaneous, Type THQMV</a> 1 page time current curve	GES-9923B	Time Current Curves

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.