

MINKA-LAVERY®

Item #: 1425-84	UPC Code: 747396044675
Product Family Name: Paradox™	Finish: BRUSHED NICKEL
Category: Chandeliers	Category Type: Chandelier
Certification E127416	
Patents	
Notes: *Also available 1425-281	



Image File Name:

1425-84--
1377121171.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
27	27	23.5	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
Yes	26.50	97.50	Yes
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight:
120	72	No	13.54
Canopy Width:	Canopy Height:	Canopy Length:	
5.00	1.00		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs:	Light Type:			
5	A19 Med			
Max Bulb Wattage:	Socket:			
100	E26 Med			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes				No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				

SHADE / GLASS

Description:	Material:	
	Glass	
Part No.:	Quantity:	
G5421	5	
Width:	Height:	Length:
6.38	4.50	6.38



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
12.500	21.500	25.500	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
20.900	3.966	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
		1	1



Title 17

Yes



UL Listed

Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties

Rev 12.31.2015