


## PT2FIT -- FRPT Pedestal Series

**PT2FIT**

Hubbell Introduces a new fire-rated poke-through fitting that accommodates various communication cable capacity levels. The new single service fire-rated poke-through incorporates a two inch conduit that is designed to support up to 36 low voltage cables in one location. These two inch single service units are UL listed for floors with a 1-2 hour fire rating.

### Product Specifications

<b>Product Type</b>	 <b>Furniture Feeds</b>
<b>Furniture Feed Services</b>	Large Capacity Furniture Feed
<b>Flush Furniture Feed Offering</b>	Through Floor Fitting
<b>Complies with:</b>	UL 514A requirements for scrub water protection.
<b>Fire Rating</b>	For use in 1, 1 1/2, 2, 3 or 4 hour rated unprotected reinforced concrete floors or in 1, 2 or 3 hour rated floors employing steel floor units and concrete topping (D900 series design).
<b>Floor Thickness Range</b>	2 1/4" (over metal deck) to 7" (57.2 to 117.8)
<b>UL Installation Spacing</b>	Minimum of 2 feet on centers and not more than one unit per 65 sq. ft. of floor area in each span.
<b>Cored Hole</b>	3" (76.2) diameter
<b>Conduit Tubes</b>	2" EMT
<b>Listings</b>	UL Listed, CSA Certified
<b>Note:</b>	When connecting conduit sweeps to through-floor fittings, ensure compliance with NEC fill tables.
<b>Wiring Capacity: Voice/Data Only</b>	Up to 36 low voltage cables at .21" (5.3) diameter.
<b>Plenum Rating</b>	Acceptable for use in environment air handling spaces per NEC article 300.22(C).
<b>Catalog Page</b>	<a href="#">Click here for catalog page M18</a>

<b>Brochures</b>	<a href="#">Click here for product brochure</a>
<b>Hubbellnet</b>	<a href="#">Click here for Hubbellnet</a>
<b>Catalog Section</b>	<a href="#">Click here for Section-M</a>
<b>UPC Number</b>	78358549815
<b>Weight in LBs</b>	3.65

