



Job Name:

Job Type:

Comments:

Quantity:

### 96116S-33: Lx LED Frosted Festoon Lamp - 2700K 12v Dimensions:



**Bulb Appearance:**

**Gas Filled:**

**Bulb Base:** festoon

**Volts:** 12

**Watts:** 0.78

**Watts Consumed:** 0.78

**Watts Rated:** 0.78

**Hours Rated:** 35000

**Bulb Temp:** 2700 °K

**CRI:** 85

#### Features:

- The advanced LED technology in Sea Gull Lighting products is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

**Collections:** Ambiance® Lx LED Festoon (Primary)  
Ambiance® LED Under Cabinet

It's a snap to upgrade existing xenon linear systems to energy saving, money saving lighting.  
No need to replace or re-invest in your entire system.  
The LED festoon is an opportunity to retrofit or replace traditional under-the-counter systems and fills the need to provide "green" lighting solutions.

Applications: Task & accent lighting for undercabinet, coves, toe-kick spaces and so much more. Directional nature of LED is ideal for in-cabinet lighting.

Retrofit/Remodel Installations for Magnetic Transformer Systems -  
JUST REPLACE THE LAMP!

Compatible as a retrofit for existing Lx xenon lamp and compatible xenon lamp systems.

Note: The unique design of the PCB (Printed Circuit Board) makes over voltage due to under capacity a non-issue.

Retrofit/Remodel Installations for Electronic Transformer Systems  
60w zero-load 12V AC electronic transformer replacing electronic transformers due to minimum load requirement. Available 60W 12V AC electronic transformers: 96223S-12 & 96223S-15.

Product Features: Ease of installation. Ease of retrofit/remodel.  
Bendable/flexibility of the system.

Dimmability: Dimmable with standard incandescent dimming switch.

A "Fit & Forget" Solution: Offering 35,000 hours of useful life  
(equivalent to 30 years at 20 hours of use per week)

Efficacy Warmer White 2700K: 30 Lumens/Watt

Color Rendering: 2700K - CRI 90+

#### Material List:

#### Safety Listing:

ETL Listed for Damp Locations  
cETL Listed for Damp Locations

#### Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1715FS)

LED Festoon Product Line Options & Features:

12v and 24v

Warm (2700K), (3000K)

Cool (4000K)

Clear lens for optimal performance

Frosted lens to reduce glare

Color-coded PCB to visually distinguish between warm and cool color temperature LED festoons

Color-coded end-caps to identify 12v (white) and 24v (black)

3 Year Warranty

UPC #:785652198618

**Shipping Information:**

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	96116S-33	1	785652198618	2	2	0.625	0.001	0.01	Yes
Master Pack		10	10785652198615	9	2.25	1	0.012	0.2	Yes