



## Catalog No. TM2415C42

Description: 150AMCB LC 24-42CRT N1 22K COMB

UPC No 783164402858

Home > Load Centers > Residential Load Centers

Panelboards No. 67 60 degree/75 degree centigrade Conductor Rating Suitable for use as service entrance equipment when Installed in accordance with the National Electrical Code 22kAIC RMS symmetrical, Except Where Noted 6-42 circuit devices UL Listed for bottom mounted lugs by installing complete unit (box, interior and front) upside down For a listing of CSA Listed load centers, visit [www.geelectrical.com](http://www.geelectrical.com) Amperage 150 A 5C422858

### Descriptors

Category	Residential Load Centers
GO Schedule	RD

### Specifications

Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Amperage	150 A
Enclosure	Indoor Type 1 Enclosure, Combination
UL/CUL Listing	UL
Phase	1 Phase
1" Space	24
1/2" Space	36
Feed	Either
Door	Yes
GSA Compliance	No

## Publications

Title	Publication No.	Publication Type
<a href="#">PowerMark Gold* Load Centers, Q-Line Circuit Breakers and Accessories Guide</a> Guide includes product features, photos, product number selection guide, knockout drawings, wiring diagrams, accessories and options list. Only available on-line. <a href="#">Indoor Load Center</a> 1 page outline drawing in pdf format.	DET1023  10103091-SH20	Application and Technical  Drawings-Outline and Dimensional

**Additional Documentation:** Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.