

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5582-31

Welbourne

The Welbourne collection features hexagonal framework with vine inspired scrolls and clear beveled glass panels. Cast aluminum construction with durable powder coat finish. One-light hanging lantern.



Diameter: 9-3/8"
Height: 14-1/16"
Overall ht. w/chain: 53"

Category: Outdoor

Finish: Textured Black (painted)

Construction:

Glass: Clear beveled glass panels

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|---|---|--|
| Ceiling chain mounted Mounting strap for outlet box included Three feet 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box 4-1/2" dia. | Pre-wired 10 feet of wire supplied 120V | Quantity: 1 100W Medium Base Medium base porcelain socket | UL-CUL Damp location listed 1 year warranty Companion fixtures are available |