RDL-ADJ MCT5





TECHNICAL SPECIFICATIONS:

- :: Multi CCT (Selectable Switch on the Back of the driver)
- :: Dimmable down to 10% using a standard TRIAC LED dimmer
- :: Tilts to 45°
- :: Can rotate after installation to align
- :: LED: Epistar chip (COB)
- :: Die-cast aluminum with white powder coat finish
- :: Trim ring: Integrated spun aluminum white powder coat finish
- :: Gasket: closed cell Neoprene foam gasket
- :: Lens: 0.125" white translucent acrylic
- :: CRI: 90
- :: Power factor: 90% +
- :: Maximum Ambient Temperature: 104°F
- :: Rated life: 50,000 hrs
- :: Suitable for West locations
- :: 5-year warranty

TECHNICAL SPECIFICATIONS:

:: LED retrofit trim have been designed to be a flexible lighting solution for retrofit and new construction applications, Ideal for closets, storage areas, attics, corridors, or general lighting solutions for residential and commercial applications



W

LED DOWNLIGHTS (ADJUSTABLE)-4" & 6" ROUND

CATALOG NO.	WATTS	COLOR TEMP	LPW	DIAMETER
RDL4-ADJ-MCT5	8W	2700K/3000K/3500K/4000K/5000K	81LM/W	4"
RDL6-ADJ-MCT5	11W	2700K/3000K/3500K/4000K/5000K	81LM/W	6"

WESTGATE MFG W W W . W E S T G A T E M F G . C O M T O L L F R E E : 877.805.2252 F A X : 877.809.2252