



Mini-Candelabra

BC100Q/CL ESN 12/1P

Bright, white light with higher performance for accent lightingHalogen Mini Candelabra T4 Capsule lamps provide bright, white light for decorative and accent lighting and general illumination. Offered in T4 bulb size with mini candelabra base configurations. These lamps offer a rated average life ranging from 1000 to 2000 hours depending upon the product.* Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

Product data

General Information	
Cap-Base	E11 [Mini Candelabra]
Operating Position	UNIVERSAL [Any or Universal (U)]
Gas Filling	Gas
Light Technical	
Luminous Flux (Nom)	1600 lm
Correlated Color Temperature (Nom)	2800 K
Color Rendering Index (Nom)	100
Operating and Electrical	
Power (Rated) (Nom)	100 W
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Filament Shape	CC-8 [Axial]
Product Data	
Order product name	BC100Q/CL ESN 12/1P
EAN/UPC - Product	046677416331
Order code	926000850098
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	926000850098
Net Weight (Piece)	0.009 kg

Datasheet, 2016, October 10 data subject to change

Mini-Candelabra

Dimensional drawing

Product

BC100Q/CL ESN 12/1PK



MINI CANDL 100W 120V T4 CC-8 CL

