



**Liquidtight Flexible Cord & Cable Fittings**

**T&B Catalog Number:**

4961NM

**UPC Number:**

78621079750

**Status:**

Active

**Description:**

1/2 in. 90 degree nylon Ranger liquidtight cord connector, cord range .310-.560

**Features**

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.

**Application**

- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.

**General**

Material	Nylon
Cord and Cable Types	S, SO, SV, ST, STD, SJ, SJO, SJT, SJTO, SVD

**Dimension Information**

Hub Size (inches)	1/2
Dimension A (inches)	1 7/32
Dimension B (inches)	1 1/4
Dimension C (inches)	5/8
Cord Range (inches)	.310-.560
Throat Diameter (inches)	0.55

**Specifications**

3dmodel	Available on Website
---------	----------------------

**Packaging**

T&B Inner Pack	25
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	6.7 lbs. per 100

**Application Support**

T&B Instruction Sheets	ta00927-tb2
Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
E 13938

**For further technical assistance, please contact us...**

8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)