

FEISS

EST. 1955

OL1900BK: 1 - Light Wall Lantern



Dimensions:

Width: 7" **Extends:** 8 1/4"
Height: 11 3/4" **Wire:** 8"
Weight: 4.75 lbs. **Connection:** Mounted To Box

Bulbs:

1 - Medium A19 100w Max. 120v - Not included

Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
-

Material List:

1 Body - Aluminum - Black

Safety Listing:

Safety Listed for Wet Locations

Instruction Sheets:

English (2019)

Collection: Castle

UPC #:014817218756

Finish: Black (BK)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Clear Glass	Undefined	1									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	7 1/2	4 1/2			4	7 3/4

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	OL1900BK	1	014817218756	14	8	9	0.583	4.7	100	Yes

Feiss reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Feiss. In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Feiss LLC, A Generation Brands Company.

NJ Pallet		84		48	40	76	84.444	394.8		No
NV Pallet		96		48	40	76	84.444	394.8		No